

## Vario Starpoint VRS-F type metric ring bolt

Screwable sling point, 360° rotation



### Application:

For the safe attachment of loads.

### Execution:

- Forged, high-strength annealed
- 100% electromagnetically crack-tested in accordance with DIN EN 1677-1
- Patented 100% crack-tested hexagon socket screw, non-detachable
- can be rotated 360°
- Stated carrying capacity for adverse load area F
- Powder-coated surface: pink, fluorescent

### Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing
- Tool-free assembly

### Delivery:

Includes annealed star profile key for tool-free assembly. Special lengths and other threads upon request.



<b>Art. no.</b>	<b>77232 030</b>
<b>Brand</b>	RUD
<b>Manufacturer Part Number</b>	25250000015194
<b>Thread dimension</b>	M30
<b>Load-carrying capacity</b>	4500 kg
<b>Distance between lower edge of retainer holder and retainer</b>	87 mm
<b>Internal width</b>	60 mm
<b>Width of support plate</b>	66 mm
<b>Usable thread length</b>	45 mm
<b>Colour</b>	Pink
<b>Gross Weight</b>	1.920 kg
<b>Product Group</b>	781