


Bootlace Ferrules



SPECIFICATION:

Temperature range	-40 ... +105 °C
Material	Copper
Insulation material	Polyamide
Surface material	Tin-Plated
Termination	Crimp



Colour System

				Dimensions (mm)			
French	German	DIN	Wire Range	Pin Length (L1)	Overall Length (L2)	Terminal Diameter (D1)	Outside Diameter (D2)
	Grey RND 465-00552		26 AWG 0.14 mm ²	6 ± 0.8	10 ± 3.0	0.70 ± 0.30	1.6 ± 0.4
Violet RND 465-00565	Light Blue RND 465-00537		24 AWG 0.25 mm ²	6 ± 0.8	10 ± 3.0	0.75 ± 0.30	1.9 ± 0.4
RND 465-00899	RND 465-00538		24 AWG 0.25 mm ²	8 ± 0.8	12 ± 3.0	0.75 ± 0.30	1.9 ± 0.4
Pink RND 465-00908	Turquoise RND 465-00564		22 AWG 0.34 mm ²	6 ± 0.8	10 ± 3.0	0.80 ± 0.30	1.9 ± 0.4
RND 465-00558	RND 465-00563		22 AWG 0.34 mm ²	8 ± 0.8	12 ± 3.0	0.80 ± 0.30	1.9 ± 0.4
White RND 465-00566	Orange RND 465-00556	White RND 465-00566	20AWG 0.5 mm ²	8 ± 0.8	14 ± 3.0	1.00 ± 0.30	2.6 ± 0.4
Blue RND 465-00540	White RND 465-00567	Grey RND 465-00546	18 AWG 0.75 mm ²	8 ± 0.8	14 ± 3.0	1.20 ± 0.30	2.8 ± 0.4
RND 465-00541	RND 465-00568	RND 465-00883	18 AWG 0.75 mm ²	12 ± 0.8	18 ± 3.0	1.20 ± 0.30	2.8 ± 0.4
Red RND 465-00559	Yellow RND 465-00569	Red RND 465-00559	18 AWG 1.0 mm ²	8 ± 0.8	14 ± 3.0	1.40 ± 0.30	3.0 ± 0.4
RND 465-00562	RND 465-00570	RND 465-00562	18 AWG 1.0 mm ²	12 ± 0.8	18 ± 3.0	1.40 ± 0.30	3.0 ± 0.4
Black RND 465-00533	Red RND 465-00561	Black RND 465-00533	16 AWG 1.5 mm ²	8 ± 0.8	14 ± 3.0	1.70 ± 0.40	3.5 ± 0.4
RND 465-00531	RND 465-00560	RND 465-00531	16 AWG 1.5 mm ²	10 ± 0.8	16 ± 3.0	1.70 ± 0.40	3.5 ± 0.4
RND 465-00534	RND 465-00884	RND 465-00534	16 AWG 1.5 mm ²	18 ± 0.8	24 ± 4.0	1.70 ± 0.4	3.5 ± 0.4



Colour System				Dimensions (mm)			
French	German	DIN	Wire Range	Pin Length (L1)	Overall Length (L2)	Terminal Diameter (D1)	Outside Diameter (D2)
Grey RND 465-00549	Blue RND 465-00542	Blue RND 465-00542	14 AWG 2.5 mm²	8 ± 0.8	14 ± 3	2.2 ± 0.4	4.2 ± 0.4
			14 AWG 2.5 mm²	12 ± 0.8	18 ± 3	2.2 ± 0.4	4.2 ± 0.4
			14 AWG 2.5 mm²	18 ± 0.8	24 ± 4	2.2 ± 0.4	4.2 ± 0.4
Orange RND 465-00886	Grey RND 465-00548	Grey RND 465-00548	12 AWG 4.0 mm²	12 ± 0.8	20 ± 3	2.8 ± 0.4	4.8 ± 0.6
			12 AWG 4.0 mm²	18 ± 0.8	26 ± 4	2.8 ± 0.4	4.8 ± 0.6
Green RND 465-00544	Black RND 465-00536	Yellow RND 465-00887	10 AWG 6 mm²	12 ± 1	20 ± 3	3.5 ± 0.5	6.3 ± 0.6
			10 AWG 6 mm²	18 ± 1	26 ± 4	3.5 ± 0.5	6.3 ± 0.6
Brown RND 465-00890	Ivory RND 465-00554	Red RND 465-00891	8 AWG 10 mm²	12 ± 0.8	22 ± 3	4.5 ± 0.4	7.6 ± 0.5
			8 AWG 10 mm²	18 ± 1.0	28 ± 4	4.5 ± 0.5	7.6 ± 0.6
Ivory RND 465-00555	Green RND 465-00545	Blue RND 465-00894	6 AWG 16 mm²	12 ± 1.0	24 ± 4.0	5.8 ± 0.5	8.8 ± 0.6
			6 AWG 16 mm²	18 ± 1.0	28 ± 4.0	5.8 ± 0.5	8.8 ± 0.6
Black RND 465-00535	Brown RND 465-00897	Yellow RND 465-00898	4 AWG 25 mm²	16 ± 1.0	30 ± 4.0	7.3 ± 0.6	11.2 ± 0.8
Red RND 465-00900	Beige RND 465-00901	Red RND 465-00900	2 AWG 35 mm²	16 ± 1.0	30 ± 4.0	8.3 ± 0.6	12.7 ± 0.8
Blue RND 465-00902	Olive RND 465-00903	Blue RND 465-00902	1/0 AWG 50 mm²	20 ± 1.0	36 ± 4.0	10.3 ± 0.6	15 ± 1.8
		Yellow RND 465-00904	2/0 AWG 70 mm²	21 ± 1.0	37 ± 4.0	13.5 ± 0.6	16 ± 1.8
		Red RND 465-00905	3/0 AWG 95 mm²	25 ± 1.0	44 ± 4.0	14.7 ± 0.6	18.5 ± 1.8
		Blue RND 465-00906	4/0 AWG 120 mm²	27 ± 1.0	48 ± 4.0	16.7 ± 0.6	20 ± 1.8
		Yellow RND 465-00907	250/3000AWG 150mm²	32 ± 1.0	58 ± 4.0	19.5 ± 0.6	23 ± 1.8