



ORDERING INFORMATION



OPERATING CHARACTERISTICS

SWITCH TYPE	PART SUFFIX	OF Max. (gf)		OP (mm)	PT Max. (mm)	OT Min. (mm)	MD Max. (mm)
		H	S				
VW1- □□□ 0-00A0- □ B00 □ -Z		H	300	14.7±0.4	1.2	1.0	0.4
		S	200				
		L	150				
		J	100				
VW1- □□□ 1-01A0- □ B00 □ -Z		H	255	15.1±0.6	2.6	1.1	0.6
		S	160				
		L	125				
		J	85				
VW1- □□□ 2-01A0- □ B00 □ -Z		H	-	15.0±1.1	5.1	1.2	1.1
		S	-				
		L	90				
		J	--				
VW1- □□□ 1-02A0- □ B00 □ -Z		H	160	14.8±0.8	4.0	1.5	0.9
		S	110				
		L	85				
		J	60				
VW1- □□□ 1-03A0- □ B00 □ -Z		H	100	12.4±2.0	7.0	-	2.5
		S	70	13.4±2.0	7.0	-	2.0
		L	55				
		J	40				
VW1- □□□ 1-04A0- □ B00 □ -Z		H	-	18.1±0.8	3.6	1.7	1.0
		S	125				
		L	-				
		J	-				
VW1- □□□ 2-04A0- □ B00 □ -Z		H	-	16.7±1.5	7.2	2.1	1.7
		S	75				
		L	-				
		J	-				
VW1- □□□ 1-05A0- □ B00 □ -Z		H	-	20.6±0.5	2.1	1.0	0.5
		S	200				
		L	-				
		J	-				
VW1- □□□ 1-06A0- □ B00 □ -Z		H	195	20.4±0.7	3.3	1.3	0.7
		S	130				
		L	-				
		J	70				
VW1- □□□ 2-06A0- □ B00 □ -Z		H	105	20.2±1.2	6.5	1.5	1.4
		S	70				
		L	-				
		J	-				

* There is another series of VW1 with MD reduced to 63%.