


**1** Resistor - Weerstand - Résistance - Widerstand - Resistencia - Motstand - Vastus - Resistenze


- ◇R1: 3K3
- ◇R2: 3K3
- ◇R3: 3K3
- ◇R4: 3K3
- ◇R5: 3K3
- ◇R6: 3K3
- ◇R7: 3K3



(Orange, Orange, Red) - (Oranje, Oranje, Rood) - (Orange, Orange, Rouge) - (Orange, Orange, Rot) - (Orange, Orange, Röd) - (Oranssi, Oranssi, Punainen) - (Naranjado, Naranjado, Rojo) - (Laranja, Laranja, Encarnado) - (Aranciato, Aranciato, Rosso)

**2**


**DIODE** ◇D1: 1N4148  
Watch the polarity!




**3**

**LED**

- ◇LD1: 5mm
- ◇LD2: 5mm
- ◇LD3: 5mm
- ◇LD4: 5mm
- ◇LD5: 5mm
- ◇LD6: 5mm
- ◇LD7: 5mm




**4**



**5**

**Capacitor - Condensateur**


- ◇C1: 10nF (103)



**6**


**ELCO**

- ◇C2: 1µF
  - ◇C3: 1µF
- Watch the polarity!




**7**

**Trim potentiometer - Potentiomètre de réglage - Potentiometro de regulacion - Trimmerpotentiometri - Trimmerpotentiometer - Trimmerpotenziometri**



**8**

**IC Socket - IC voet - Support de CI - IC Fuß - Soporto del CI - IC Socket - Mikroopiirkanta - IC sokkel - Zoccolo IC**




**9**

**IC - CI**

IC1: 555

IC2: 4015



**10**

