

Proximity Switch and Magnet Set

Part Number : CEA-203
Product Data Sheet



PICTURE DIMENSIONS 43 1000 500 17 44 43 Countersunk MAGNET SIZE THE SAME AS SVITCH Drawings not to scale All dimensions in mm nominal

SPECIFICATION				
Contact Form / Style		Normally Open + Supervisory loop		
Grade		2		
Switching Voltage	Max Volts AC/DC	50		
Switching Current	Max Amps	0.5		
Carry Current	Max Amps	0.8		
Switching Capacity	Max W/VA	10		
Insulation Resistance	Max MOhms	100		
Contact Resistance	Max mOhm's	120		
Operating Temperature	Celsius	- 40° to 85°		
Case Material		Aluminium		
Operating Distance	Millimetres	15		
Applications Include		Options		

- Alarm Systems.
- Appliance switching.
- Production Automation.
- Safety Door Guards.

- Armoured or non armoured types available.
- Normally closed and Change over types available.

Did you know we also sell?



- Custom cable types, cable lengths, connectors or crimp terminals.
- If you do not see what you need, just ask, as there is a strong possibility we can do it!

Rev. No.	Revision Note	Date	Signature
1	Datasheet	01-07-15	ML

Solid State



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: +44 (0)1255 862236

www.comus-intl.com

Fax: +44 (0)1255 862014