




AS-Interface diagnosis module

AS-i Tuner IP67



Application	
Application	diagnostic tool for AS-i
Electrical data	
Nominal voltage DC [V]	26.5...31.6
Max. current consumption from AS-i [mA]	60
Reverse polarity protection	yes
Undervoltage monitoring	yes
Operating conditions	
Ambient temperature [°C]	0...55
Protection	IP 67
Tests / approvals	
MTTF [years]	140
AS-i classification	
AS-i certificate pending	yes

AC1146



AS-Interface diagnosis module

AS-i Tuner IP67

Mechanical data		
Weight [g]	196.5	
Materials	PBT	
Displays / operating elements		
Display	operation	LED, green
	warning	LED, yellow
	errors	LED, red
Accessories		
Accessories (optional)	Module lower part, AC5000	
Remarks		
Remarks	no addressing required current rating of the AS-i distribution socket max. 1 A	
Pack quantity	1 pcs.	
Electrical connection		
contact pins to module lower part, FK:		
	AS-i distribution socket M12	
1	AS-i +	
3	AS-i -	
Connector: M12		