

Product information

00 21 35

Tool Case "Robust23" Electric



- Equipped with 25 brand tools, partly VDE-tested according to DIN EN 60900
- Max. payload: 25 kg
- Volume: 23 litres
- For the toughest conditions: Dust-tight, waterproof and temperatureresistant
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with space for 33 tool pockets and various tool straps
- With a total of 49 inserting options
- Base tray with aluminium inserts
- Dimensions exterior (W x H x D): 470 x 370 x 190 mm; dimensions interior (W x H x D): 437 x 307 x 172 mm
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle



General	
Article No.	00 21 35
EAN	4003773084365
Weight	6,775 g
Dimensions	307 x 172 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Dimension exterior (interior) width mm	470 mm (437 mm)
Dimension exterior (interior) height mm	190 mm (172 mm)
Dimension exterior (interior) depth mm	370 mm (307 mm)

technical change and errors excepted

