


Tantalum, MnO2 Tantalum, Commercial Grade, T354, 47 uF, 10%, 35 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 6.35mm



General Information	
Dielectric:	MnO2 Tantalum
Style:	Radial
Series:	T354
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Dimensions	
D	10.2mm
H	18.6mm
S	6.35mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.5mm +/-0.05mm

Specifications	
Capacitance:	47 uF
Capacitance Tolerance:	10%
Voltage DC:	35 VDC (85C), 28 VDC (125C Surge), 0.35 V (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	8%
Leakage Current:	4.3 uAmps

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	100