



PRODUCT CATALOGUE

19/20 · BRITISH STANDARD


brennenstuhl®

_ smart technology.


brennenstuhl®



– smart technology.

**It is our aspiration to be your reliable
and trustworthy partner.
This will also be true for the future.**

There have truly been calmer times. Our industry faces rapidly changing markets and major challenges. Rest assured that you are in good hands with our family-run company. Reliability and trustworthiness in our customer relationships is our task.

In fast-paced times, this is no longer a matter of fact. Many things have to be adjusted on the test stand to satisfy the latest market requirements. In order to be a good partner, however, we don't have to re-invent ourselves. We feel obliged to do so - not only tomorrow, but always. You can rely on us!

Thank you for your trust.



Dr. Wolfgang Dehler-Brennenstuhl
Managing Director




Sebastian Brennenstuhl
Managing Director

INDEX

	POWER DISTRIBUTION 400 V / 240 V 240 V 110 V - POWER DISTRIBUTION & LIGHTING	5
	EXTENSION SOCKETS BS 1363 SURGE PROTECTION	27
	PLUG-IN APPLIANCES BS 1363 SURGE PROTECTION	53
	LIGHTING	65
	HOME SECURITY & SAFETY	97
	HOME, WORKSHOP & DIY	101
	ADVERTISING MEDIA & DISPLAYS	115



Key to cable quality



1 Definition

- H = Harmonised cable
- A = Nationally recognised cable

2 Nominale Voltage (Volt)

- 03 = 300 / 300 V
- 05 = 300 / 500 V
- 07 = 450 / 750 V

3 Isolating Sheath

- V = PVC
- R = Natural or synthetic rubber
- S = Silicone rubber
- B = Synthetic rubber

4 Outer Sheath

- V = PVC
- R = Natural or synthetic rubber
- N = Neoprene
- J = Glass fibre
- T = Textile
- Q = Polyurethane

5 Cable Type

- U = Round, single-wire cable
- R = Round, multi-wire cable
- K = Fine wire for permanent installation
- F = Fine wire for moveable cables
- H = Extremely fine wire for moveable cables
- Y = Tinsel wire

6 Number of Wires

- G = With green-yellow wire
- X = Without green-yellow wire

8 Diameter of Cable Core in mm²

The right cable for every use:



Standard version for normal use in dry conditions.
With insulated inner wire coating and outer cable casing made of flexible PVC.



Standard version for durable use in dry conditions and for temporary outside use.
Inner wire coating and outer cable casing made of synthetic rubber.



BREMAX[®]

NO7 cable: For outside use
NOS cable: For temporary outside use.



High mechanical loading capacity. Applicable down to -35 °C, oil- and UV-resistant and highly abrasion-resistant. Outer cable casing made of highly flexible special plastic.



For long-term outside use.
Resistant against oils and acids. Inner wire coating made of natural or synthetic rubber. Outer cable casing made of neoprene.



International Protection Classes

Code letters International Protection		First index figure Foreign bodies protection		Second index figure Water protection	
IP		6		8	
Index		Index		Index	
0	No protection against accidental contact, no protection against solid foreign bodies	0	No protection against water		
1	Protection against contact with any large area by hand and against solid foreign bodies with $\varnothing > 50$ mm	1	Protection against vertical water drops		
2	Protection against contact with the fingers, protection against solid foreign bodies with $\varnothing > 12,5$ mm	2	Protection against diagonal water drops (up to a 15° angle)		
3	Protection against tools, wires or similar objects with $\varnothing > 2.5$ mm, protection against solid foreign bodies with $\varnothing > 2.5$ mm	3	Protection against diagonal water drops (up to a 60° angle)		
4	As 3, but $\varnothing > 1$ mm	4	Protection against splashed water from all directions		
5	Full protection against contact, protection against interior injurious dust deposits	5	Protection against water (out of a nozzle) from all directions		
6	Total protection against contact, protection against penetration of dust	6	Protection against ingress of water in case of powerful water-jets		
		7	Protection against ingress of water in case of temporary immersion		
		8	Protection against ingress of water in case of continuous immersion, requirements under agreement of user and manufacturer		

Degrees of protection to IEC 529 EN 60529

- IP 20** Protected against access to hazardous parts with a finger
- IP 21** Protected against vertically falling water drops
- IP 23** Protected against spraying water
- IP 40** Protected against solid objects of 1 mm diameter and greater
- IP 43** Protected against solid objects 1 mm and against spraying water
- IP 44** Protected against solid objects 1 mm and against splashing water
- IP 50** Dust-protected
- IP 54** Dust-protected and protected against splashing water
- IP 55** Dust-protected and protected against water-jets
- IP 56** Dust-protected and protected against powerful water-jets
- IP 65** Dust-tight and protected against water-jets
- IP 67** Dust-tight and protected against temporary immersion in water
- IP 68** Dust-tight and protected against continuous immersion in water

Guaranteed Top Quality

All electrical appliances are manufactured by Brennenstuhl according to strictest quality and safety rules. They correspond to the valid international regulations and are approved by an appropriate authority.



POWER DISTRIBUTION



CABLE REELS

CEE 400 / 240 V

6



CABLE REELS

BS 240 V

10



POWER DISTRIBUTION & DOMESTIC CABLE REELS

BS 240 V

16



CABLE REELS & DOMESTIC CABLE REELS

CEE 110 V

20



POWER DISTRIBUTION & LIGHTING

CEE 110 V

23



CABLEPILOT



Hands-free transport
Carry reels with ease with the **CABLEPILOT**, even if you don't have a hand free.



Practical to hang up
The **CABLEPILOT** lets you hang the cable reel securely from a scaffold or ladder.



Super fast, safe roll-up and roll-out
Perfect cable management even when the cable is reeled in quickly; the **CABLEPILOT** keeps the cable on track.



Pendulum handle
Cable from the right or left - the **CABLEPILOT** is flexibly adaptable.



The autopilot for cable reels.



Garant® CEE 1 IP 44 Cable Reel

Practical and suitable for outdoor use, IP 44.

- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Innovative and ergonomic cable guide handle „cable pilot“ for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- 1 CEE-plug 400 V/16 A,
1 CEE-socket 400 V/16 A,
with 2-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- The **BREMAXX**® cable is extremely sturdy, applicable down to -35 °C, oil- and UV-resistant and highly abrasion-resistant.
- Earthed sockets connected to separate phases.
- With 3-pin safety cut-out and thermal overload protection.



Article No.	EAN-Code	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Socket
1 18277 3	630882	1	25 m	AT-N07V3V3-F 5G1,5	BREMAXX ®	Red	290 mm	1 x 400 V/16 A 2 x 13 A BS

Patent pending.



CEE Extension Cable IP 44

For universal outdoor use and permanent use on sites, IP 44.

- Ideal for hard outdoor use.
- Special rubber extension cable with CEE-socket and plug with cap.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Plug	Socket	Number of poles
1.5 mm² cable									
1 16771 0	005796	1	10 m	H07RN-F 5G1,5	Rubber-Neoprene	Black	CEE 400 V/16 A	CEE 400 V/16 A	5
1 16773 0	005826	1	30 m	H07RN-F 5G1,5	Rubber-Neoprene	Black	CEE 400 V/16 A	CEE 400 V/16 A	5
2.5 mm² cable									
1 16774 0	018239	1	10 m	H07RN-F 5G2,5	Rubber-Neoprene	Black	CEE 400 V/16 A	CEE 400 V/16 A	5
1 16772 0	021550	1	25 m	H07RN-F 5G2,5	Rubber-Neoprene	Black	CEE 400 V/16 A	CEE 400 V/16 A	5
4.0 mm² cable									
1 16797 0	029112	1	10 m	H07RN-F 5G4,0	Rubber-Neoprene	Black	CEE 400 V/32 A	CEE 400 V/32 A	5
1 16850 0	190867	1	25 m	H07RN-F 5G4,0	Rubber-Neoprene	Black	CEE 400 V/32 A	CEE 400 V/32 A	5



BREmaxX® CEE Extension Cable IP 44

Practical and suitable for outdoor use, IP 44.

- BREmaxX® cable - anti-freezing, highly flexible down to -35 °C, oil and UV resistant, high mechanical loading capacity.
- Excellent abrasion resistance.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Plug	Socket	Number of poles
1 16858 0	151929	1	10 m	AT-N07V3V3-F 5G1,5	BREmaxX®	Signal red	CEE 400 V/16 A	CEE 400 V/16 A	5
1 16859 0	151936	1	25 m	AT-N07V3V3-F 5G1,5	BREmaxX®	Signal red	CEE 400 V/16 A	CEE 400 V/16 A	5



Garant® CEE 2 IP 44 Cable Reel for Site & Industry

For universal outdoor use and permanent use on sites, IP 44.

- Tested acc. to EN 61316.
- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Innovative and ergonomic cable guide handle „cable pilot“ for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- CEE plug 230 V/16 A, 2 CEE sockets 230 V/16 A.
- With single pole safety cut-off and overheating protection.

- 1 RN cable is approved to exacting site standards as per VDE 0100 part 704.
- 2 The **BREMAXX**® cable is extremely sturdy, applicable down to -35 °C, oil- and UV-resistant and highly abrasion-resistant.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø
1 18276 0	140572	1	25 m	H07RN-F 3G2,5	Rubber-Neoprene	Black	290 mm
2 123807 3	081165	1	40 m	AT-N07V3V3-F 3G2,5	BREMAXX ®	Orange	320 mm

Design protected. / Patent pending.

Adapter 230 V/CEE

- Plug: CEE 16 A, 200 - 250 V, 50/60 Hz.
- Socket: BS 13 A, 240 V, 50/60 Hz, IP 54, childproof.



Article No.	EAN-Code 4007123...	UP	Plug	Socket	Equipment
1 08099 3	648221	1	CEE 16 A, 200 - 250 V, 50/60 Hz	BS 13 A, 240 V, 50/60 Hz, IP 54	with childproof socket
2 108099 0	648207	1	CEE 16 A, 230 V, 50/60 Hz	Schuko 16 A, 230 V, 50/60 Hz, IP 44	with childproof socket



Garant® G CEE IP 44 Cable Reel For Camping/Yacht Marina

Practical and suitable for outdoor use, IP 44.

- CEE plug 230 V/16 A.
- CEE socket 230 V/16 A.
- Extension cable reel with plug and trailing socket.
- Innovative and ergonomic cable guide handle „cable pilot“ for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- Rotary handle for comfortable rolling up.
- Reel body made from special plastic fitted to a galvanised steel tube frame.
- The **BREMAXX**® cable is extremely sturdy, applicable down to -35 °C, oil- and UV-resistant and highly abrasion-resistant.
- Thermal cut-out protection, indicator shows overheating.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø
1 18247 0	654451	1	20 m	AT-N07V3V3-F 3G2,5	BREMAXX ®	Orange	290 mm

Design protected. / Patent pending.



CEE 230 V Extension Cable IP 44

For site, industrial use, camping and yacht/marina, IP 44.

- Ideal for hard outdoor use.
- Special rubber extension cable with CEE-socket and plug with cap.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Plug	Socket
1.5 mm² cable								
1 16765 0 110	650781	2	10 m	H07RN-F 3G1,5	Rubber-Neoprene	Black	CEE 230 V/16 A	CEE 230 V/16 A
2.5 mm² cable								
1 16765 0 210	650798	2	10 m	H07RN-F 3G2,5	Rubber-Neoprene	Black	CEE 230 V/16 A	CEE 230 V/16 A
1 16765 0 225	650866	2	25 m	H07RN-F 3G2,5	Rubber-Neoprene	Black	CEE 230 V/16 A	CEE 230 V/16 A



Brobusta® Cable Reel

Quality for the highest demands.

- Extra heavy-duty, double welded steel-tube frame, galvanised & powder-coated, with ergonomic carrying handle.
- Drum is made of special highly breakproof plastic.
- All electrical parts are safety insulated from the reel body.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Thermal cut-out protection, indicator shows overheating.



Article No.	EAN-Code	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 31130 3	058105	1	50 m	H05VV-F 3G1,5	Plastic	Black	290 mm	13 A	BS 1363

Design Patent.



Super-Solid Cable Reel

Quality for the highest demands.

- Extra stable, shock-absorbing steel tube frame with galvanised steel tube, exclusive stability.
- Carry handle with comfortable cable guide management during winding.
- Rotary handle for comfortable rolling up.
- Reel body made of special plastic with reinforced ribbed structure.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Thermal cut-out protection, indicator shows overheating.



Article No.	EAN-Code	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 30895 3	576500	1	50 m	H05VV-F 3G1,5	Plastic	Black	290 mm	13 A	BS 1363

Patent pending.



Super-Solid S Cable Reel

Quality for the highest demands.

- Extra stable, shock-absorbing steel tube frame with galvanised steel tube, exclusive stability.
- Reel body made from rust-resistant and galvanised sheet steel.
- Carry handle with comfortable cable guide management during winding.
- Rotary handle for comfortable rolling up.
- All electrical parts are safety insulated from the reel body.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Thermal cut-out protection, indicator shows overheating.



Article No.	EAN-Code	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 30945 3	612017	1	50 m	H05VV-F 3G1,5	Plastic	Black	290 mm	13 A	BS 1363

Patent pending.





Garant® Cable Reel

Top in quality and design, for every requirement and use.

- Reel body made from special plastic fitted to a galvanised steel tube frame.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Ergonomic cable guide handle for perfect cable-management during winding.
- With thermal cut-out protection against overheating.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Reel-Ø	Cable colour	Nominal current	Plug
1 20801 3	118977	1		without cable		290 mm		13 A	

1.5 mm² cable

1 21805 3	017584	1	25 m	H05VV-F 3G1,5	Plastic	240 mm	Black	13 A	BS 1363
1 20806 3	017591	1	50 m	H05VV-F 3G1,5	Plastic	290 mm	Black	13 A	BS 1363

2.5 mm² cable

1 20811 3	118984	1	20 m	H05VV-F 3G2,5 extra heavy-duty cable	Plastic	240 mm	Black	13 A	BS 1363
1 20812 3	118991	1	40 m	H05VV-F 3G2,5 extra heavy-duty cable	Plastic	290 mm	Black	13 A	BS 1363

Design protected. / Patent pending.



Garant® Cable Reel with RCD plug

Top in quality and design, for every requirement and use.

- Reel body made from special plastic fitted to a galvanised steel tube frame.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Ergonomic cable guide handle for perfect cable-management during winding.
- With thermal cut-out protection against overheating.
- RCD-plug 30 mA provides effective protection against electric shocks.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Reel-Ø	Cable colour	Nominal current	Plug
RCD-plug 30 mA									
1 21875 3	133000	1	25 m	H05VV-F 3G1,5	Plastic	240 mm	Black	13 A	RCD-plug 30 mA

Design protected. / Patent pending.



With Bretec® non-turning socket system. Socket outlet remains stationary while reel body rotates. Prevents the cable of appliances connected from twisting while winding.

Garant® Bretec® Cable Reel

With the unique Bretec® Anti Cable Twist System for comfortable working.

- No more dangerous twisting of connected appliances when winding or unwinding.
- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Innovative and ergonomic cable guide handle „cable pilot“ for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- Rotary handle for comfortable rolling up.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- With thermal cut-out protection against overheating.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 20885 3	054893	1	25 m	H05VV-F 3G1,5	Plastic	Red	240 mm	13 A	BS 1363
1 20886 3	054909	1	50 m	H05VV-F 3G1,5	Plastic	Red	290 mm	13 A	BS 1363

Design protected. / Patent pending.



Garant® G Cable Reel

For mobile working with electrical garden tools.

- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Ergonomic cable guide handle for perfect cable-management during winding.
- With rubber socket 240 V.
- Thermal cut-out protection against overheating.
- E.g. for use when operating lawn mowers, hedgecutters, electric trimmers, trimmers etc, when working at height, or carrying out work across a large area.
- For mobile working of a large radius, reel remains next to the power source connected to.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 14174 3 015	656400	1	25 m	H05VV-F 3G1,5	Plastic	Blue	240 mm	13 A	BS 1363

Design protected. / Patent pending.



Garant® S Cable Reel

Top in quality and design, for every requirement and use.

- Reel body made from rust-resistant and galvanised sheet steel.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Ergonomic cable guide handle for perfect cable-management during winding.
- Thermal cut-out protection, indicator shows overheating.
- With hinged rotary handle for comfortable rolling up.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 19801 3	142026	1		without cable			290 mm	13 A	
1.5 mm² cable									
1 19805 3	133017	1	25 m	H05VV-F 3G1,5	Plastic	Black	240 mm	13 A	BS 1363
1 19806 3	133024	1	50 m	H05VV-F 3G1,5	Plastic	Black	290 mm	13 A	BS 1363
2.5 mm² cable									
1 19811 3	133031	1	20 m	H05VV-F 3G2,5 extra heavy-duty cable	Plastic	Black	240 mm	13 A	BS 1363
1 19809 3	166572	1	40 m	H05VV-F 3G2,5 extra heavy-duty cable	Plastic	Black	290 mm	13 A	BS 1363

Patent pending.



Garant® S Compact Cable Reel

Top in quality and design, for every requirement and use.

- Reel body made from rust-resistant and galvanised sheet steel fitted to a particularly sturdy galvanised steel tube frame.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Ergonomic handle for comfortable carrying.
- With thermal cut-out protection against overheating.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 07293 3	662531	1	15 m	H05VV-F 3G1,5	Plastic	Black	190 mm	13 A	BS 1363

**MADE
IN GERMANY**

Standard AK 260 Cable Reel

- Reel body made of break-resistant plastic.
- Robust, galvanised steel tube frame.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- With thermal cut-out protection against overheating.

Article No.	EAN-Code 4007123...	UP	Packaging	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 09825 3 001	140817	1	Single boxed	25 m	H05VV-F 3G1,5	Plastic	Black	260 mm	13 A	BS 1363
1 09825 3 027	140800	27	Unboxed pallet	25 m	H05VV-F 3G1,5	Plastic	Black	260 mm	13 A	BS 1363
1 09841 3 001	147540	1	Single boxed	50 m	H05VV-F 3G1,5	Plastic	Black	260 mm	13 A	BS 1363

Design protected.

**MADE
IN GERMANY****NEW**

Rubber Cable Reel X-GUM

- Compact and robust lightweight with integrated carrying handle.
- Reel body made of a special rubber mixture for long-term load bearing.
- Unbreakable, impact resistant, aging and weather resistant.
- Resistant to a variety of oils, greases, gasoline and acids, UV and ozone radiation.
- 3 earthed sockets with self-closing covers.
- With thermal cut-out protection against overheating.

Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 16972 3 150	661848	2	15 m	H05VV-F 3G1,5	Plastic	Black	13 A	BS 1363


**MADE
IN GERMANY**

Compact AK 180 Cable Reel

- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- Galvanized steel tube frame.
- Small and handy reel, fits in most tool boxes.
- With thermal cut-out protection against overheating.

Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 07818 3 004	140787	4	15 m	H05VV-F 3G1,5	Plastic	Black	180 mm	13 A	BS 1363

Design protected.



Hanging Workshop Power Distributor

A height-adjustable power distributor with suspension facility.

- Housing made of break-resistant plastic.
- With double-sided, triple socket outlet 13 A BS and a hook for large tools.
- 3 m galvanised steel chain for hanging.
- With thermal cut-out protection against overheating or overload.
- 5 m connecting cable.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Socket
1 15176 3	049325	1	5 m	H05VV-F 3G1,5	Plastic	Black	13 A	2 x 3 BS 1363

Design protected.



Automatic Rewind Cable Reel

Convenient automatic rewind.

- For fitting on walls and ceilings.
- Slewable up to 180°.
- Robust plastic housing.
- With safety cut-out.
- Childproof socket.
- For safe storage of the cable after use.
- Cable quality: - PVC cable or
- rubber-neoprene (RN), robust, oil-resistant and especially suited for professional use.
- In colourful display-packaging.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 24102 3 300	621705	1	9 + 2 m	H05VV-F 3G1,5	Plastic	Black	13 A	BS 1363
1 24100 3 300	621699	1	16 + 2 m	H07RN-F 3G1,5 oil resistant	Rubber-Neoprene	Black	13 A	BS 1363



Safe-Box BIG IP 44

For extra safety when connecting cables, even outdoors, IP 44.

- Extra large Safe-Box for safe connection of plug and socket and to protect from damp.
- Ideal for particularly large plugs and sockets, especially larger export versions.
- Most suitable for use when camping, mowing the lawn, for seasonal or Christmas lighting, or when working with electrical equipment outdoors.
- Recommended as additional protection for small children as well.



Article No.	EAN-Code	UP
	4007123...	
1 16044 0	170784	10



Circuit Breaker Plug BDI-S 30 (RCD)

The ideal safety circuit breaker for connection to frequently used electrical appliances.

- Provides effective protection against electric shocks. Instantly disconnects the live lead from the mains as soon as residual current is present.
- 2-pole cut-out.
- In blister packaging.



Article No.	EAN-Code	UP	Nominal voltage	Nominal current	Residual current	Feature	Plug
	4007123...						
1 29064 3	593828	1	240 V	13 A	30 mA	for cable 3G1.5-cable	BS 1363



Circuit Breaker Adapter BDI-A 30 (RCD)

Transferable adapter, protects users of power tools, domestic appliances, etc. against electrical hazards.

- Provides effective protection against electric shocks. Instantly disconnects the live lead from the mains as soon as residual current is present.
- 2-pole cut-out.
- In blister packaging.



Article No.	EAN-Code	UP	Nominal voltage	Nominal current	Residual current	Plug
	4007123...					
1 29063 3	593804	1	240 V	13 A	30 mA	BS 1363



Vario-Line Cable Box

A compact, handy cable reel for home, office and DIY.

- Housing made of break-resistant plastic.
- Practical carrying handle.
- Twin feet ensure excellent stability.
- Easy to wind and rewind.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- With thermal cut-out protection against overheating or overload.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Colour	Nominal current	Plug
1.5 mm² cable									
1 09820 3	133048	5	5 m	H05VV-F 3G1,5	Plastic	Black	Blue	13 A	BS 1363
1 10856 3	140831	5	10 m	H05VV-F 3G1,5	Plastic	Black	Blue	13 A	BS 1363
1 09320 3	641482	5	10 m	H05VV-F 3G1,5	Plastic	Black	Black	13 A	BS 1363
1 10890 3	140848	5	15 m	H05VV-F 3G1,5	Plastic	Black	Blue	13 A	BS 1363
1 09420 3	641468	5	15 m	H05VV-F 3G1,5	Plastic	Black	Black	13 A	BS 1363



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Colour	Nominal current	Plug
1.0 mm² cable									
1 10855 3	147595	5	10 m	H05VV-F 3G1,0	Plastic	Black	Grey	10 A	BS 1363
1 10820 3	142019	5	20 m	H05VV-F 3G1,0	Plastic	Black	Grey	10 A	BS 1363



Primera-Line Cable Box

A compact, handy cable reel for home, office and DIY.

- Compact design, for comfortable handling.
- Practical carrying handle.
- Variable use, standing or flat.
- Robust, rigid construction.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- With thermal cut-out protection against overheating or overload.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Colour	Nominal current	Plug
1 09545 3	598212	2	10 m	H05VV-F 3G1,5	Plastic	Black	Black/Light Grey	13 A	BS 1363

Design protected.



Comfort-Line Cable Box CL-S

Desk socket for home & office.

- Ergonomic design with a functional and practical rewind ring for easy handling.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- With thermal cut-out protection against overheating or overload.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Colour	Nominal current	Plug
1 10922 3	637195	4	3 m	H05VV-F 3G1,5	Plastic	Black	Black/White	13 A	BS 1363
1 10923 3	641505	4	3 m	H05VV-F 3G1,5	Plastic	Black	Black/Blue	13 A	BS 1363

Design protected.



4-Way Powerblock With Extension Cable

- Extension lead with a 4-socket Powerblock made of impact- and break-resistant plastic.
- With foldable metal hanging hook.
- Sockets in 80° arrangement with self-closing covers.
- With self-closing cover providing protection against dust and contamination.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 16820 3	190720	3	5 m	05VV-F 3G1,25	Plastic	Blue	13 A	BS 1363
1 16821 3	190737	3	14 m	05VV-F 3G1,25	Plastic	Blue	13 A	BS 1363



Extension Cable

- With rubberized socket 13 A BS.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 16650 3 015	657407	5	14 m	H05VV-F 3G1,5	Plastic	Blue	13 A	BS 1363
1 16654 3 015	657414	5	25 m	H05VV-F 3G1,5	Plastic	Blue	13 A	BS 1363
1 16655 3 015	657421	10	2 m	H05VV-F 3G1,5	Plastic	White	13 A	BS 1363
1 16656 3 015	657438	10	3 m	H05VV-F 3G1,5	Plastic	White	13 A	BS 1363
1 16657 3 015	657445	10	5 m	H05VV-F 3G1,5	Plastic	White	13 A	BS 1363



Super-Solid 110 V CEE 2 Cable Reel

- Extra stable, shock-absorbing steel tube frame with galvanised steel tube, exclusive stability.
- Carry handle with comfortable cable guide management during winding.
- Reel body made of special plastic with reinforced ribbed structure.
- With twin socket 110 V/16 A.
- With thermal cut-out protection against overheating or overload.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 30895 3 110	576517	1	50 m	H05VV-F 3G1,5	Plastic	Yellow	290 mm	16 A	110 V

Patent pending.



Garant® 110 V CEE 2 Cable Reel

Top in quality and design, for every requirement and use.

- No more dangerous twisting of connected appliances when winding or unwinding.
- No more plugging in or out when moving the cable reel.
- Avoids unnecessary actions!
- Reel body made from special break-resistant Brefflexx rubber fitted to a galvanised steel tube frame.
- With twin socket 110 V/16 A.
- Ergonomic cable guide handle for perfect cable-management during winding.
- With thermal cut-out protection against overheating or overload.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 14877 3	140909	1	25 m	H05VV-F 3G1,5	Plastic	Yellow	240 mm	16 A	110 V
1 13887 3	140879	1	50 m	H05VV-F 3G1,5	Plastic	Yellow	290 mm	16 A	110 V
1 13195 3	059805	1	25 m	H05VV-F 3G2,5 extra heavy-duty cable	Plastic	Yellow	240 mm	16 A	110 V

Design protected. / Patent pending.



Garant® S 110 V CEE 2 Cable Reel

The robust cable reel made of rust-resistant, hot-dip galvanised steel sheet.

- With twin socket 110 V/16 A.
- Robust, galvanised steel tube frame.
- Ergonomic cable guide handle for perfect cable-management during winding.
- With thermal cut-out protection against overheating or overload.



Article No.	EAN-Code 4007123...	UP	QTY, pallet	Cable length	Cable	Cable colour	Reel-Ø	Nominal current	Plug
1 19807 3	140916	1	45	25 m	H05VV-F 3G1,5	Yellow	240 mm	16 A	110 V

Patent pending.



With Bretec® non-turning socket system. Socket outlet remains stationary while reel body rotates. Prevents the cable of appliances connected from twisting while winding.

Garant® Bretec® 110 V CEE 2 Cable Reel

With the unique Bretec® Anti Cable Twist System for comfortable working.

- No more dangerous twisting of connected appliances when winding or unwinding.
- No more plugging in or out when moving the cable reel.
- Avoids unnecessary actions!
- With twin socket 110 V/16 A.
- Innovative and ergonomic cable guide handle „cable pilot“ for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- With thermal cut-out protection against overheating or overload.

The one has got a Bretec:
the other's got a mess.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 14885 3	140923	1	25 m	H05VV-F 3G1,5	Plastic	Yellow	240 mm	16 A	110 V

Design protected. / Patent pending.



Standard AK 260 110 V CEE 2 Cable Reel

- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Robust, galvanised steel tube frame.
- With twin socket 110 V/16 A.
- Thermal cut-out protection, indicator shows overheating.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Reel-Ø	Nominal current	Plug
1 09874 3	141067	1	25 m	H05VV-F 3G1,5	Plastic	Yellow	260 mm	16 A	110 V
1 09878 3	616046	1	50 m	H05VV-F 3G1,5	Plastic	Yellow	260 mm	16 A	110 V

Design protected.



Rubber Cable Reel X-GUM CEE 110V

- Compact and robust lightweight with integrated carrying handle.
- Reel body made of a special rubber mixture for long-term load bearing.
- Unbreakable, impact resistant, aging and weather resistant.
- Resistant to a variety of oils, greases, gasoline and acids, UV and ozone radiation.
- With thermal cut-out protection against overheating.
- CEE-plug 110 V/16 A, 2x 110 V/16A CEE sockets.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 16974 3 140	661862	2	14 m	H05VV-F 3G1,5	Plastic	Yellow	16 A	110 V



Automatic Rewind Cable Reel 110 V CEE IP 44

Convenient automatic rewind.

- For fitting on walls and ceilings.
- Slewable up to 180°.
- Robust plastic housing.
- With safety cut-out.
- CEE socket 110 V.
- For safe storage of the cable after use.
- Cable quality: Rubber-neoprene (RN), robust, oil-resistant and especially suited for professional use.
- In colourful display-packaging.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 24100 3 110	622580	1	16 + 2 m	H07RN-F 3G1,5 oil resistant	Rubber-Neoprene	Black	16 A	110 V
1 24101 3 110	635740	1	9 + 2 m	H07RN-F 3G1,5 oil resistant	Rubber-Neoprene	Black	16 A	110 V



Splitter Box CEE 4

A robust 4 socket power distributor for multi-purpose use.

- Casing made of break-resistant special plastic, with 2 holes on either side suitable for wall-mounting.
- Slots around the body allow cable to be wound.
- With 4 sockets 110 V/16 A.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Socket	Plug
1 15141 3	014057	3	2 m	Extra heavy-duty cable H05VV-F 3G2,5	Plastic	Yellow	16 A	4 x CEE 110 V	110 V



Extension Cable CEE 110 V



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Cable quality	Cable colour	Nominal current	Plug
1 16646 3	081288	10	14 m	H05VV-F 3G1,5	Plastic	Yellow	16 A	110 V
1 16846 3	109968	8	14 m	Extra heavy-duty cable H05VV-F 3G2,5	Plastic	Yellow	16 A	110 V



Mobile LED Light JARO 110 V

For indoor and outdoor use, IP 65.




- LED light with ultra-bright Everlight SMD LEDs.
- Solid, modern aluminium housing.
- Robust steel tubular frame with protective plastic edges and ergonomically shaped plastic handle.
- Continuously adjustable light which can be locked with one hand by means of a quick-release fastener.
- With safety glass.
- With sturdy cable storing.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.

NEW



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Plug	LEDs	Power	Luminous flux	Efficacy	Colour temperature
1 17125 3 230	656035	1	2 m	H07RN-F 3G1.0	CEE 110 V	28	20 W	1870 lm	94 lm/W	6500 K
1 17125 3 330	656066	1	3 m	H07RN-F 3G1.0	CEE 110 V	42	30 W	2870 lm	94 lm/W	6500 K
1 17125 3 530	656110	1	5 m	H07RN-F 3G1.0	CEE 110 V	75	50 W	4540 lm	90 lm/W	6500 K
1 17125 3 830	656165	1	5 m	H07RN-F 3G1.0	CEE 110 V	112	80 W	7200 lm	91 lm/W	6500 K





Tripod LED Light JARO

For indoor and outdoor use, IP 65.

- LED light with ultra-bright Everlight SMD LEDs.
- Spotlight continuously adjustable and lockable.
- Solid, modern aluminium housing.
- With safety glass.
- Telescopic tripod made of stable tubular powder-coated steel.
- Handy and reliable tube clamping nuts.
- With sturdy cable storing.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.



NEW



Article No.	EAN-Code	UP	Cable length	Cable	Plug	LEDs	Power	Luminous flux	Efficacy	Colour temperature	Telescopic
1 17125 3 338	656233	1	5 m	H07RN-F 3G1.0	CEE 110 V	44	30 W	2870 lm	94 lm/W	6500 K	max. 1.8 m
2 17125 3 438	657704	1	2.5 m	H07RN-F 3G1.0	CEE 110 V	2 x 28	2 x 20 W	2 x 1870 lm	95 lm/W	6500 K	max. 1.6 m



Premium-Line

The Star Among Extension Sockets!



1 Premium Quality

An exceptionally stable and well-designed compact extension socket made of virtually unbreakable plastic. Meets the highest standards for products „Made in Germany“

2 Exclusive Design

Elegant, slim, timeless, high-quality design.


3 Sockets

Earthed sockets with child proof in a 80° arrangement, also suitable for right-angle plugs.

4 Safe to Switch On/Off

Illuminated safety switch, 2-pole on/off.

Innovative Mounting System



For Quick And Easy Attachment

The clever detachable mounting plate attaches quickly and easily on the back of the Premium-Line. Simply detach the strap by pressing lightly on the detent. By turning the plate 180° and snapping it back into the extension socket the mounting holes can be positioned correctly for mounting.

5 Handy and Compact

Cable compartment for safe and tidy storage.

6 Innovative Mounting System

Removable mounting plate for quick and easy attachment.

7 Individual Mounting Options

Additional and handy straps for mounting with Velcro® tape, cable ties, etc. are located on both ends on the back.



8 High Quality Cable

Top-quality, safe cable.

9 2 USB-charging units

Total charging amperage of max. 3100 mA for quick reload.



EXTENSION SOCKETS



EXTENSION SOCKETS
BS WITH SURGE PROTECTION



28



EXTENSION SOCKETS
BS WITH/WITHOUT SAFETY FUSE BUTTON

32



EXTENSION SOCKETS
BS WITH USB

28

31-34

49-51



Premium-Line 30.000 A Extension Socket With Surge Protection And USB-Charger







- Protection for your appliance from malfunctions in the mains, such as surges, indirect lightning strikes or circuit noises, with a maximum sum of leakage current of up to 30.000 A.
- Suppresses visual and acoustic interference in TV sets, video recorders and audio systems.
- Protects sensitive electronics from high frequency interference voltages.
- Light indicating surge voltage is active.
- Illuminated 2-pole safety switch.
- 2 USB-charging units.
- Total charging amperage of max. **3100 mA** for quick reload.
- With replaceable 10 A fuse.
- Three-core arrangement protects phase, neutral and earth leads.




Insurance cover for up to **5 million Euros** for personal injury and material damage within the framework of our product liability insurance.



Article No.	EAN-Code	UP	Cable	Cable length	Socket	Interference filter	Colour	Nominal current	Plug
1 15605 3 534	662913	2	05VV-F 3G1,25	3 m	 4	EMI/RFI	Black/Light Grey	10 A	BS 1363
									
1 15600 3 536	663583	2	05VV-F 3G1,25	3 m	 6	EMI/RFI	Black	10 A	BS 1363
									

High quality overvoltage protectors with practical, well thought-out details.



- 1 Efficient interference filter, reliably suppresses HF interference through the use of special coils and capacitors, prevents video and audio interference.
- 2 Overvoltage protection display, indicates operating status of overvoltage protection.
- 3 High-capacity metal oxide varistors, with low response voltage for swift reactions and reliable discharge of excess energy.
- 4 Protected 230 V mains connections, high quality, 3-pole AC voltage protection by varistors and gas discharge tube, ensuring reliable power supply to your equipment.
- 5 Thermal security system, monitors all varistors for impermissible heating through overload and cuts out in time to prevent danger.
- 6 Earthed sockets with child protection.
- 7 Two-pole mains switch, (230 V/16 A) with integral operating status indicator light.
- 8 High quality mains lead, 3 m long with 3 x 1,25 mm² cross section, replaceable.
- 9 2 USB-charging units.





Premium-Line 30.000 A Extension Socket With Surge Protection



Insurance cover for up to **5 million Euros** for personal injury and material damage within the framework of our product liability insurance.

- Protection for your appliance from malfunctions in the mains, such as surges, indirect lightning strikes or circuit noises, with a maximum sum of leakage current of up to 30.000 A.
- Suppresses visual and acoustic interference in TV sets, video recorders and audio systems.
- Protects sensitive electronics from high frequency interference voltages.
- Light indicating surge voltage is active.
- Illuminated 2-pole safety switch.
- With replaceable 10 A fuse.
- Three-core arrangement protects phase, neutral and earth leads.



Article No.	EAN-Code	UP	Cable	Cable length	Socket	Interference filter	Colour	Nominal current	Plug
1 15605 3 394	110605	2	05VV-F 3G1,25	3 m	4	EMI/RFI	Black/Light Grey	10 A	BS 1363
									
1 25605 3 378	110568	2	05VV-F 3G1,25	3 m	8 DUO	-	Black/Light Grey	10 A	BS 1363
									



hugo! 19.500 A Extension Socket With Surge Protection

Colourful, stylish, cool. With surge protection.




**ENGINEERED
IN GERMANY**

Insurance cover for up to
5 million Euros
for personal injury and
material damage within the
framework of our product
liability insurance.



- Protects expensive devices from overloads with a max. surge current of up to 19.500 A.
- Optical function display for overload protection.
- Shapely and stable enclosure due to polished, highly break-proof polycarbonate.
- Illuminated 2-pole ON/OFF safety switch.
- With widely spaced sockets positioned at a 90° angle.
- Childproof sockets.
- With mounting facilities for wall installation.
- In blister packaging.

Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
8-way, 3 m cable									
1 15061 3 378	620616	1	3 m	05VV-F 3G1,25	57 cm	8	Rubin-red	13 A	BS 1363
									
1 15061 3 328	620647	1	3 m	05VV-F 3G1,25	57 cm	8	White	13 A	BS 1363
									
1 15061 3 318	620678	1	3 m	05VV-F 3G1,25	57 cm	8	Anthracite	13 A	BS 1363
									



Eco-Line 13.500 A Extension Socket With Surge Protection



**ENGINEERED
IN GERMANY**

Insurance cover for up to
5 million Euros
for personal injury and
material damage within the
framework of our product
liability insurance.



- The competitively priced quality socket outlet rail for DIY, home and office.
- Prevents damage or destruction from voltage peaks, and provides effective protection against indirect lightning strikes.
- Suitable for wall fixing. With 2 m cable with BS-plug 13 A.
- Equipped with an illuminated on/off switch and surge neon indicator.
- In blister packaging.
- Light indicating surge voltage is active.

Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15675 3	118106	4	2 m	05VV-F 3G1,25	41 cm	5	Anthracite	13 A	BS 1363



Desktop-Power 13.500 A Surge Protected Socket With USB-Hub 2.0 Splitter with switch and surge protection

Indispensable extension socket on your desk, ideal to connect your laptop, including 4 USB-ports, as splitter (no chargers!)



- Protects expensive devices from overloads with a max. surge current of up to 13.500A.
- Polished surface.
- 4 USB-ports as splitter for e.g. memory stick, Bluetooth etc.
- Childproof sockets in a practical 80° arrangement.
- 1.8 m of connecting cable 13 A/240 V.
- 1.0 m connecting cable with USB-plug.
- With illuminated on/off safety switch.
- In blister packaging.



Insurance cover for up to **5 million Euros** for personal injury and material damage within the framework of our product liability insurance.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	USB-ports	Nominal current	Plug
1 15354 3 134	213931	1	1,8 m	05VV-F 3G1,25	24 cm	4	4	13 A	BS 1363



Primera-Line 13.500 A Surge Protected Adapter



- Efficient surge protection made from gas discharge tube and metal oxide varistors with thermal fuse.
- Protects electrical appliances against surges with a max. up to 13.500 A.
- Protects phase, neutral- and the protective earth.
- Indicator for the protective function.
- Childproof socket.
- Max. load 3120 W/13 A.
- In blister packaging.



Insurance cover for up to **5 million Euros** for personal injury and material damage within the framework of our product liability insurance.



Article No.	EAN-Code	UP	Nominal current	Colour	Plug
1 50695 3	191499	6	13 A	Silver/Black	BS 1363



USB everywhere! Nothing doing without power!

Sockets are becoming available again at last, thanks to integrated USB chargers.

Smartphones, tablets, cameras, power banks and the like are always hungry for power. Most households use a large number of power packs and cables to satisfy that appetite. Frequently, these use up all available sockets, making a free slot a scarce commodity.

Our new **multiple outlet strips with a powerful integrated USB charger** offer the perfect solution.

You can put them on or under your desk or workspace, with or without overvoltage protection - the choice is yours. Our range even includes a version that can be concealed in the desk top.

What connects them all is the high USB charging current output of 5 V with 2100 mA or 3100 mA for extra fast charging.




Premium-Alu-Line FB Extension Socket With Safety Fuse Button And USB-Charger and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Attractive, timeless, sturdy housing made from aluminium with hardwearing, matt-finished surfaces.
- Hole suitable for hanging.
- Wall-mounting holes.
- Innovative and individual fixture system.
- Earthed sockets in a 80° arrangement.
- 2 USB-charging units 2100 mA.
- Excess cable can be wound around the housing.
- Extra robustness.
- Childproof sockets.
- Illuminated 2-pole ON/OFF safety switch.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Socket	Nominal current	Plug
1 39100 3 515	648573	4	3 m 	H05VV-F 3G1,5	5	13 A	BS 1363





Premium-Alu-Line FB Technics Extension Socket With Safety Fuse Button And USB-Charger and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Attractive, timeless, sturdy housing made from aluminium with hardwearing, matt-finished surfaces.
- Hole suitable for hanging.
- Wall-mounting holes.
- Innovative and individual fixture system.
- 2 USB-charging units **3100 mA**.
- Earthed sockets in a 80° arrangement.
- Excess cable can be wound around the housing.
- Extra robustness.
- Childproof sockets.
- Illuminated 2-pole ON/OFF safety switch.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 39100 3 900	663576	2	3 m	H05VV-F 3G1,5	65,5 cm	12 (2 x 6 sockets switched)	Black	13 A	BS 1363








Premium-Line FB Extension Socket With Safety Fuse Button And USB-Charger and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- 2 USB-charging units 2100 mA.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Plug
1 95115 3 600	648542	4	3 m	H05VV-F 3G1,5	60 cm	5	Black	BS 1363



Premium-Office-Line FB Extension Socket With Safety Fuse Button And USB-Charger and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Elegant, ageless desktop design made from extremely durable special synthetic material.
- Comfortable to directly plug-in and switch-on the desk.
- Earthed sockets in a 80° arrangement.
- 2 USB-charging units 2100 mA.
- Illuminated 2-pole ON/OFF safety switch.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Socket	Colour	Plug
1 15625 3 515	648566	4	3 m	H05VV-F 3G1,5	5	Black	BS 1363





Premium-Alu-Line FB Extension Socket With Safety Fuse Button

and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Attractive, timeless, sturdy housing made from aluminium with hardwearing, matt-finished surfaces.
- Hole suitable for hanging.
- Wall-mounting holes.
- Innovative and individual fixture system.
- Earthed sockets in a 80° arrangement.
- Excess cable can be wound around the housing.
- Extra robustness.
- Childproof sockets.
- Illuminated 2-pole ON/OFF safety switch.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Nominal current	Plug
1 39100 3 644	643066	4	3 m	H05VV-F 3G1,5	41 cm	4	13 A	BS 1363
1 39100 3 654	643097	4	5 m	H05VV-F 3G1,5	41 cm	4	13 A	BS 1363
1 39100 3 646	643127	4	3 m	H05VV-F 3G1,5	54 cm	6	13 A	BS 1363



Premium-Alu-Line Extension Socket

For connection of data processing/Video/HiFi equipment and other appliances, e.g. PC, printer, modem, etc. for industrial, trade and private use.

- Attractive, timeless, sturdy housing made from aluminium with hardwearing, matt-finished surfaces.
- Hole suitable for hanging.
- Wall-mounting holes.
- Earthed sockets in a 80° arrangement.
- Excess cable can be wound around the housing.
- Extra robustness.
- Childproof socket.
- Illuminated 2-pole ON/OFF safety switch.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Nominal current	Plug
1 39100 3 014	142071	4	1.8 m	05VV-F 3G1,25	41 cm	4	13 A	BS 1363
1 39100 3 016	142095	4	3 m	05VV-F 3G1,25	54 cm	6	13 A	BS 1363
1 39100 3 018	166596	4	3 m	05VV-F 3G1,25	66 cm	8	13 A	BS 1363



Premium-Line FB Extension Socket With Safety Fuse Button

and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 95114 3 603	643059	4	3 m	H05VV-F 3G1,5	40 cm	4	Black	13 A	BS 1363
1 95154 3 603	643073	4	3 m	H05VV-F 3G1,5	40 cm	4	Black/Light Grey	13 A	BS 1363
1 95114 3 604	643080	4	5 m	H05VV-F 3G1,5	40 cm	4	Black	13 A	BS 1363

























Patent pending.



Premium-Line Extension Socket

- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 95113 3 100	647934	4	3 m	H05VV-F 3G1,5	39,5 cm	3	Black		BS 1363
									
1 95513 3 100	647941	4	3 m	H05VV-F 3G1,5	39,5 cm	3	Grey/Black		BS 1363
									
1 95113 3 101	647958	4	5 m	H05VV-F 3G1,5	39,5 cm	3	Black		BS 1363
									
1 95114 3 100	627004	4	1,8 m	05VV-F 3G1,25	40 cm	4	Black	13 A	BS 1363
									
1 95154 3 100	627141	4	1,8 m	05VV-F 3G1,25	40 cm	4	Black/Grey	13 A	BS 1363
									
1 95554 3 100	627486	4	1,8 m	05VV-F 3G1,25	40 cm	4	Grey	13 A	BS 1363
									
1 95154 3 101	627288	4	3 m	05VV-F 3G1,25	40 cm	4	Black/Grey	13 A	BS 1363
									
1 95154 3 102	628155	4	5 m	05VV-F 3G1,25	40 cm	4	Black/Grey	13 A	BS 1363
									



Premium-Line FB Extension Socket With Safety Fuse Button

and „easy reset function“ in case of overload


Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 95116 3 602	643103	4	3 m	H05VV-F 3G1,5	53 cm	6	Black	13 A	BS 1363
1 95156 3 601	643110	4	3 m	H05VV-F 3G1,5	53 cm	6	Black/Light Grey	13 A	BS 1363
1 95116 3 603	643134	4	5 m	H05VV-F 3G1,5	53 cm	6	Black	13 A	BS 1363
1 95118 3 601	643141	4	3 m	H05VV-F 3G1,5	65 cm	8	Black	13 A	BS 1363

Patent pending.



Premium-Line Extension Socket

- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 95116 3 100	627264	4	3 m	05VV-F 3G1,25	53 cm	6	Black	13 A	BS 1363
1 95156 3 100	627301	4	3 m	05VV-F 3G1,25	53 cm	6	Black/Light Grey	13 A	BS 1363
1 95556 3 100	627509	4	3 m	05VV-F 3G1,25	53 cm	6	Light Grey	13 A	BS 1363
1 95156 3 101	627585	4	5 m	05VV-F 3G1,25	53 cm	6	Black/Light Grey	13 A	BS 1363
1 95118 3 100	627028	4	3 m	05VV-F 3G1,25	65 cm	8	Black	13 A	BS 1363
1 95158 3 100	627325	4	3 m	05VV-F 3G1,25	65 cm	8	Black/Light Grey	13 A	BS 1363
1 95558 3 100	627523	4	3 m	05VV-F 3G1,25	65 cm	8	Light Grey	13 A	BS 1363

Patent pending.



Premium-Line FB Technics Extension Socket With Safety Fuse Button

and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Advanced „fuse button reset function“ eliminates time consuming plug fuse replacement. Simply resettable in case of overload.
- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 95112 3 601	663323	2	3 m	H05VV-F 3G1,5	100 cm	12 (2 x 6 sockets switched)	Black	13 A	BS 1363





Premium-Line Technics Extension Socket

- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
5-way Extension Socket „3 + 2 x 1“									
1 95155 3 600	627165	4	3 m	05VV-F 3G1,25	53 cm	5 (1 x 3 + 2 x 1) sockets switched	Black/Light Grey	13 A	BS 1363



12-way Extension Socket „8 + 4“									
1 95152 3 600	627127	2	3 m	05VV-F 3G1,25	100 cm	12 (1 x 8 + 1 x 4) sockets switched	Black/Light Grey	13 A	BS 1363




Patent pending.



Premium-Line Technics Extension Socket British Standard/German Standard


- Quality extension sockets in top design and modern colour combinations.
- Housing made of break-resistant plastic.
- With 2 holes on either side suitable for wall-mounting.
- Childproof socket.
- Excess cable can be wound around the housing.
- With illuminated 2-pole switch with protection cover.
- Some types with extra widely spaced sockets to accommodate large charging units, etc.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15605 3 024	610761	4	3 m	05VV-F 3G1,25	55 cm	4 x BS + 2 x earthed	Black/Light Grey	13 A	BS 1363









Design protected.



Premium-Line Extension Socket with IEC Plug

- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Elegant, sleek, timeless, high-quality design.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Innovative and individual fixture system.
- Childproof sockets.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Nominal current	Colour
1 95118 3 605	627042	4	2 m	05VV-F 3G1,25	67 cm	8	10 A	Black
				 				
1 95150 3 605	627189	2	2 m	05VV-F 3G1,25	85,5 cm	10	10 A	Black/Light Grey
				 				



Alu-Office-Line Extension Socket


For convenient connection of data processing/Video and audio sets directly with different appliances on the desk.



- Elegant, ageless desktop design made from aluminium with unsusceptible, matt-finished surface.
- Conceived cable routing and easy operation.
- Comfortable to directly plug-in and switch-on the desk.
- Earthed sockets in a 80° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Nominal current	Plug
1 39400 3 416	561698	1	3 m	05VV-F 3G1,25	38 cm	6	13 A	BS 1363



Premium-Office-Line Extension Socket

For convenient connection of data processing/Video and audio sets directly with different appliances on the desk.



- Elegant, ageless desktop design made from extremely durable special synthetic material.
- Comfortable to directly plug-in and switch-on the desk.
- Earthed sockets in a 80° arrangement.
- Illuminated 2-pole ON/OFF safety switch.
- Childproof sockets.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15625 3 416	561681	1	3 m	05VV-F 3G1,25	38 cm	6	Black/Light Grey	13 A	BS 1363





Super-Solid-Line FB Extension Socket With Safety Fuse Button


and „easy reset function“ in case of overload

Extra H/D cable 3G1.5 mm² for high product safety.

- Extremely sturdily constructed extension socket made from highly break-resistant polycarbonate.
- With illuminated 2-pole ON/OFF switch.
- Earthed sockets in a 90° arrangement, for angled plugs as well.
- The distance between the sockets allows the use of large charger units.
- With practical hanging facility.
- With childproof sockets.
- Special feature: cable output is fitted opposite the switch. Therefore, no surplus cable e.g. on the desk.
- Rubber pads prevent extension socket from slipping.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15334 3 625	942977	1	2,5 m	H05VV-F 3G1,5	44,5 cm	5	Black/Light Grey	13 A	BS 1363
1 15334 3 628	642984	1	2,5 m	H05VV-F 3G1,5	63 cm	8	Black/Light Grey	13 A	BS 1363







Super-Solid-Line Extension Socket

- Extremely sturdily constructed extension socket made from highly break-resistant polycarbonate.
- With illuminated 2-pole ON/OFF switch.
- Earthed sockets in a 90° arrangement, for angled plugs as well.
- The distance between the sockets allows the use of large charger units.
- With practical hanging facility.
- With childproof sockets.
- Special feature: cable output is fitted opposite the switch. Therefore, no surplus cable e.g. on the desk.
- Rubber pads prevent extension socket from slipping.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15334 3 215	596102	1	2.5 m	05VV-F 3G1,25	44,5 cm	5	Black/Light Grey	13 A	BS 1363
1 15334 3 218	596119	1	2.5 m	05VV-F 3G1,25	63 cm	8	Black/Light Grey	13 A	BS 1363





hugo! Extension Socket

Colourful, stylish, cool.

- Shapely and stable enclosure due to polished, highly break-proof polycarbonate.
- Illuminated 2-pole ON/OFF safety switch.
- With widely spaced sockets positioned at a 90° angle.
- Childproof sockets.
- With mounting facilities for wall installation.
- In blister packaging.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1150613114	620319	2	2 m	05VV-F 3G1,25	35 cm	4	Anthracite	13 A	BS 1363
1150613174	620265	2	2 m	05VV-F 3G1,25	35 cm	4	Ruby Red	13 A	BS 1363
1150613124	620289	2	2 m	05VV-F 3G1,25	35 cm	4	White	13 A	BS 1363
1150613178	620524	2	3 m	05VV-F 3G1,25	57 cm	8	Ruby Red	13 A	BS 1363
1150613128	620555	2	3 m	05VV-F 3G1,25	57 cm	8	White	13 A	BS 1363



Primera-Line Extension Socket

The design multiple sockets with clever features.

- With cable clip for the storage of surplus cable.
- Option of variable cable output on both sides.
- Sockets arranged at 90° angles.
- Convenient spacing of the sockets.
- With mounting facilities for wall installation.
- Packaging: Shrink-wrapped - for protection against dust and contamination.



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15330 3 128	214396	4	2 m	05VV-F 3G1,25	59,5 cm	8	Black	13 A	BS 1363
1 15339 3 128	214457	4	2 m	05VV-F 3G1,25	59,5 cm	8	Silver	13 A	BS 1363
1 15330 3 120	214358	4	2 m	05VV-F 3G1,25	47 cm	10	Black	13 A	BS 1363
1 15339 3 120	214419	4	2 m	05VV-F 3G1,25	47 cm	10	Silver	13 A	BS 1363

Patent pending.


1 Cable Storage



2 Variable Cable output



3 Variable Cable output





ECOLOR Extension Socket

- Elegant, sleek, timeless, high-quality design.
- Polished surface.
- Illuminated 2-pole ON/OFF safety switch.
- Childproof sockets.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15323 3 000	651405	8	1,5 m	H05VV-F 3G1,5	20 cm	3	Black/Black	13 A	BS 1363
1 15323 3 020	644230	8	1,5 m	H05VV-F 3G1,5	20 cm	3	White/Black	13 A	BS 1363
1 15323 3 070	651412	8	1,5 m	H05VV-F 3G1,5	20 cm	3	Red/Black	13 A	BS 1363
1 15323 3 320	655458	8	3 m	H05VV-F 3G1,5	20 cm	3	White/Black	13 A	BS 1363
1 15323 3 329	657452	8	3 m	H05VV-F 3G1,5	20 cm	3	White/Green	13 A	BS 1363




















ECOLOR FB Extension Socket With Safety Fuse Button and „easy reset function“ in case of overload
Extra H/D cable 3G1.5 mm² for high product safety.

- Elegant, sleek, timeless, high-quality design.
- Polished surface.
- Illuminated 2-pole ON/OFF safety switch.
- Childproof sockets.















Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15325 3 000	651399	8	1,5 m	H05VV-F 3G1,5	29 cm	5	Black/Black	13 A	BS 1363
				 					
1 15325 3 020	644261	8	1,5 m	H05VV-F 3G1,5	29 cm	5	White/Black	13 A	BS 1363
				 					
1 15325 3 070	651429	8	1,5 m	H05VV-F 3G1,5	29 cm	5	Red/Black	13 A	BS 1363
				 					
1 15325 3 320	655465	8	3 m	H05VV-F 3G1,5	29 cm	5	White/Black	13 A	BS 1363
				 					
1 15325 3 329	657469	8	3 m	H05VV-F 3G1,5	29 cm	5	White/Green	13 A	BS 1363
				 					

ECOLOR FB Extension Socket With Safety Fuse Button + USB charger and „easy reset function“ in case of overload
Extra H/D cable 3G1.5 mm² for high product safety.

- Elegant, sleek, timeless, high-quality design.
- Polished surface.
- Illuminated 2-pole ON/OFF safety switch.
- Childproof sockets.
- **2 USB-charging units 2100 mA.**



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15324 3 006	654918	4	3 m	H05VV-F 3G1,5	29 cm	4	Black/Black	13 A	BS 1363
				  					
1 15324 3 026	644261	4	3 m	H05VV-F 3G1,5	29 cm	4	White/Black	13 A	BS 1363
				  					
1 15324 3 029	651429	4	3 m	H05VV-F 3G1,5	29 cm	4	White/Green	13 A	BS 1363
				  					



ALEA-Power USB-Charger socket block

High-gloss design, cube-shaped desk power outlet with USB charging function and stand adapter to attach on or under the table.

- Shapely and stable enclosure due to polished, highly break-proof polycarbonate.
- Two-colour design.
- 2 USB-charging units 2100 mA.
- With LED operating indicator.
- With stand adapter and fixing material.
- Childproof sockets.
- In colourful display-packaging.



NEW



Article No.	EAN-Code	UP	Cable length	Cable	Socket	Colour	USB-Charging units
1150103	648276	1	3 m	H05VV-F 3G1,5	3	White/Light Grey	2



Eco-Line Comfort Switch Extension Socket

Multi-way extension socket with comfortable, external hand/foot switch.

- For easy and comfortable on/off switching of all electrical appliances connected by the external foot-operated switch, while the socket outlet remains invisible under the desk or behind the cupboard.
- Robust foot switch with control light.
- Safe and energy efficient through 2-pole disconnection.
- 1.5 m flexible control cable to the external foot switch.
- 2 m loadable mains cable.
- Max. load of 13 A/3120 W.
- Childproof sockets in a practical 90° arrangement.
- In colourful display-packaging.

**ENGINEERED
IN GERMANY**



Article No.	EAN-Code	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15945 3 616	621446	2	2 m	05VV-F 3G1,25	39 cm	6	Anthracite	13 A	BS 1363



Tower Power Pop-Up Extension Socket With USB-Charger

Retractable desk outlet for permanent installation. Installs flush with the desktop. Suitable for office, kitchen, workshop, etc.

- Innovative desk outlet for flexible workspace design.
- Retracts completely into the desktop.
- Stylish and robust aluminium housing.
- 2 USB-charging units 2100 mA.
- Slim design.
- Quick and easy to install, 60 mm bore diameter.
- Power indicator.
- Earthed sockets in a 90° arrangement.
- Childproof sockets.
- In blister packaging.



Article No.	EAN-Code	UP	Cable length	Cable	Socket	Colour	Plug
1 39620 3 013	645381	1	2 m	H05VV-F 3G1,5	3	Alu/Black	BS 1363



Tower Power Pop-Up Extension Socket

Retractable desk outlet for permanent installation. Installs flush with the desktop. Suitable for office, kitchen, workshop, etc.

- Innovative desk outlet for flexible workspace design.
- Retracts completely into the desktop.
- Stylish and robust aluminium housing.
- Slim design.
- Quick and easy to install, 60 mm bore diameter.
- Power indicator.
- Earthed sockets in a 90° arrangement.
- Childproof sockets.
- In blister packaging.







Article No.	EAN-Code	UP	Cable length	Cable	Socket	Colour	Plug
1 39620 3 003	637461	1	2 m	H05VV-F 3G1,5	3	Alu/Black	BS 1363



Eco-Line Extension Socket

- The competitively priced quality socket outlet rail for DIY, home and office.
- With illuminated 2-pole switch with protection cover.
- 2 holes suitable for wall-mounting.
- Made of highly impact-resistant special plastic in attractive design.
- With illuminated on/off safety switch.





Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
4-way, 1.5 m cable · With tab for hanging									
1 15040 3	059683	8	1.5 m	05VV-F 3G1,25	33 cm	4	Black	13 A	BS 1363
									
1 15042 3	212200	8	1.5 m	05VV-F 3G1,25	33 cm	4	White	13 A	BS 1363
									
6-way, 1.5 m cable · With tab for hanging									
1 15950 3	059706	8	1.5 m	05VV-F 3G1,25	43 cm	6	Black	13 A	BS 1363
									
1 15952 3	212217	8	1.5 m	05VV-F 3G1,25	43 cm	6	White	13 A	BS 1363
									

Design protected.



4-Way Extension Socket With Neon Indicator



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Length approx.	Socket	Colour	Nominal current	Plug
1 15062 3 444	173396	20	2 m	05VV-F 3G1,25	27 cm	4	White	13 A	BS 1363
									
1 15062 3 454	173402	20	5 m	05VV-F 3G1,25	27 cm	4	White	13 A	BS 1363
									





BS · PLUG-IN APPLIANCES



REMOTE CONTROL SETS

54



WEEKLY TIMER

55



WATTAGE & CURRENT METER

56



ADAPTER

57



LED NIGHTLIGHT

57



TRAVEL ADAPTER

59



CABLE ORGANISATION


62



Primera-Line Remote Control Set 1 + 3 RC 3600

Control up to 3 devices comfortably and securely via remote control.

- Control appliances connected from your arm-chair and save power!
- Easy to use 4 channel hand transmitter to switch all channels.
- Remote control and receiver socket, any combination.
- Sockets can be operated manually.
- Self learning coding, automatic storage.
- Switching capacity max. 3120 W, 50/60 Hz.
- Range up to 25 Meters (Frequency 433.92 MHz).
- 12 V battery (type A23) for remote control included.
- Childproof socket.
- In blister packaging.



Article No.	EAN-Code	UP	Battery type	Scope of delivery	Description	Plug
1 50747 3	192076	6	1 x A23	1 x 4 channel hand held transmitter, 3 x radio controlled receiver RCR 3600, max. 3120 W	Primera-Line Remote Control Set RC 3600, 220 - 250 V~, 50/60 Hz	BS 1363






Comfort-Line Remote Control Set RC CE1 3001 with Selflearning Coding

For comfortably switching electrical devices and lamps up to 1000 W ON and OFF; for use indoors.

- 3 outlet adapter with wireless receiver for indoors IP 20.
- Switch position indicator on the receiver; can also be operated manually.
- Simple and flexible use by means of self-teaching coding.
- Fail-safe due to more than 65,000 different codes.
- Continuous storage of the coding even in the event of a longer power failure.
- 4-channel manual transmitter for simultaneous universal operation of individual or multiple receivers.
- Switching capacity 1.000 W.
- Range up to 25 Meters (Frequency 433.92 MHz).
- 3 V battery (type CR2032) for remote control included.
- Childproof sockets.
- In blister packaging.



NEW



Article No.	EAN-Code	UP	Battery type	Scope of delivery	Plug
1 50704 3	651658	1	1 x CR2032	1 x 4 channel sender, 3 x remote receivers sockets IP 20	BS 1363



Primera-Line Digital Weekly Timer DT

- Extra large display for days, hours in 12 and 24 hour-format, minutes and seconds.
- 20 ON/OFF programmes for day, hour and minute setting.
- Easy 4 button operation.
- Shortest switching-time 1 minute.
- Countdown function.
- Random function.
- Summer/Winter time.
- Manual ON/OFF.
- Programme: Interruption during operation is possible.
- Data memory in case of power cut.
- Practical housing when using switch and socket combination the switch will not be covered.
- Inclusive 2 batteries AG13 (LR44).
- Childproof socket.
- In blister packaging.

**ENGINEERED
IN GERMANY**



Article No.	EAN-Code	UP	Further information	Plug
1 50750 3	192137	6	Max. load 13 A/3120 W, 220 - 250 V~, 50/60 Hz	BS 1363



24 hour Timer MZ 20-1

The competitively priced timer with 24-hour programme.

- Up to 96 on/off switching times per day can be set.
- Shortest switching time: 15 minutes.
- Easy to set.
- Childproof socket.
- In blister packaging.



Article No.	EAN-Code	UP	Further information	Plug
1 50645 3	150007	6	Max. load 13 A/3120 W, 220 - 250 V~, 50/60 Hz	BS 1363



Primera-Line Wattage & Current Meter PM 231 E

Helps to save costs and energy.

- Measuring of voltage, frequency, current, efficiency, factor and power output.
- Calculation of the entire energy consumption and energy costs.
- Measuring time in hours and minutes.
- 2 individually adjustable current rates (day + night).
- Inclusive 3 LR44 batteries for data storage in case of a power failure.
- Childproof socket.



Article No.	EAN-Code	UP	Further information	Plug
1 50660 3	598076	1	Max. load 3120 W, 13 A, 220 - 250 V, 50/60 Hz	BS 1363



3-Way Adapter for Standard Sockets



- Plug with 3 BS sockets.
- In blister packaging.




Article No.	EAN-Code	UP	Colour	Plug
1 50826 3	645855	5	White	BS 1363

LED Nightlight Color NL 09 RCD with twilight sensor



- LED Nightlight with twilight sensor.
- Three colours: green, blue and white, 3 LEDs each.
- Colours to be chosen by rotary switch.
- Socket with childproof can still be used.
- Exceptionally low electricity consumption, approx. 0.8 W.
- In blister packaging.



Article No.	EAN-Code	UP	Luminous flux	Colour temperature	Measurements	Further information	Plug
1 17326 3	637652	6	10 lm	10000 K	82 x 82 x 76 mm	LEDs switchable: 3 x blue, 3 x green, 3 x white	BS 1363



LED Nightlight OL 02E with twilight sensor

- Nightlight with twilight sensor and 2 LEDs for years of continuous operation.
- Exceptionally low electricity consumption.
- Switches on automatically at dusk.
- Provides safety in dark rooms.
- Soft lighting.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Further information	Plug
1 17322 3	610495	4	2	220 - 250 V~, 50/60 Hz	BS 1363



Battery LED Nightlight NLB 02 BS with PIR sensor and push switch


- Battery LED nightlight with 2 LEDs.
- PIR sensor with 100° horizontal detection angle and max. 3 m range.
- Soft lighting.
- Push switch On/Off.
- Independent from the socket.
- 2 magnets and hooks.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Light duration	Battery type	Colour	Measurements
1 17329 0	637683	6	2 SMD	60 lm	20 h	3 x AA (included)	White	Ø = 84 mm; H = 61 mm



**ENGINEERED
IN GERMANY**



Travel Adapter GB/Earthed


Adapter enabling electrical equipment using the British plug system to be used in countries using an earthed socket system, e.g. DE, FR, BE, PL, NL, ES, PT, SE, FI, NO, GR, TR, AT ...

- This travel adapter is not a transformer or a frequency converter.
- Childproof socket.
- In blister packaging.

Article No.	EAN-Code	UP	Max. load
1 50853 0	4007123...	5	13 A/250 V



**ENGINEERED
IN GERMANY**



Travel Adapter Earthed/GB

Adapter enabling electrical equipment using an earthed socket system to be used in countries with the British plug system.

- This travel adapter is not a transformer or a frequency converter.
- Childproof socket.
- With 13 A fuse.
- In blister packaging.

Article No.	EAN-Code	UP	Max. load
1 50853 3	4007123...	5	13 A/250 V



Travel Adapter USA/Euro

Adapter enabling electrical equipment using the 2-pin plug system in the USA to be used in countries using the Euro plug system. For all European countries except Great Britain.

- This travel adapter is not a transformer or a frequency converter.
- With 2,5 A fuse.
- In blister packaging.

Article No.	EAN-Code	UP	Max. load
1 50850 0 010	645848	5	2,5 A/250 V




Travel Adapter USA, Japan/Earthed

Adapter enabling electrical equipment using the USA and Japanese earthed plug system to be used in countries using an earthed socket system, e.g. DE, FR, BE, PL, NL, ES, PT, SE, FI, NO, GR, TR, AT ...

- This travel adapter is not a transformer or a frequency converter.
- In blister packaging.

Article No.	EAN-Code	UP	Max. load
1 50852 0	170722	5	15 A/250 V



Travel Adapter Earthed/USA, Japan

Adapter enabling electrical equipment using earthed plug system in countries like the USA or Japanese which use an earthed socket system.

- This travel adapter is not a transformer or a frequency converter.
- Childproof socket.
- In blister packaging.



Article No.	EAN-Code	UP	Max. load
1 50855 0	561452	5	15 A/125 V



Travel Adapter Earthed/South Africa, India

Adapter enabling electrical equipment using the earthed plug system to be used in countries with South African or India socket system.

- This travel adapter is not a transformer or a frequency converter.
- Childproof socket.
- In blister packaging.




Article No.	EAN-Code	UP	Max. load
1 50846 0	566334	5	16 A/250 V



Hook And Loop Fastener

For interior and exterior use.

- Hook and loop strips.
- Perfect to fix cable bundles.
- Reusable as often as required.
- Soft and flexible material.
- In blister packaging.



20
stk/pcs

Article No.	EAN-Code	UP	Contents	Colour	Measurements
	4007123...				
1 16434 0	562367	1	20	Black	B = 12 mm x L = 125 mm
1 16432 0	562343	1	20	Black	B = 12 mm x L = 200 mm



Cable Protector


- Stable, tread-resistant PVC conduit.
- Bottom section has 3 chambers.
- 2 well-spaced holes for mounting the conduit.
- Extendable.
- In poly bag with tab for hanging.

Article No.	EAN-Code	UP	Colour	Measurements
	4007123...			
1 16055 0	172849	5	Grey	100 x 5 x 1,2 cm
1 16065 0	172832	5	Grey	100 x 7,5 x 1,7 cm




Spiral Coiled Tube

- Perfect solution to bundle and protect cables and lines in special surroundings as well as in offices or at home.
- Practical winding tool for quick and easy handling included.
- In blister packaging.



Article No.	EAN-Code	UP	Colour	Measurements
1 16436 0	562381	1	Grey	L = 2,5 m, Ø = 20 mm



Site Bulb Fitting E27

- Ready wired with a 2-pin luster terminal.
- With a fastening plate with 3 holes.
- Connecting cable 15 cm.
- For bulbs with E27 fitting.

Article No.	EAN-Code	UP	Number of poles
1 17990 0	188963	10	2





LIGHTING



LED-/HEAD-TORCHES

66



RECHARGEABLE LAMPS AND LAMPS

70




INSPECTION LAMPS

76



LED SITE LIGHTING AND TRIPODS

77



WALL-MOUNTED LIGHTING

81



PIR MOVEMENT DETECTORS

94



SOLAR LED LAMPS

95



LuxPremium Focus-LED-Flashlight TL 250F IP 44

Highest luminosity in the smallest space.

- With extra bright CREE-LED for powerful light.
- Infinitely focus from laminary light nearby to high beam focused light.
- Switch with soft-touch function for 100 % - 30 % - SOS.
- Durable aluminum housing with wrist strap.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17860 0 161	633586	1	CREE	250 lm	160 m	4 h	3 x AAA (included)	L = 13 cm; Ø = 33 mm



LuxPremium Focus-LED-Flashlight TL 100F IP 54

Very handy Penlight with high luminosity.

- With extra bright CREE-LED for powerful light.
- Infinitely variable focus.
- Dust protected and splash-proof, IP 54.
- Durable aluminum housing with clip.
- Versatile and pocket-sized.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17860 0 051	633579	10	CREE-LED	100 lm	60 m	5 h	2 x AAA (included)	L = 14,6 cm; Ø = 16 mm



Eco-LED Laser Light

Laser pointer with LED torch.

- 8 powerful LEDs.
- Handy metal housing.
- With integrated, powerful laser pointer class 2: P< = 1 mW, l = 650 nm (DIN 60825-1:2008-05).
- Soft-touch switch with 2 functions:
 1. LEDs on
 2. Laser pointer on.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements	Further information
1 17989 0 100	633807	4	8	45 lm	Laser 50 m	12 h	3 x AAA (included)	L = 11 cm, Ø = 28 mm	Laser category 2




LuxPrimera Focus 150 LED Flashlight IP 54

Extreme bright LED flashlight with new focus technology.

Continuous adjustable from a constant close light to a zooming distance light.

- With new extra bright CREE high performance LED.
- Problem-free adjustable by one-hand operation.
- Very long range.
- 2 different settings and flashing function.
- Elegant, robust aluminium housing with wrist strap.
- ON/OFF switch with soft-touch-function in „American Style“ at the end.
- Dust protected and splash-proof, IP 54.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17875 0	600021	1	CREE-LED	150 lm	120 m	3,5 h	3 x AAA (included)	L = 11 cm, Ø = 30 mm



LuxPrimera Focus 100 LED Flashlight IP 54

Extreme bright LED flashlight with new focus technology.
Continuous adjustable from a constant close light to a zooming distance light.

- With high-performance CREE Power LED.
- Problem-free adjustable by one-hand operation.
- High range.
- 2 different settings and flashing function.
- Elegant, robust aluminium housing with wrist strap.
- ON/OFF switch with soft-touch-function in „American Style“ at the end.
- Dust protected and splash-proof, IP 54.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17874 0	600014	1	CREE-LED	70 lm	50 m	3,5 h	1 x AA (included)	L = 9,7 cm, Ø = 25 mm



LuxPremium rechargeable LED Headlight KL 250AF IP 44

Versatile with very long lighting duration.

- With extremely bright CREE LED at front with up to 30 h lighting duration.
- Switch with 100 % - 50 % - 10 % - SOS, rear light red/red flash functions.
- Infinitely focus from laminary light nearby to high beam focused light.
- Battery pack at the rear head for good balance
- Exchangeable lithium-ion battery 3.7 V/2.6 Ah with charging indicator.
- Focus angle can be adjusted.
- USB charging cable included.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17730 0	656769	1	CREE	250 lm	100 m	30 h	Lithium-ions	10,5 x 8,5 x 7 cm



LuxPremium LED-Headlight KL 200F IP 44

Ultra lightweight for more comfort.

- With extra bright CREE-LED for powerful light.
- Infinitely focus from laminary light nearby to high beam focused light.
- Front and rear lights.
- Back of head battery pack for balanced and comfortable wearing.
- Switch with 4 different settings (40 %, 100 %, 100 % and red-blinking light at back, SOS).
- Focus angle can be adjusted.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17878 0	636761	1	CREE	200 lm	100 m	16 h	3 x AA (included)	11 x 11 x 10 cm



LuxPremium LED-Headlight KL 100 IP 44

Ultra lightweight for more comfort.

- With extra bright CREE-LED for powerful light.
- Ideal for any application (work, sports, leisure) leaving both hands free.
- Switch with 3 different settings (100 %, 20 %, SOS).
- Focus angle can be adjusted.
- Back of head battery pack for balanced and comfortable wearing.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Headlight range	Light duration	Battery type	Measurements
1 17876 0	636723	10	CREE-LED	100 lm	40 m	35 h	2 x AA (included)	6 x 2,7 x 3,4 cm



Mobile Rechargeable Battery LED Lamp Flexible ML CA 130 F IP 54

For indoor and outdoor use, IP 54.

Flexible use 30 W rechargeable lamp with integrated magnet.

- Bright light, all the time, even in areas without an electrical connection.
- Replaceable high-quality lithium-ion battery, charging time approx. 4.5 hrs.
- Equipped with integrated overcharge and total discharge protection and battery charging indicator.
- 2 regulating notches: 100 % and 50 % light (safe energy).
- Powerbank function: USB charging port 2 A for devices with USB charging cables such as smart phones, MP3 players, tablets, etc.
- High power adapter (100 - 240V AC, 50/60 Hz, output 2 A) for a shorter charging time and 12 V car adapter cable included.
- Casing made of high-quality plastic.
- Stable, multi-stage, folding frame. The lamp can be standing, hung up, or mounted on metal surfaces with four strong, integrated magnets.
- Emitter can also be swivelled in the frame.
- With ON/OFF switch.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	Power	Luminous flux	Light duration	Lamp efficacy	Rechargeable battery	Colour temperature	Energy efficiency class
1 17143 3	635764	1	30 W	2600 lm	3 h	87 lm/W	7,4 V / 10400 mAh	6500 K	A+

Recommended accessories:

Article No.	EAN-Code	UP	Description	Voltage	Capacity
1 17143 0 050	635825	1	Spare Li-Ion battery	7,4 V	10400 mAh



10 + 1 LED Rechargeable Mini Lamp HL 0400 A

Extremely small and handy, high light output.

- 10 super-bright Osram SMD LEDs on the front provide up to 6 hours of light ON time.
- Additional switching step for 1 SMD LED in the lamp head.
- On/off switch for front light (100 %, 50 %) and spotlight.
- Charging time about 4 hours.
- Rubber-clad housing.
- Integrated magnet on the rear.
- Integrated Li-Ion battery 3.6 V/2.6 Ah with charging indicator.
- USB charging interface, including USB charging cable.
- In blister packaging.

Osram LED inside



Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	Measurements
1 17159 0	654093	1	10 + 1	max. 400 + 80 lm	5700 K	max. 6 + 8 h	26 x 3 x 2 cm



Rechargeable LED Hand Lamp SANSA 400 A

Extremely slim lamp for tight spaces.

- 12 super-bright SMD LEDs at front.
- Additional switching step for 1 SMD LED in the lamp head.
- Continuous dimming function 0 to 100% for particularly long lighting duration.
- Charging period approx. 3 hours.
- Rubber-clad housing.
- Bendable and rotatable lamp head, foldable to pocket format.
- 2 magnets at the back, one in the holding foot and fold-out hook for flexible use.
- Integrated Li-Ion battery 3.7 V/2.0 Ah with charging indicator.
- USB charging interface, including USB charging cable.
- Packaged in a window carton.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	Measurements
1 17737 0	657711	1	12 SMD + 1 SMD	400 + 70	6000 K	80 h	30 x 4,4 x 3,4 cm



6 + 1 LED Rechargeable Multi-Function Light HL2 DA 61 M3H2

Multi-purpose, robust with excellent lighting capacity.

- 6 super-bright SMD LEDs on the front with more than 3 hours of lighting if the battery is fully charged.
- Additional switching stage for a SMD-LED light in the head.
- Charging time about 4 hours.
- Rubber-clad housing.
- Base foot can be folded up to 200° with an integrated magnet.
- 2 magnets on the back and two hooks that can be rotated 360° for flexible use.
- Integrated Li-Ion rechargeable battery 3.7 V/2.2 Ah with charging indicator.
- With ON/OFF switch.
- USB charging cable included.
- Packaged in a clear box with a 6" display.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	Measurements
1 17567 0	641642	6	6 SMD + 1 SMD	Front: 300 lm / Spot: 100 lm	6500 K	3 h / 10 h	67 x 50 x 273 mm



Rechargeable LED Spot IP 54

Rechargeable work lamp for use indoors and outdoors, IP 54.

- Bright light, all the time, even in areas without an electrical connection.
- Splashproof.
- Equipped with integrated overcharge and total discharge protection and battery charging indicator.
- With ON/OFF switch.
- 2 regulating notches: 100 % and 50 % light (safe energy).
- Powerbank function: USB charging port for devices with USB charging cables such as smart phones, MP3 players, GPS, etc.
- Charging via micro USB connection, USB cable included.
- Casing made of die-cast aluminum, edge protection made of high-quality plastic.
- Impact-resistant and drop-proof up to 2 m.
- Stable, multi-stage, folding frame.
- With a robust matching bag for safe transport.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	Power	Luminous flux	Light duration	Rechargeable battery	Micro USB Connection	Colour temperature
1 17308 0	646869	1	10 W	max. 1000 lm	3 h (100 %) / 6 h (50 %)	Li-Ion 3,7 V / 4400 mAh	5V, 1A	6500 K
1 17287 0	652822	1	20 W	max. 2000 lm	3 h (100 %) / 6 h (50 %)	Li-Ion 7,4 V / 4400 mAh	5V, 2A	6500 K



Magnetic holder

for Rechargeable LED Spot IP 54.

- Suitable for: 1172870, 1173080

Article No.	EAN-Code	UP	Colour
1 17264 0 002	653201	1	black



4 + 1 LED Rechargeable Clip-on Lamp HL DA 41 MC

Very easy to handle, robust with excellent lighting capacity.

- 4 super-bright Seoul SMD LEDs on the front with more than 3.5 hours of lighting when fully charged.
- Additional switching step for 1 CREE LED in the lamp head.
- Charging period approx. 3 hours.
- Clip with integrated magnet can be rotated 90°.
- Rubber-coated, ergonomic handle and carrying strap.
- Integrated Li-Ion rechargeable battery 3.7 V/1.6 Ah with charging indicator.
- With ON/OFF switch.
- USB charging cable included.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	USB-charging units	Measurements
1 17589 0	645831	1	Front: 4 Seoul SMD, Top: 1 CREE	200 + 150 lm	6500 K	3,5 h / 3,5 h	1	2 x 3 x 17 cm



4 LED Rechargeable Hand Lamp HL DA 40 MH

Small, handy with excellent light.

- 4 super-bright SMD-LEDs on the front with up to 3 hours of lighting when fully charged.
- ON/OFF switch 100/50 %.
- Rubber-clad housing.
- Base foot with integrated magnet can be folded up to 180°.
- Belt clip and 360° rotatable hook for flexible use.
- Integrated LiFePo4 Akku 3.7 V/1.8 Ah.
- USB charging cable included.
- In blister packaging.




Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	Measurements
1 17644 0	648238	1	4 SMD	200 / 100 lm	6500 K	3 h	20 x 60 x 122 mm



Rechargeable LED Outdoor Light OLI 0300 A

Compact, multifunctional and high-quality.

- Highly versatile for use in the house, in the garden, when camping and for outdoor activities.
- Very bright non-blinding light with additional spot, can be combined or used individually.
- All lighting functions can be smoothly dimmed from 100 to 5%.
- Additional SOS and flashing function.
- Integrated Li-Pol rechargeable battery 3.7 V/3.0 Ah with charging indicator and integrated USB charging cable.
- Powerbank function: USB charging port for devices with USB charging cables such as smart phones, MP3 players, GPS, etc.
- Mounting options provided by 2 magnets and 2 hooks.
- Packaged in a clear box.



NEW



Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	Measurements
1 17154 0	653973	9	12 LED + 1 CREE	max. 350 lm	4000 K	70 h	76 x 74 x 69 mm



LED Outdoor Light OLI 0200

Small, variable and high-quality.

- Highly versatile for use in the house, in the garden, when camping and for outdoor activities.
- Non-blinding flood light.
- Switch with 3 different settings (100 - 50 %, 10 %, SOS).
- Mounting options provided by 2 magnets and 2 hooks.
- 9 pcs. delivered in an attractive sales box.

NEW



Article No.	EAN-Code	UP	LEDs	Luminous flux	Battery type	Colour temperature	Light duration	Measurements
1 17155 0	653980	9	12 LED	max. 180 lm	3 x AAA	4000 K	4 / 8 / 45 h	68,5 x 50,5 x 50,5 mm



SMD LED-Universal Lamp HL DB 81 M1H1

Compact, practical for a variety of uses.

- 8 super bright SMD LEDs with special lens optics.
- More than 4 hours of light when fully charged.
- Additional switching step for 1 SMD LED in the lamp head.
- Plastic bracket with integrated magnet can be folded 200°.
- 360° hanging hook and magnet facility.
- With ON/OFF switch.
- In blister packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Battery type	Colour temperature	Light duration	Measurements
1 17541 0 010	641611	1	8 + 1 SMD	250 + 100 lm	3 x AA	6500 K	4 h / 10 h	5,5 x 4,7 x 21,5 cm



4 + 3 SMD LED-Universal Lamp HL DB43 MH

Bright light in pocket size, for multi-purpose.

- 4 super-bright SMD LEDs on the front with more than 6 hours of lighting if the batteries are full.
- Additional switching step for 3 LEDs in the lamp head.
- Plastic handle with integrated magnet, 360° bendable.
- 360° swivelled, retractable hanging hook.
- With ON/OFF switch.
- Packaged in a clear box with a 10" display.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Battery type	Colour temperature	Light duration	Measurements
1 17542 0 010	641628	10	4 SMD + 3 CREE	200 + 20 lm	3 x AAA	6500 K	6 h / 24 h	6,3 x 3,6 x 9,8 cm



Rubber Handlamp

- A robust and handy inspection lamp.
- Handle made of high quality hard rubber for comfort when in constant use.
- Glass bulb protector and wire basket.
- 240 V.

Article No.	EAN-Code	UP	Cable length	Cable	Power	Fittings	Plug
1 17678 3	021987	10	5 m	H05VV-F 2x0,75	60 W	E27	BS 1363



Safety Inspection Lamp

- Competitively priced.
- With impact-resistant, flexible basket.
- Glass bulb protector.
- 240 V.

Article No.	EAN-Code	UP	Cable length	Cable	Power	Fittings	Plug
1 17601 3	021970	10	5 m	H05VV-F 2x0,75	60 W	E27	BS 1363



Professional Building Telescopic Tripod BS 250

For fixing power-jet lights and halogen lamps up to 1000 W and Chip-LED lamps.

- Hinged, extremely stable feet made from square steel section, with ground mounting plates.
- Heavy-duty, stable and robust design.
- Sturdy stand tubes, made from robust steel section, zinc-plated, continuous height adjustment up to a max. 2.5 m.
- Solid attachment with anchor screws, alternatively with included handles.
- In colourful display-packaging.



Article No.	EAN-Code	UP	Height-adjustable	Loading capacity
1 17061 0	190614	1	100 - 250 cm	10 kg



Professional Site Tripod Brobusta® ST 300

Comes with diagonal bar, suitable to carry 2 halogens up to 500 W, halogen spots up to 1000 W and Chip-LED lamps.

- Extra stable and robust tripod.
- Tube made of light steel, galvanized and powder-coated.
- Extra long feet (95 cm) guarantees high stability.
- Adjustable at any height.
- Continuous height adjustment up to a max. of 3 m.
- Handy, reliable locking screws.



Article No.	EAN-Code	UP	Height-adjustable	Loading capacity	Colour
1 17031 0	090433	1	115 - 300 cm	10 kg	Yellow



Mobile LED Light JARO


For indoor and outdoor use, IP 65.

- LED light with ultra-bright Everlight SMD LEDs.
- Solid, modern aluminium housing.
- Robust steel tubular frame with protective plastic edges and ergonomically shaped plastic handle.
- Continuously adjustable light which can be locked with one hand by means of a quick-release fastener.
- With safety glass.
- With sturdy cable storing.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.

NEW



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Plug	LEDs	Power	Luminous flux	Efficacy	Colour temperature
1 17125 3 233	656028	1	2 m	H07RN-F 3G1.0	BS 1363	28	20 W	1870 lm	95 lm/W	6500 K
1 17125 3 343	656059	1	3 m	H07RN-F 3G1.0	BS 1363	44	30 W	2930 lm	95 lm/W	6500 K
1 17125 3 533	656103	1	5 m	H07RN-F 3G1.0	BS 1363	75	50 W	4770 lm	98 lm/W	6500 K
1 17125 3 833	656158	1	5 m	H07RN-F 3G1.0	BS 1363	120	80 W	7200 lm	91 lm/W	6500 K





Mobile Rechargeable LED Light JARO

For indoor and outdoor use, IP 54.



- Bright light, all the time, even in areas without an electrical connection.
- Integrated lithium-ion battery.
- Equipped with integrated overcharge and total discharge protection and battery charging indicator.
- 3 switching stages: 100 %, 50 % and 10 % light (for extended lighting duration).
- Includes power supply 100-240VAC, 50/60Hz.
- Solid and modern aluminium casing.
- Steplessly pivotable light which can be locked with one hand by means of a quick-release fastener.
- Stable steel tube frame with plastic corner protectors.
- With safety glass.
- With adapter earthed/BS.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



NEW



Article No.	EAN-Code 4007123...	UP	LEDs	Power	Luminous flux	Rechargeable battery	Light duration	Colour temperature
1 17125 3 235	656493	1	40	20 W	2000 lm	7,4 V / 4,4 Ah	3h (100%), 6h (50%), 14h (10%)	6500 K
1 17125 3 335	656509	1	56	30 W	3000 lm	11,1 V / 4,4 Ah	3h (100%), 6h (50%), 14h (10%)	6500 K





Tripod LED Light JARO

For indoor and outdoor use, IP 65.



- LED light with ultra-bright Everlight SMD LEDs.
- Spotlight continuously adjustable and lockable.
- Solid, modern aluminium housing.
- With safety glass.
- Telescopic tripod made of stable tubular powder-coated steel.
- Handy and reliable tube clamping nuts.
- With sturdy cable storing.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.



Article No.	EAN-Code	UP	Cable length	Cable	Plug	LEDs	Power	Luminous flux	Efficacy	Colour temperature	Telescopic
1 17125 3 334	656226	1	5 m	H07RN-F 3G1.0	BS 1363	44	30 W	2930 lm	95 lm/W	6500 K	max. 1.8 m
2 17125 3 434	657698	1	2.5 m	H07RN-F 3G1.0	BS 1363	2 x 28	2 x 20 W	2 x 1870 lm	95 lm/W	6500 K	max. 1.6 m



Halogen Light H 500 IP 44

- Fitted to a galvanized steel-tube frame. May be tilted and clamped at any desired angle.
- With safety glass and protective grill.
- Housing made of aluminium pressure casting.
- Voltage: 220 - 240 V~, 50/60 Hz.
- In colourful display-packaging.
- This luminaire is compatible with bulbs of the energy classes: B - E.
- The luminaire is sold with a bulb of the energy class: C.
- Plug: BS 1363



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Power	Luminous flux	Lamp efficacy	Colour temperature	Fittings
1 17148 3	565832	1	1,5 m	H05VV-F 3G1,0	400 W	8545 lm	21 lm/W	2900 K	R7s

Recommended accessories:

Article No.	EAN-Code 4007123...	UP	Description	Power	Luminous flux	Fittings	Length approx.	Diameter approx.	Energy efficiency class	E c (kWh/1000h)
1 17856 0 400	619573	10	Halogen bulb	400 W	8545 lm	R7s	119,6 mm	12 mm	C	400



Battery LED Light LUFOS 200 with infrared motion detector

For indoor and outdoor use, IP 44.

- LED lights can be used flexibly - without cable - due to battery operation.
- Universal use indoors and outdoors, e.g. for stairs indoors and outdoors, garages, carports or sheds.
- 4 super bright LG SMD-LEDs.
- PIR sensor with max 180° angle of reach and max. of 10 m of surrounding.
- Switch-on duration can be set up to 30 seconds.
- Service life with one set of batteries about 800 days with 6 switch-ons daily.
- Light head can be tilted and swivelled.
- Easy to install.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code 4007123...	UP	LEDs	Power	Luminous flux	Battery type	Battery duration	Colour temperature
1 17890 0	656936	4	4 x LG	2 W	210 lm	3x LR 14/C/Baby	Max. 800 Days (6x10 Sec./Day)	5000 K



NEW



LED Light JARO

For indoor and outdoor use, IP 65.

- LED light with ultra-bright Everlight SMD LEDs.
- Easy to mount thanks to external water-tight terminal clamp.
- With safety glass.
- Solid, modern aluminium housing.
- With adjustable mounting bracket for mounting.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.

Article No.	EAN-Code 4007123...	UP	LEDs	Power	Luminous flux	Efficacy	Colour temperature
1 17125 0 131	656257	1	14	10 W	900 lm	91 lm/W	6500 K
1 17125 0 231	656288	1	28	20 W	1870 lm	95 lm/W	6500 K
1 17125 0 331	656301	1	44	30 W	2930 lm	95 lm/W	6500 K
1 17125 0 531	656332	1	75	50 W	4770 lm	98 lm/W	6500 K
1 17125 0 831	656363	1	120	80 W	7200 lm	91 lm/W	6500 K
1 17125 0 031	656387	1	150	100 W	8850 lm	92 lm/W	6500 K





LED Light JARO with PIR sensor

For indoor and outdoor use, IP 44.

- LED light with ultra-bright Everlight SMD LEDs.
- Perfect for automatic lighting of entrance areas, driveways or carports and added security against break-ins and theft.
- PIR sensor horizontally and vertically rotatable. Range of detection up to 10 m, coverage angle approx. 120°.
- Duty cycle adjustable from between 10 seconds and approx. 5 minutes.
- With adjustable twilight switch.
- Easy to mount thanks to external, water-tight connection terminal.
- With safety glass.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.



NEW



Article No.	EAN-Code 4007123...	UP	LEDs	Power	Luminous flux	Efficacy	Colour temperature
1 17125 0 132	656271	1	14	10 W	900 lm	91 lm/W	6500 K
1 17125 0 232	656295	1	28	20 W	1870 lm	94 lm/W	6500 K
1 17125 0 332	656325	1	44	30 W	2930 lm	94 lm/W	6500 K
1 17125 0 532	656356	1	75	50 W	4770 lm	96 lm/W	6500 K





LED Light AL

For indoor and outdoor use, IP 44.

- LED light with super-bright OSRAM SMD-LEDs.
- Warm, impressive light colour.
- Broad light emission due to curved reflector disc.
- User-friendly installation due to external, waterproof connecting terminal.
- Solid, modern aluminium housing.
- With adjustable mounting bracket for mounting.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.



Article No.	EAN-Code 4007123...	UP	LEDs	Power	Luminous flux	Efficacy	Colour temperature
1 17801 0	645763	1	18	10 W	1060 lm	107 lm/W	3000 K
1 17802 0	645770	1	30	20 W	2080 lm	103 lm/W	3000 K
1 17803 0	645787	1	50	30 W	3050 lm	105 lm/W	3000 K





LED Light AL

For indoor and outdoor use, IP 44.

- LED light with super-bright OSRAM SMD-LEDs.
- Warm, impressive light colour.
- Ideal for automatic illumination of entry areas, driveways or carports and for deterring break-in and theft.
- Motion detector can be swivelled horizontally and vertically.
- Switch-on duration from approx. 10 seconds to approx. 4 minutes.
- User-friendly installation due to external, waterproof connecting terminal.
- Solid, modern aluminium housing.
- With adjustable mounting bracket for mounting.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+.

Osram LED inside

NEW



Article No.	EAN-Code 4007123...	UP	LEDs	Power	Luminous flux	Efficacy	Colour temperature
1 17801 0 010	656577	1	18	10 W	1.060 lm	106 lm/W	3000 K
1 17802 0 010	653584	1	30	20 W	2.080 lm	103 lm/W	3000 K
1 17803 0 010	653591	1	50	30 W	3.050 lm	105 lm/W	3000 K





Halogen Light H 500 IP 54

For installation indoors and outdoors, IP 54.

- Housing and frame made of aluminium pressure casting with coated surface.
- Optimal diffusion by means of an aluminium reflector.
- With safety glass.
- Adjustable mounting bracket for mounting on a tripod 117061 O or 117031 O.
- In colourful display-packaging.
- This luminaire is compatible with bulbs of the energy classes: B - E.
- The luminaire is sold with a bulb of the energy class: C.



Article No.	EAN-Code 4007123...	UP	Power	Luminous flux	Lamp efficacy	Colour temperature	Fittings	Colour
1 17138 0	249503	1	400 W	8545 lm	21 lm/W	2900 K	R7s	Black
1 17121 0	249497	1	400 W	8545 lm	21 lm/W	2900 K	R7s	White

Recommended accessories:

Article No.	EAN-Code 4007123...	UP	Description	Power	Luminous flux	Fittings	Length approx.	Diameter approx.	Energy efficiency class	E c (kWh/1000h)
1 17856 0 400	619573	10	Halogen bulb	400 W	8545 lm	R7s	119,6 mm	12 mm	C	400



Halogen Light H 500 IP 44 with PIR sensor

For installation indoors and outdoors, IP 44.

- Ideal for automatically lighting entryways to houses, garages, footpaths, etc. as well as for preventing break-ins and theft.
- Housing and frame made of aluminium pressure casting with coated surface.
- Range of detection: up to 12 metres, angle approx. 180°.
- Duty cycle adjustable between 15 sec. and 5 min.
- With twilight and sensivity switch.
- In colourful display-packaging.
- This luminaire is compatible with bulbs of the energy classes: B - E.
- The luminaire is sold with a bulb of the energy class: C.



Article No.	EAN-Code 4007123...	UP	Power	Luminous flux	Lamp efficacy	Colour temperature	Fittings	Colour
1 17236 0	249466	1	400 W	8545 lm	21 lm/W	2900 K	R7s	Black
1 17239 0	249329	1	400 W	8545 lm	21 lm/W	2900 K	R7s	White

Recommended accessories:

Article No.	EAN-Code 4007123...	UP	Description	Power	Luminous flux	Fittings	Length approx.	Diameter approx.	Energy efficiency class	E c (kWh/1000h)
1 17856 0 400	619573	10	Halogen bulb	400 W	8545 lm	R7s	119,6 mm	12 mm	C	400



LED Spot Premium City SH 8005 IP 44

For interior and exterior wall mounting, IP 44.
With 80 x 0,5 Watt high power LEDs.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- Light can be swiveled vertically and locked.
- 80 bright LG high performance LEDs.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Colour	Energy efficiency class
1 17929 0 310	633005	1	80 x 0,5 W	40 W	3700 lm	93 lm/W	6000 K	Anthracite	A+
1 17929 0 320	632992	1	80 x 0,5 W	40 W	3700 lm	93 lm/W	6000 K	White	A+

Design protected. / Patent pending.



Sensor LED Spot Premium City SH 8005 PIR IP 44 with PIR sensor

For interior and exterior wall mounting, IP 44.
With 80 x 0,5 Watt high power LEDs and PIR sensor.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- Light can be swiveled vertically and locked.
- 80 bright LG high performance LEDs.
- PIR sensor vertically pivoting.
- Range of detection: up to 10 metres, angle approx. 180°.
- Duty cycle adjustable between 10 sec. and 4 min.
- Continuous light function can be activated if a wall light switch is available.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Colour	Energy efficiency class
1 17929 0 311	632985	1	80 x 0,5 W	40 W	3700 lm	93 lm/W	6000 K	Anthracite	A+
1 17929 0 321	632978	1	80 x 0,5 W	40 W	3700 lm	93 lm/W	6000 K	White	A+

Design protected. / Patent pending.



Sensor LED Spotlight Premium City SH2705 PIR IP 44 with PIR sensor

For interior and exterior wall mounting, IP 44.
With 27 x 0,5 Watt high power LEDs and motion detector.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- 27 powerful LEDs with bunched ray of light.
- PIR sensor vertically pivoting.
- Range of detection: up to 10 metres, angle approx. 180°.
- Duty cycle adjustable between 10 sec. and 4 min.
- Spotlight can be rotated and locked.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Energy efficiency class
1 17961 0	617074	1	27 x 0,5 W	18 W	1080 lm	60 lm/W	6400 K	A

Design protected. / Patent pending.



Sensor LED Zone Lighting Premium City LH2705 PIR IP 44 with PIR sensor

For interior and exterior wall mounting, IP 44.
With 27 x 0,5 Watt high power LEDs and motion detector.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- 27 powerful LEDs with frosted glass for wide illumination.
- PIR sensor vertically pivoting.
- Range of detection: up to 10 metres, angle approx. 180°.
- Duty cycle adjustable between 10 sec. and 4 min.
- Light can be rotated and locked.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Energy efficiency class
1 17962 0	617098	1	27 x 0,5 W	18 W	1080 lm	60 lm/W	6400 K	A

Design protected. / Patent pending.



LED Spotlight Duo Premium City SV5405 IP 44

For interior and exterior wall mounting, IP 44. With 54 x 0,5 Watt high power LEDs.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- 54 powerful LEDs with bunched ray of light.
- Both spotlights horizontal and vertical adjustable.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Energy efficiency class
1 17967 0	617197	1	54 x 0,5 W	30 W	2160 lm	72 lm/W	6400 K	A

Design protected. / Patent pending.



Sensor LED Spotlight Duo Premium City SV5405 PIR IP 44

with PIR sensor

For interior and exterior wall mounting, IP 44.

With 54 x 0,5 Watt high power LEDs and motion detector.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- 54 powerful LEDs with bunched ray of light.
- PIR sensor vertically pivoting.
- Range of detection: up to 10 metres, angle approx. 180°.
- Duty cycle adjustable between 10 sec. and 4 min.
- Both spotlights horizontal and vertical adjustable.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Energy efficiency class
1 17965 0	617159	1	54 x 0,5 W	31 W	2160 lm	70 lm/W	6400 K	A

Design protected. / Patent pending.



LED Zone Lighting Duo Premium City LV5405 IP 44

For interior and exterior wall mounting, IP 44. With 54 x 0,5 Watt high power LEDs.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- 54 powerful LEDs with frosted glass and wider illumination.
- Both lights horizontal and vertical adjustable.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Energy efficiency class
1 17968 0	617210	1	54 x 0,5 W	30 W	2160 lm	72 lm/W	6400 K	A

Design protected. / Patent pending.



Sensor LED Zone Lighting Duo Premium City LV5405 PIR IP 44

with PIR sensor

For interior and exterior wall mounting, IP 44.

With 54 x 0,5 Watt high power LEDs and motion detector.

- Easy to mount thanks to the power connection provided on the mounting bracket. Simply insert the light or spotlight into the bracket after mounting.
- Solid and modern aluminium casing.
- 54 powerful LEDs with frosted glass and wider illumination.
- PIR sensor vertically pivoting.
- Range of detection: up to 10 metres, angle approx. 180°.
- Duty cycle adjustable between 10 sec. and 4 min.
- Both lights horizontal and vertical adjustable.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	LEDs	Power	Luminous flux	Lamp efficacy	Colour temperature	Energy efficiency class
1 17966 0	617173	1	54 x 0,5 W	31 W	2160 lm	70 lm/W	6400 K	A

Design protected. / Patent pending.



City LED Sales Panel

- Sales panels are the best way to realize sales deals.
- Attractive wooden display stand, digitally printed.
- 2 lights with easy connectable power plugs to demonstrate brightness at the POS.
- Size: 1/2 palette (60 x 80 cm).
- Height: 190 cm.

Article No.	EAN-Code	UP	Languages	Scope of delivery
1 17969 3 010	629480	1	EN	3 x 117963 0 + 6 x 117964 0 9 x 117962 0 3 x 117965 0 + 6 x 117966 0
1 17969 3 020	629510	1	EN	6 x 117961 0 + 6 x 117962 0 9 x 117965 0 9 x 117966 0
1 17969 3 030	629541	1	EN	9 x 117964 0, 9 x 117968 0, 6 x 117966 0, 3 x 117965 0



Coloured Round Lamp IP 44

Ideal for indoors and outdoors, IP 44.

- Solid housing made of plastic.
- Cover: Crystal-clear glass with inner prismatic structure.
- Suitable for mounting on either walls or ceilings.
- This luminaire is compatible with bulbs of the energy class: A++ - E.
- Delivery without bulbs.



Article No.	EAN-Code	UP	Power	Fittings	Colour	Measurements
1 27072 0	031429	2	100 W	E27	White	Diameter = 220 mm, Depth = 100 mm



Coloured Bulk Head Light IP 44

Ideal for indoors and outdoors, IP 44.

- Solid housing made of plastic.
- Cover: Crystal-clear glass with inner prismatic structure.
- Suitable for mounting on either walls or ceilings.
- This luminaire is compatible with bulbs of the energy class: A++ - E.
- Delivery without bulbs.



Article No.	EAN-Code	UP	Power	Fittings	Colour	Measurements
1 27042 0	031375	4	60 W	E27	White	178 x 122 x 112 mm



Bulk Head Light IP 44

Splash-proof, IP 44.

- Housing constructed out of solid synthetic material with galvanised protective grill cover.
- Cover: Crystal-clear glass with inner prismatic structure.
- Compact lights for installation in garages, workshops, cellars and external environments.
- Suitable for mounting on either walls or ceilings.
- This luminaire is compatible with bulbs of the energy class: A++ - E.
- Delivery without bulbs.



Article No.	EAN-Code	UP	Power	Fittings	Colour	Measurements
1 27012 0	031344	4	60 W	E27	Grey	176 x 122 x 110 mm



LED Oval Lamp L DN 5402 IP 44

Ideal for the garage, cellar, workshop and outdoors.

- Compact LED oval lamp made of plastic with a translucent cover.
- Suitable for mounting on either walls or ceilings.
- LEDs have a very long lifespan, are shock-proof and maintenance-free.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.



Article No.	EAN-Code	UP	Power	Luminous flux	Lamp efficacy	Colour temperature	Colour	Measurements	Energy efficiency class
1 27079 0	641697	1	10 W	800 lm	80 lm/W	6400 K	Light Grey	17,5 x 12 x 6,5 cm	A+



PIR Motion Detector PIR 240 IP 44

Automatically switches lamps on and off (incandescent, halogen, energy-saving bulbs and LED lamps) when someone enters the detection zone.

- For indoor and outdoor use, IP 44.
- Detection angle 240°. Max. range 12 m.
- Duty cycle adjustable between 10 sec. and 4 min.
- Response brightness adjustable from 10 to 150 lux.
- Switching capacity max. 1000 Watt (bulbs), max. 300 Watt (energy-saving lamp), max. 100 Watt (LED).
- Adjustable vertically and horizontally.
- With corner attachment.
- In colourful display-packaging.



Article No.	EAN-Code	UP	Voltage	Colour
	4007123...			
1 17091 0	249831	1	230 V	White
1 17191 0	619368	1	230 V	Anthracite



PIR Motion Detector PIR 180 IP 44

Automatically switches lamps on and off (incandescent, halogen, energy-saving bulbs and LED lamps) when someone enters the detection zone.

- For indoor and outdoor use, IP 44.
- Detection angle 180°. Max. range 12 m.
- Duty cycle adjustable between 10 sec. and 4 min.
- Response brightness adjustable.
- Switching capacity max. 1000 Watt (bulbs), max. 300 Watt (energy-saving lamp), max. 100 Watt (LED).
- Adjustable vertically and horizontally.
- In colourful display-packaging.



Article No.	EAN-Code	UP	Voltage	Colour
	4007123...			
1 17090 0	249817	1	230 V	White
1 17190 0	619344	1	230 V	Anthracite



Solar LED Spot SOL 80 ALU IP 44 with PIR sensor

In a stylish aluminium casing.
For outdoor use, IP 44.

- Solar LED spotlights can be used independently of the power grid because they generate their own environmentally friendly solar electricity.
- Solar LED light with PIR sensor and separate solar module
- Spotlight and solar module in a compact, well-designed aluminium casing.
- 8 high performance LEDs for illumination of large areas.
- Pivoting solar lamp.
- PIR sensor with max. 130° detection angle and max. range 10 m.
- Switch-on time adjustable to a max. of approx. 1 minute.
- Response intensity adjustable by a twilight switch.
- Sensitivity adjustable.
- 3 rechargeable and exchangeable NiMH Mignon AA batteries included.
- With integrated overcharge and total discharge protection to ensure continuous charging of the batteries.
- Light ON time is approx. 110 minutes with fully charged batteries.
- Battery capacity: 2,200 mAh.
- In colourful display-packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Cable length	Colour
1 17084 0	602209	1	8 x 0,5 W	350 lm	4,75 m	Alu



Solar LED Light SOL 800 IP 44 with PIR sensor

Practical and suitable for outdoor use, IP 44.

- Can operate independent from the mains - ideal for carports, porchs, gardens.
- 8 very bright LG-SMD LEDs for illumination of large areas.
- Solar panel can be mounted independent from the spot on the sunny side (incl. 4,75 m cable).
- Easy to mount. Simply insert the light or spotlight into the bracket after mounting.
- Spotlight horizontal and vertical adjustable.
- Pivoting PIR sensor with max. 180° detection angle and max. range 12 m.
- Switch-on time adjustable to a max. of approx. 1 minute.
- Includes rechargeable Li-ion battery, 3.7 V/3.6 Ah with built-in overcharge and deep discharge protection.
- Operating time of approx. 3 hours with fully loaded rechargeable battery.
- Quick-charge option when charging with power supply (not included).
- Solarmodul: 200 x 160 mm - Solar power 2.2 Wp.
- In colourful display-packaging.



Article No.	EAN-Code	UP	LEDs	Luminous flux	Colour temperature	Light duration	Cable length	Colour
1 17085 0 010	646418	1	8 LG SMD	400 lm	6000 K	3 h	4,75 m	White
1 17095 0 010	646425	1	8 LG SMD	400 lm	6000 K	3 h	4,75 m	Black





Solar LED Wall Lamp SOL 04 Plus IP 44 with PIR sensor

Practical and suitable for outdoor use, IP 44.

- Compact solar lamp with integrated solar module and PIR sensor.
- 2 super-bright LEDs, good light for orientation.
- Detection angle approx. 100°, max. range 7 m.
- Light switches itself on automatically for approx. 1 minute when the detection area is breached.
- Can operate independent of the mains.
- With twilight sensor.
- All in a housing, no connection by a cable necessary.
- Operating time of approx. 80 - 90 minutes with fully loaded rechargeable battery.
- 3 rechargeable and exchangeable NiMH Mignon AA batteries included.
- In colourful display-packaging.



Article No.	EAN-Code 4007123...	UP	LEDs	Luminous flux	Colour
1 17087 0	611799	1	2 x 0,5 W	85 lm	White
1 17097 0	611812	1	2 x 0,5 W	85 lm	Black



Solar LED Wall Light SOL WL 02007 IP 44

Practical and suitable for outside use.

- Solar LED external light with compact und shapely stainless steel casing.
- Features one standby LED that switches on at dusk; a second high-performance LED is switched on when motion is detected.
- Easy to install.
- All in a housing, no connection by a cable necessary.
- With LiFePO4 3.2 V rechargeable battery.
- In colourful display-packaging.



Article No.	EAN-Code 4007123...	UP	LEDs	Luminous flux	Measurements	Colour
1 17078 0	619696	1	2	30 lm	8 x 5 x 17 cm	Stainless steel



HOME SECURITY & SAFETY



SMOKE ALARM

98



CO DETECTOR

99



FIRE BLANKET

100



Smoke Detector RM L 3100

Particularly suitable for long-term use.

- VDS tested according to DIN EN 14604.
- Smoke detector with quality seal „Q“, complies to the increased demands of regulations 14-01 vfdb.
- With approved long-life cycle and reduction of false alarm signals.
- Increased stability against outer effect.
- 10 years of operational life without changing battery.
- 3 V lithium battery fixed in devices for constant operational readiness.
- Optical function display, with test button for the functional check.
- Includes mute function for false alarm and „Do not disturb function“ for low battery level.
- Shrill alarm - 85 dB.
- Optical and acoustic signal when the battery is low.
- Includes mounting materials.
- In colourful display-packaging.



Article No.	EAN-Code	UP	Height x Diameter	Signal sound	Battery type
1 29005 0	631636	1	31 x 100 mm	85 dB	3 V DC



Smoke Detector RM C 9010

Smoke detectors save lives!

More safety for you, your family and your property!

- Photoelectric detector, tested in accordance with EN 14604.
- Optical function display, with test button for the functional check.
- Shrill alarm - 85 dB.
- Acoustic signal when the battery is low.
- Includes nine-volt battery. Service life at least 1 year.
- Includes mounting materials.
- In colourful display-packaging.



Article No.	EAN-Code	UP	Height x Diameter	Signal sound	Battery type
1 29008 0	640911	1	35 x 100 mm	85 dB	1 x 9 V



Magnet Assembly Plate BR 1000 for Smoke Detector

- Mounting your smoke alarm without drilling, screwing or noise.
- No damage to the ceiling or cables/ducts.
- Very easy and fast assembly with two self-adhesive magnetic plates.
- Easy to remove the smoke alarm (for tests, replacing the battery, etc.).
- Not suitable for vinyl wallpapers, styrofoam, non-stick coated, silicized or Teflon-coated surface. Only limitedly suitable for smoke alarms with a diameter of less than 8 cm.



Article No.	EAN-Code	UP
	4007123...	
1 29000 0	637096	1



CO Detector CM L 4050

Protects against poisonous carbon monoxide (CO).

- For use in garages, living quarters with open fire places or when camping.
- Durable, modern electro-chemical sensor.
- Alarm signal and LED display.
- Signal tone at the end of the sensor service life.
- Shrill alarm - 85 dB.
- Optical and acoustic signal when the battery is low.
- Includes 3 batteries 1.5 V AA.
- In colourful display-packaging.



Article No.	EAN-Code	UP	Height x Diameter	Signal sound	Battery type
	4007123...				
1 29149 0	641581	1	42 x 107 mm	85 dB	3 x 1,5 V AA



Fire Blanket BLD-02

For more safety in your house!

- Tested acc. to EN 1869:2001.
- High quality glass fibre.
- 100 % fibreglass.
- Both sides are coated.
- Extinguish fires in seconds, ideal for home and work.
- Heat resistant up to 550 °C.
- Delivered in hard box for wall fastening.



Article No.	EAN-Code	UP	Measurements
1 29121 0	640867	6	120 x 120 cm



HOME, WORKSHOP & DIY



MULTIFUNCTION DETECTORS

102



HOUSE & HOBBY

103



HOSE REELS

105



TRESTLES & LADDERS

108



Electronic Multi-Tester MT 6 S/2

- Non-contact location of cables with AC voltage.
- Checking phase, neutral and earthing conductor at the sockets.
- Continuity check, e.g. of fuses, bulbs, etc.
- Polarity check, e.g. of batteries.
- Display through the LED.
- Small and handy.
- Because of the super-bright LED, can also be used as a torch.
- Inclusive 3 replaceable coin cells.
- In blister packaging.



Article No.	EAN-Code	UP
1 29715 0	249916	5



Moisture Detector MD

- To determine the moisture content of wood or building material, such as, e.g. concrete, brick, screed, plasterboard, wallpaper, etc.
- Measurement range of 5 - 50 % for wood, or 1.5 - 33 % for building material.
- Display on a large LCD display (in percent, resolution 0.1 %) as well as acoustically (can be deactivated).
- Practical „hold“ function also makes measurement possible at locations difficult to access.
- Automatic switch-off approx. 3 mins, after last application.
- Battery low voltage display.
- Robust, ergonomic housing with separate compartment for 9 V monobloc battery (not included).
- With protective cap.
- In colourful display-packaging.



Article No.	EAN-Code	UP
1 29868 0	249893	1




PMR Walkie Talkie TRX 3500

Free communication up to a distance of 5 km.

- In leisure time or when undertaking private or professional activities.
- Easy to use, small, handy and robust.
- LC display with background lighting.
- Eight channels with automatic channel search.
- Automatic battery saving function.
- Four ring tones, Roger Beep.
- Automatic noise suppressor.
- Keypad interlock.
- Battery monitoring.
- Including belt clip.
- Six AAA batteries required per set (batteries not included).
- In blister packaging.



Article No.	EAN-Code	UP
1 29094 0	632725	1





Signograph 25 Diamant-Set

Electric engraver - Engraving is as easy as writing.

- The universal set for all materials from soft to extra hard. With diamond, hard metal and hardened styluses. 2 forming heads for soft metals such as copper, tin and aluminium.
- Vibration strength: a (peak)~ = 74,02 m/s² = 7,545 g (peak value)
a (rms)~ = 52,34 m/s² = 5,336 g (rms-value/root-mean-square-value).
- In colourful display-packaging.

Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Plug
1 50076 3	051656	1	1,8 m	H05VV-F 2x0,75	BS 1363



Signograph 25 Set


Electric engraver - Engraving is as easy as writing.

- A powerful engraver with interchangeable hardened stylus and hard metal stylus.
- Vibration strength: a (peak)~ = 74,02 m/s² = 7,545 g (peak value)
a (rms)~ = 52,34 m/s² = 5,336 g (rms-value/root-mean-square-value).
- In colourful display-packaging.

Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Plug
1 50074 3	051649	1	2 m	H05VV-F 2x0,75	BS 1363

Recommended accessories for Article No.: 1 50076 0 + 1 50074 0:

Article No.	EAN-Code 4007123...	UP	Description
1 50813 0	020485	1	Adapter for spare stylus
1 50053 0	011964	1	Diamond stylus 2,5 x 18 mm
1 50824 0	020508	1	Modelling tool, ball tip
1 50825 0	020515	1	Modelling tool, pointed
1 50054 0	020492	1	Sintered carbide stylus



Compressor Hose Reel Anti Twist

With anti-twist centre for professional use.


- Ideal for any air tools.
- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Suitable for wall-mounting, comes with 2 hooks.
- Available either with PCL or DIN quick couplings.
- Advantage:
Hose can be unwound / wound while the connecting hose (2 m) is fitted to the compressor.

Article No.	EAN-Code 4007123...	UP	Hose length	Hose-Ø	Working pressure	Fittings
1 12703 3	091447	1	20 m	9/15 mm	15 bar	PCL (British System)
1 12703 0	002481	1	20 m	9/15 mm	15 bar	DIN



Compressor Hose Reel Standard

- Ideal for any air tools.
- Reel body made from special plastic fitted to a galvanised steel tube frame.
- Suitable for wall-mounting, comes with 2 hooks.
- Available either with PCL or DIN quick couplings.
- Hose has to be unwound before connected to the compressor.



Article No.	EAN-Code 4007123...	UP	Hose length	Hose-Ø	Working pressure	Fittings
1 12704 3	091454	1	20 m	9/15 mm	15 bar	PCL (British System)
1 12702 0	001392	1	20 m	6/12 mm	15 bar	DIN



Water Hose Reel WS 32

The light, practical and mobile water hose extension.

- Special hose with textile inlay and spiral wound cross-weave.
- Flexible and pressure-resistant.
- With a spraying nozzle with waterstop and a top connector.
- Drum is made of special highly breakproof plastic.
- Strong carrying frame made of galvanized tubular steel.
- Easy to wind and rewind.



Article No.	EAN-Code	UP	Hose length	Hose-Ø	Reel-Ø
1 23712 0	079575	1	20 m	1/2"	320 mm



Rubber Cable Reel X-GUM

- Compact and robust lightweight with integrated carrying handle.
- Reel body made of a special rubber mixture for long-term load bearing.
- Unbreakable, impact resistant, ageing and weather resistant.
- Resistant to a variety of oils, greases, gasoline and acids, UV and ozone radiation.



Article No.	EAN-Code	UP
1 16970 0 010	661824	4



Garant® Storage Reel - Empty

For everything that needs to be rolled up.

- Tubes.
- Rolls of fencing.



Article No.	EAN-Code	UP	Reel-Ø
1 13071 0	000647	1	290 mm



Brobusta® G Storage Reel - Empty

For everything that needs to be rolled up.

- Tubes.
- Rolls of fencing.



Article No.	EAN-Code	UP	Reel-Ø
1 31900 0	058266	1	380 mm



Steel Workstand MB 110

- Strong, stable square-profile steel tubing.
- Impact and scratch-resistant plastic coating.
- Folds up to save space.
- Easy to install.
- Box contents require partial assembly.



Article No.	EAN-Code 4007123...	UP	Height	Width	Loading capacity	Weight appr.
1 44480 0	101658	4	0,71 m	0,64 m	110 kg	3,0 kg



Extending Workstand MB 120 KH With Quick-Clamping System

- Strong, stable steel trestle.
- Ideal on staircases; feet fitted with protective caps.
- Fitted with quick-clamping system. Legs individually and conveniently height-adjustable up to 83 cm.
- Impact and scratch-resistant plastic coating.
- Wide, non-slip surface.
- Compact, can be folded up, comes with carrying handle.
- In colourful display-packaging.



Article No.	EAN-Code 4007123...	UP	Height	Width	Loading capacity	Height-adjustable	Weight appr.
1 44461 0	147687	2	0,83 m	0,97 m	120 kg	61 - 83 cm	6,3 kg



Telescopic Extending Workstand MB 160 H

- Strong, stable square-profile steel tubing.
- Impact and scratch-resistant plastic coating.
- Folds up to save space.
- Vertically adjustable - stability assured by user-friendly locking pins.
- Extending locking hooks prevent the worktop from sliding off sideways (max. 64 cm wide).
- Easy to install.
- Box contents require partial assembly.



Article No.	EAN-Code	UP	Height	Width	Loading capacity	Height-adjustable	Weight appr.
1 44470 0	101641	2	1,31 m max.	0,56 m	160 kg	81 - 131 cm	6,3 kg





Saw Horse MB 150 S

- Strong, stable, angled steel profile.
- Galvanised finish ensures effective protection against rust.
- Non-slip, serrated supporting surface.
- Compact, can be folded up.
- Easy to carry.
- Box contents require partial assembly.



Article No.	EAN-Code 4007123...	UP	Height	Width	Depth	Loading capacity	Weight appr.
1 44084 0	112319	2	0,79 m	0,81 m	0,85 m	150 kg	8,4 kg



Wooden Stepladder and Trestle HAB 150

- Solid and stable.
- Workmanship of the highest quality.
- The side rails are made of selected pine, and premium quality beech is used for the rungs.
- The ladder comes complete with robust galvanised fittings to give even greater stability.



Article No.	EAN-Code 4007123...	UP	Height	Width	Loading capacity	Rungs	Weight appr.
1 48501 0	030453	1	0,95 m	0,64 m	150 kg	2 x 3	5 kg



Aluminium Double-Sided Stepladder

- The very practical and stable ladder which can be climbed on both sides. Ideal for renovation and redecoration.
- Optimal firm positioning by wide, ribbed rungs for easy working.
- Spreader straps.
- With strong safety holding straps and a wide dimensioned and safe hinge joint.
- High-strength side rails, profiled rungs and non-slip plastic feet guarantee optimal inbuilt safety and high stability.



Article No.	EAN-Code 4007123...	UP	Rungs	Height of stepladder	Transport dimensions: length x width x depth	Weight appr.
1 40203 0	020171	1	2 x 3	0,60 m	0,7 x 0,41 x 0,16 m	2,5 kg
1 40204 0	020188	1	2 x 4	0,81 m	0,9 x 0,44 x 0,16 m	3,4 kg
1 40205 0	020195	1	2 x 5	1,03 m	1,1 x 0,46 x 0,16 m	4,2 kg
1 40206 0	020201	1	2 x 6	1,24 m	1,4 x 0,48 x 0,16 m	5,1 kg
1 40207 0	020218	1	2 x 7	1,46 m	1,6 x 0,50 x 0,16 m	7,9 kg
1 40208 0	020225	1	2 x 8	1,67 m	1,8 x 0,53 x 0,16 m	9,2 kg



Wooden Stepladder

The safe one, also suitable for electrical and decorating work.

- Top quality wood and careful manufacturing guarantee the user the topmost comfort and safety.
- The side rails are made of selected pine, and premium quality beech is used for the rungs.
- All sizes come complete with a practical and useful hook and also robust galvanised fittings to give even greater stability.



Article No.	EAN-Code 4007123...	UP	Rungs	Height	Height of stepladder	Transport dimensions: length x width x depth	Weight appr.
1 48104 0	029365	1	2 x 4	1,17 m	1,05 m	1,24 x 0,5 x 0,13 m	7,4 kg
1 48105 0	029372	1	2 x 5	1,4 m	1,32 m	1,52 x 0,53 x 0,13 m	8,9 kg
1 48106 0	029389	1	2 x 6	1,7 m	1,58 m	1,8 x 0,56 x 0,13 m	10,4 kg
1 48107 0	029396	1	2 x 7	2 m	1,84 m	2,08 x 0,58 x 0,13 m	12,5 kg
1 48108 0	029402	1	2 x 8	2,2 m	2,11 m	2,36 x 0,61 x 0,13 m	14,3 kg



Aluminium Stepladder with Work-Tray

The extra-light and reliable aluminium ladder with a big work-tray (approx. 28 x 11 cm) for any kind of tools, etc.

Saves time and unnecessary climbing up and down.

- Exceptional firm positioning by wide, ribbed rungs (with extra safety straps for the versions larger than 6 steps).
- A combination of high-quality aluminium profiles and expert workmanship guarantees prolonged serviceability and safety.
- High safety rail (60 cm).
- Compact for easy transporting and storage.



Article No.	EAN-Code 4007123...	UP	Level	Platform height	Transport dimensions: length x width x depth	Weight appr.
1 40123 0	020102	1	3	0,55 m	1,22 x 0,41 x 0,08 m	3,3 kg
1 40124 0	020119	1	4	0,76 m	1,45 x 0,43 x 0,08 m	3,9 kg
1 40125 0	020126	1	5	0,98 m	1,68 x 0,46 x 0,08 m	4,3 kg
1 40126 0	020133	1	6	1,2 m	1,91 x 0,48 x 0,08 m	5,2 kg
1 40127 0	020140	1	7	1,41 m	2,18 x 0,5 x 0,08 m	6,8 kg
1 40128 0	020157	1	8	1,62 m	2,4 x 0,53 x 0,08 m	7,6 kg






Multifunction Telescopic Aluminium Ladder

The variable lightweight ladder for universal applications.



- Can be used as a straight ladder or a stepladder, and this also on stairs or uneven surfaces.
- Can be quickly adapted from a stepladder to a straight ladder thanks to the unlockable and lockable safety hinges.
- Effortless adjustment from rung to rung thanks to the side clamping levers.
- Stable due to profiled rungs.
- Exceptionally compact for easy transporting and storage.
- Side rails and rungs of aluminium.



Article No.	EAN-Code 4007123...	UP	Rungs	Height of stepladder	Length of ladder	Transport dimensions: length x width x depth	Weight appr.
1 42044 0	655373	1	4 x 4	1,70 m	3,46 m	1,23 x 0,57 x 0,21 m	14,3 kg
1 42045 0	655380	1	4 x 5	2,22 m	4,60 m	1,51 x 0,61 x 0,21 m	17,0 kg



From digital to reality!




3D shelf planning

We offer you a quick and free option for planning shelf walls. With our 3D shelf planner, we arrange and visualise your individual assortment for you as a sales wall.

This way you get a realistic impression of the assortment at the P.O.S. The exact placing coordination for the stockers, the exact numbered amounts to be hung and product values are, so to speak, delivered all in one work process. That guarantees absolute certainty in planning and transparency and promises good sales and revenue - directly from the start.




Configure your shelving dimensions quickly and easily.



Display your products together as a range.



Rearrange and swap around your products in a matter of minutes.




Your made-to-measure shelving program awaits you. It is really efficient, as your valuable sales space will be allocated perfectly.

Tailor-made to the last detail - simple and effective!





ADVERTISING MEDIA & DISPLAYS



STICKER, BANNER & SIGNBOARDS

116



DUMP BINS + DISPLAYS

118



SALES STANDS

121



Transparent Sticker with Logo

- Can be ordered from your local sales representative.

Article No.	EAN-Code 4007123...	UP	Imprint	Measurements	Colour
0 41612 3	190959	1	Logo	25 x 15 cm	Red/Black
0 41612 4	190966	1	Logo	16,3 x 10 cm	Red/Black
0 41612 5	190973	1	Logo	16,3 x 10 cm	Red/White
0 41612 6	190980	1	Logo	13 x 8 cm	Red/Black
0 41612 7	190997	1	Logo	6,5 x 4 cm	Red/Black

Banner PVC

- Can be ordered from your local sales representative.

Article No.	EAN-Code 4007123...	UP	Languages	Description	Measurements
0 48685 0	635788	1	Neutral	Logos Made in Germany + Engineered in Germany	2 x 1 m

0 48685 1	635795	1	Neutral	Logos Engineered in Germany + Products	2 x 1 m
-----------	--------	---	---------	--	---------



Signboard: Logo With Internet Address

- For all countries.
- Can be ordered from your local sales representative.

Article No.	EAN-Code 4007123...	UP	Languages	Measurements
0 41562 2	156399	1	Neutral	98 x 40 cm
0 45257 2	566549	1	Neutral	125 x 40 cm



Signboard: Quality Products

- Can be ordered from your local sales representative.



Article No.	EAN-Code	UP	Languages	Measurements
0 45425 8	598274	1	EN	98 x 40 cm
0 47125 3	612383	1	EN	100 x 20 cm



Signboard: Made in Germany

- Can be ordered from your local sales representative.

Article No.	EAN-Code	UP	Languages	Measurements
0 47166 3	616442	1	EN	125 x 40 cm



Signboard: German Engineering & Product Safety

- Can be ordered from your local sales representative.

Article No.	EAN-Code	UP	Languages	Measurements
0 47166 4	616459	1	EN	125 x 40 cm



LuxPremium-LED Demo Display

For totally 3 items!

- For displaying 3 pcs. LuxPremium-LED torches of product range 2016/2017.
- Fixed to the display by nylon wire.
- Labels and topper to be ordered separately.
- Display comes without torches.

Article No.	EAN-Code	UP	Languages	Description	Colour	Measurements
	4007123...					
0 99660 0	637768	1	Neutral	Display empty for 3 torches including fuses and cable ties	Red	30 x 27,5 x 35 cm
0 99661 3	637799	1	EN	Inlay	Black/Red	30 x 35 cm



Promo Box „Big“

- Delivery without products.
- Can be ordered from your local sales representative.

Article No.	EAN-Code	UP	Languages	Measurements
	4007123...			
1 99986 0	036981	1	Neutral	59 x 59 x 80 cm



Universal Promo Box

- Delivery without products.
- Can be ordered from your local sales representative.

Article No.	EAN-Code 4007123...	UP	Languages	Description	Measurements
0 01084 4	093816	1	Neutral	with logo	53,4 x 29,7 x 24 cm
0 41868 1	215607	1	Neutral	Neutral	53,4 x 29,7 x 24 cm



Promo Box Neutral

- Delivery without products.
- Varied quantities!

Article No.	EAN-Code 4007123...	UP	Languages	Description	Measurements
0 47395 0	632312	1	Neutral	Headboard with brennenstuhl® logo	34 x 25 cm
0 01085 4	632466	1	Neutral	Promo box without brennenstuhl® logo	34 x 39,7 x 13,6 cm



Stackable Promo Box

- Delivery without products.
- Can be ordered from your local sales representative.

Article No.	EAN-Code	UP	Languages	Description	Measurements
	4007123...				
0 01083 7	091478	1	Neutral	Box for stackable promo box	54,5 x 36,8 x 25 cm
0 01083 8	091485	1	Neutral	Headboard for stackable promo box	49,7 x 54,5 cm
0 45103 7	249176	1	1. side german, 2. side EN, NL, SE, ES, GR, TR, RU, PT, FI	Headboard „standby“	49,7 x 54,5 cm



Stackable Promo Box With Separating Web


- Delivery without products.
- Can be ordered from your local sales representative.

Article No.	EAN-Code	UP	Languages	Description	Measurements
	4007123...				
0 01085 6	610341	1	Neutral	Stackable Promo Box with Separating Web	58,6 x 37,4 x 27,5 cm
0 01085 7	610877	1	Neutral	Separating web	
0 01086 1	634491	1	Neutral	Corrugated cardboard	58,4 x 37,2 cm



1

Wire Stand without Sign Board



2

- Delivery without products.
- Can be ordered from your local sales representative.

6

5

4

3

Article No.	EAN-Code 4007123...	UP	Languages	Description
1 99951 0	164479	1	-	Wire Stand with 4 wheels
2 1 99951 0 010	662210	1	-	Wire Stand L-Format. Non-wheeled for wall-fixing/wall leaning
Extras to order:				
3 1 99952 0	164486	1	-	Wire bottom (use on its own or as a bottom for a dump bin)
4 1 99953 0	164493	1	-	Basket (please order additional wire bottom)
5 1 99955 0	164523	1	-	Hanging Hook 20 cm
6 1 99954 0	164509	1	Neutral	„brennenstuhl“ sign board



Universal Display

- Size: 1/4 palette (60x40 cm)
- Delivery without products.
- Can be ordered from your local sales representative.

Article No.	EAN-Code 4007123...	UP	Languages	Description
1 99612 0 010	661046	1	Neutral	1x Ground Base + 3x Stacking Box grey
0 49790 6	657070	1	EN	Headboard »LED«
0 49967 4	639724	1	Neutral	Headboard »Brennenstuhl«



Universal Sales Display Stand (Cable Reels)

- Will be supplied FOC on request for orders of 16 cable reels, or for a mixture of reels and extension leads.
- Basic dimensions 62 x 50 cm.
- Delivery without products.
- Can be ordered from your local sales representative.

Article No.	EAN-Code	UP
	4007123...	
1 19900 0	020621	1



City LED Sales Panel

- Sales panels are the best way to realize sales deals.
- Attractive wooden display stand, digitally printed.
- 2 lights with easy connectable power plugs to demonstrate brightness at the POS.
- Size: 1/2 palette (60 x 80 cm).
- Height: 190 cm.

Article No.	EAN-Code	UP	Languages	Scope of delivery
	4007123...			
1 17969 3 010	629480	1	EN	3 x 117963 0 + 6 x 117964 0 9 x 117962 0 3 x 117965 0 + 6 x 117966 0
1 17969 3 020	629510	1	EN	6 x 117961 0 + 6 x 117962 0 9 x 117965 0 9 x 117966 0
1 17969 3 030	629541	1	EN	9 x 117964 0, 9 x 117968 0, 6 x 117966 0, 3 x 117965 0



City LED Sales Display 2. Generation

- Sales panels are the best way to realize sales deals.
- Attractive wooden display stand, digitally printed.
- 2 lights with easy connectable power plugs to demonstrate brightness at the POS.
- Size: 1/2 palette (60 x 80 cm).
- Height: 190 cm.

Article No.	EAN-Code	UP	Languages	Scope of delivery
1 17929 3 031	638642	1	EN	without products, mounted with 117929 0 613 and 117929 0 321

Article No.	Page
0 01083 7	120
0 01083 8	120
0 01084 4	119
0 01085 4	119
0 01085 6	120
0 01085 7	120
0 01086 1	120
0 41562 2	116
0 41612 3	116
0 41612 4	116
0 41612 5	116
0 41612 6	116
0 41612 7	116
0 41868 1	119
0 43135 3	119
0 43135 6	119
0 45103 7	120
0 45257 2	116
0 45425 8	117
0 47125 3	117
0 47166 3	117
0 47166 4	117
0 47395 0	119
0 47488 1	117
0 47488 2	117
0 47490 3	117
0 47490 4	117
0 48685 0	116
0 48685 1	116
0 49790 6	121
0 99660 0	118
0 99661 3	118
1 07293 3	14
1 07818 3 004	15
1 08099 0	8
1 08099 3	8
1 09320 3	18
1 09420 3	18
1 09545 3	18
1 09820 3	18
1 09825 3 001	15
1 09825 3 027	15
1 09841 3 001	15
1 09874 3	22
1 09878 3	22
1 10820 3	18
1 10855 3	18
1 10856 3	18
1 10890 3	18

Article No.	Page
1 10922 3	19
1 10923 3	19
1 12702 0	105
1 12703 0	105
1 12703 3	105
1 12704 3	105
1 13071 0	107
1 13195 3	20
1 13887 3	20
1 14174 3 015	13
1 14877 3	20
1 14885 3	21
1 15010 3	50
1 15040 3	52
1 15042 3	52
1 15061 3 114	46
1 15061 3 124	46
1 15061 3 128	46
1 15061 3 174	46
1 15061 3 178	46
1 15061 3 328	30
1 15061 3 378	30
1 15062 3 444	52
1 15062 3 454	52
1 15141 3	23
1 15176 3	16
1 15323 3 000	48
1 15323 3 020	48
1 15323 3 070	48
1 15323 3 320	48
1 15323 3 329	48
1 15324 3 006	49
1 15324 3 026	49
1 15324 3 029	49
1 15325 3 000	49
1 15325 3 020	49
1 15325 3 070	49
1 15325 3 320	49
1 15325 3 329	49
1 15330 3 120	47
1 15330 3 128	47
1 15334 3 215	45
1 15334 3 218	45
1 15334 3 625	44
1 15334 3 628	44
1 15339 3 120	47
1 15339 3 128	47
1 15354 3 134	31
1 15600 3 536	28

Article No.	Page
1 15605 3 024	41
1 15605 3 394	29
1 15605 3 534	28
1 15625 3 416	43
1 15625 3 515	34
1 15675 3	30
1 15945 3 616	50
1 15950 3	52
1 15952 3	52
1 16044 0	17
1 16055 0	62
1 16065 0	62
1 16432 0	62
1 16434 0	62
1 16436 0	63
1 16646 3	23
1 16650 3 015	19
1 16654 3 015	19
1 16655 3 015	19
1 16656 3 015	19
1 16657 3 015	19
1 16765 0 110	9
1 16765 0 210	9
1 16765 0 225	9
1 16771 0	7
1 16772 0	7
1 16773 0	7
1 16774 0	7
1 16797 0	7
1 16820 3	19
1 16821 3	19
1 16846 3	23
1 16850 0	7
1 16858 0	7
1 16859 0	7
1 16970 0 010	106
1 16972 3 150	15
1 16974 3 140	22
1 17031 0	77
1 17061 0	77
1 17078 0	96
1 17084 0	95
1 17085 0 010	95
1 17087 0	96
1 17090 0	94
1 17091 0	94
1 17095 0 010	95
1 17097 0	96
1 17121 0	86

Article No.	Page
1 17125 0 031	81
1 17125 0 131	81
1 17125 0 132	82
1 17125 0 231	81
1 17125 0 232	82
1 17125 0 331	81
1 17125 0 332	82
1 17125 0 531	81
1 17125 0 532	82
1 17125 0 831	81
1 17125 3 230	24
1 17125 3 233	78
1 17125 3 235	79
1 17125 3 330	24
1 17125 3 334	80
1 17125 3 335	79
1 17125 3 338	25
1 17125 3 343	78
1 17125 3 434	80
1 17125 3 438	25
1 17125 3 530	24
1 17125 3 533	78
1 17125 3 830	24
1 17125 3 833	78
1 17138 0	86
1 17143 0 050	70
1 17143 3	70
1 17148 3	85
1 17154 0	74
1 17155 0	74
1 17159 0	70
1 17190 0	94
1 17191 0	94
1 17236 0	86
1 17239 0	86
1 17264 0 002	72
1 17287 0	72
1 17308 0	72
1 17322 3	58
1 17326 3	57
1 17329 0	58
1 17541 0 010	75
1 17542 0 010	75
1 17567 0	71
1 17570 0	70
1 17589 0	73
1 17601 3	76
1 17644 0	73
1 17678 3	76

Article No.	Page
1 17730 0	68
1 17737 0	71
1 17801 0	83
1 17801 0 010	84
1 17802 0	83
1 17802 0 010	84
1 17803 0	83
1 17803 0 010	84
1 17856 0 400	85
1 17856 0 400	86
1 17856 0 400	86
1 17860 0 051	66
1 17860 0 161	66
1 17874 0	68
1 17875 0	67
1 17876 0	69
1 17878 0	69
1 17890 0	85
1 17929 0 310	87
1 17929 0 311	87
1 17929 0 320	87
1 17929 0 321	87
1 17929 3 031	123
1 17961 0	88
1 17962 0	88
1 17965 0	89
1 17966 0	90
1 17967 0	89
1 17968 0	90
1 17969 3 010	91
1 17969 3 010	122
1 17969 3 020	91
1 17969 3 020	122
1 17969 3 030	91
1 17969 3 030	122
1 17989 0 100	67
1 17990 0	63
1 18247 0	9
1 18276 0	8
1 18277 3	6
1 19801 3	14
1 19805 3	14
1 19806 3	14
1 19807 3	21
1 19809 3	14
1 19811 3	14
1 19900 0	122
1 20801 3	12
1 20806 3	12

Article No.	Page
1 20811 3	12
1 20812 3	12
1 20885 3	13
1 20886 3	13
1 21805 3	12
1 21875 3	12
1 23712 0	106
1 23807 3	8
1 24100 3 110	23
1 24100 3 300	16
1 24101 3 110	23
1 24102 3 300	16
1 25605 3 378	29
1 27012 0	93
1 27042 0	92
1 27072 0	92
1 27079 0	93
1 29000 0	99
1 29005 0	98
1 29008 0	98
1 29063 3	17
1 29064 3	17
1 29094 0	103
1 29121 0	100
1 29149 0	99
1 29715 0	102
1 29868 0	102
1 30895 3	10
1 30895 3 110	20
1 30945 3	11
1 31130 3	10
1 31900 0	107
1 39100 3 014	35
1 39100 3 016	35
1 39100 3 018	35
1 39100 3 515	32
1 39100 3 644	35
1 39100 3 646	35
1 39100 3 654	35
1 39100 3 900	33
1 39400 3 416	43
1 39620 3 003	51
1 39620 3 013	51
1 40123 0	112
1 40124 0	112
1 40125 0	112
1 40126 0	112
1 40127 0	112
1 40128 0	112

Article No.	Page
1 40203 0	111
1 40204 0	111
1 40205 0	111
1 40206 0	111
1 40207 0	111
1 40208 0	111
1 42044 0	113
1 42045 0	113
1 44084 0	110
1 44461 0	108
1 44470 0	109
1 44480 0	108
1 48104 0	111
1 48105 0	111
1 48106 0	111
1 48107 0	111
1 48108 0	111
1 48501 0	110
1 50053 0	104
1 50054 0	104
1 50074 3	104
1 50076 3	104
1 50645 3	56
1 50660 3	56
1 50695 3	31
1 50704 3	55
1 50747 3	54
1 50750 3	55
1 50813 0	104
1 50824 0	104
1 50825 0	104
1 50826 3	57
1 50846 0	61
1 50850 0 010	60
1 50852 0	60
1 50853 0	59
1 50853 3	59
1 50855 0	61
1 95112 3 601	40
1 95113 3 100	37
1 95113 3 101	37
1 95114 3 100	37
1 95114 3 603	36
1 95114 3 604	36
1 95115 3 600	34
1 95116 3 100	39
1 95116 3 602	38
1 95116 3 603	38
1 95118 3 100	39

Article No.	Page
1 95118 3 601	38
1 95118 3 605	42
1 95150 3 605	42
1 95152 3 600	41
1 95154 3 100	37
1 95154 3 101	37
1 95154 3 102	37
1 95154 3 603	36
1 95155 3 600	41
1 95156 3 100	39
1 95156 3 101	39
1 95156 3 601	38
1 95158 3 100	39
1 95513 3 100	37
1 95554 3 100	37
1 95556 3 100	39
1 95558 3 100	39
1 99612 0 010	121
1 99951 0	121
1 99951 0 010	121
1 99952 0	121
1 99953 0	121
1 99955 0	121
1 99986 0	118

brennenstuhl®

_ smart technology.

brennenstuhl® International Group



Hugo Brennenstuhl GmbH & Co. KG
Headquarter Werk 1



Hugo Brennenstuhl GmbH & Co. KG
Headquarter Werk 2

BERNOLSHEIM
France 

TÜBINGEN
Germany 

TAUFKIRCHEN
Austria 

BAAR
Switzerland 



Brennenstuhl S.A.S.



Lectra Technik Ges.m.b.H.



Lectra Technik AG




brennenstuhl®



_ smart technology.

We are exactly where you need us.




Our brennenstuhl® Sales Representatives - on the road throughout Germany but always at your disposal. Contact **Telephone +49 (0) 70 71 - 88 01-0**

Just call us. We would be very pleased in choosing the right products for your demand together with you.

Together we will start the successful sales of our products.



brennenstuhl® is a certified AEO, or authorised economic operator, and as such is eligible for all simplified customs procedures within and outside the EU



You find us also on:



brennenstuhl®

_ smart technology.

**Hugo Brennenstuhl GmbH & Co.
Kommanditgesellschaft**

Elektrotechnik · Elektronik · Sicherheitstechnik
72074 Tübingen · Seestraße 1-3 · Germany

Tel. +49 (0) 70 71 - 88 01 - 0 · Fax +49 (0) 70 71 - 8 76 57
www.brennenstuhl.com · export@brennenstuhl.de

ILN-Nr. 40-07123-00000-5
Ust.-Id.-Nr. DE 146890047

