

## Han 10M-Metal Cover-DL-Seal-for Hood




Image is for illustration purposes only. Please refer to product description.

Part number	09 37 010 5403
Specification	Han 10M-Metal Cover-DL-Seal-for Hood
HARTING eCatalogue	<a href="https://b2b.harting.com/09370105403">https://b2b.harting.com/09370105403</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> M
Type of accessory	Protection cover
Description of the accessory	for hoods Metal With fixing cord

### Version

Size	10 B
Locking type	Double locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	111.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140055544
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors