

SDAC clamp holder for lathes, positive

For longitudinal and copy turning using DC indexable inserts

ATORN[®]

Application

For longitudinal and copy turning using DC 55° indexable inserts



Version

- Precision-made steel support, bronzed, hardened, type D, pitch angle 90°, tip angle 55°, clearance angle 7°

Art. no.	17829 030
ISO name	SDAC R/L 0808 X07-A
Shaft height	8 mm
Shank width	8 mm
Length	115 mm
Programming size	8 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Right
DIN	4983

EAN-Code

4050293692778