

Hydraulic jacks

Application:

For simple lifting of vehicles and components.

Execution:

- Steel, with pressure limiting valve to prevent overload.
- Models A, AX with one piston and one spindle.
- Models AT, ATDX with double piston
- ATN model with double telescopic piston for especially low overall height. Suitable for vehicles with limited ground clearance and confined space such as buses, low loaders, etc. The lever is operated horizontally, as vertical operation is often not possible with overhanging bodywork.
- Loading of the lever in axial direction only and over the entire surface extends the service life.
- Models AX 8-220, A 10-220, A 12-230, A 12-270, AX 15-230, AX 20-240, A 30-240, ATDX 3-185 and AT 5-215 with crown footprint.

Delivery:

1x hydraulic jack made of steel A 2-170 20 KN, 115 mm stroke.



Art. no.	29760 010
Model	A2-170
Compressive force	20 kN
Construction height, retracted	170 mm
Lift height	115 mm
Spindle stroke	92 mm
Gross Weight	4.020 kg
Product Group	269