

Rotating transport trolley

Carrying capacity 1–6 t



Application:

For transporting machines and other heavy loads. The specific characteristic is that very closely positioned heavy loads can be steered in any direction.

Execution:

- Sturdy, torsion-free steel welded construction
- Can be very easily moved and turned at 360° thanks to the special mounting
- GKS-alperfekt® roller, slightly steerable, low rolling resistance
- Support surfaces with non-slip waffle rubber
- 5-year warranty

Advantage:

- Several rotating transport trolleys can be used at the same time depending on the contact point and weight distribution of the heavy load as well as of the condition of the floor



Art. no.	50261 472
Brand	GKS PERFECT
Manufacturer Part Number	10238
Load-carrying capacity	2 t
Number of load rollers	3 PCS
Installation height of load rollers	110 mm
Wheel diameter	85 mm
Wheel width	85 mm
Length	685 mm
Width	515 mm
Height	110 mm
Diameter of contact surface	170 mm
Gross Weight	30.000 kg
Product Group	5AH

EAN

0705632933107