

Flat magnetic grips, hard ferrite core, steel jacket

With bore hole and countersink

ORION[®]

Application:

Auxiliary materials with universal application during clamping, assembling, lifting and welding operations, and for installing in devices etc.

Version:

- With hard ferrite core
- Surface galvanised
- Magnetic shielding
- With bore hole and countersink
- Operating temperature up to 100°C

Advantage:

- Fastening option from inside with a screw



| | |
|---------------------------|------------------|
| Art. no. | 51146 770 |
| Outer diameter | 50 mm |
| Height | 10.5 mm |
| Bore diameter | 6.5 mm |
| Adherence strength | 180 N |

EAN-Code

4039247261956

