

Torque wrench Safe-Torque A 2 set 1

With 1/4 inch direct bit mount, set of 23 pieces



Execution:

- Slip-over release mechanism - overtightening not possible
- Torque lock function - torque function can be switched off
- and can be used as a standard ratchet with high release torque
- For controlled right- and left-hand tightening and loosening with and without torque values
- Easy adjustment and securing of the desired torque value,
- with audible and perceptible click when scale values are reached
- Finely toothed ratchet 72 teeth with low return angle of only 5°
- With 1/4 inch hexagon bit direct mount, with strong permanent magnet
- Includes inserts with hexagon drive in AF 5.5/6/7/8/9/10/11/12/13 mm
- 50 mm long bit inserts in AF PH 2, TX 10, 15, 20, 25, 27, 30, hexagon socket 2.5/3/4/5/6 mm



Delivery:

In fabric pouch with hook-and-loop fastener

Art. no.	52261 630
Brand	WERA
Manufacturer Part Number	05075832001
Tip size	1/4 inch
Max. torque	12 Nm
Min. torque	2 Nm
Scale value torque	0.1 Nm
Length	245.5 mm
Min./max. torque	2-12 Nm
Error limit (%)	10 %
Gross Weight	1.070 kg
Product Group	542

EAN

4013288223043