

## Electronics Super Knips ESD

Stainless steel polished, without chamfer, with or without wire clamp



### Application:

For precision cutting tasks in electronics and precision mechanics fields.

### Execution:

- INOX surgical stainless steel, air-hardened
- Polished head
- Ground, very sharp blades without chamfer for flush cutting
- Joint with stainless steel rivet
- With opening spring and opening limiter

### Advantage:

- Safe, ergonomic and fatigue-free working thanks to two-component handles
- Precisely shaped tips also cut close-fitting wires from a diameter of 0.2 mm
- Extremely smooth action for fatigue-free working
- ESD design, discharges electricity



<b>Art. no.</b>	<b>53107 100</b>
<b>Brand</b>	KNIPEX
<b>Manufacturer Part Number</b>	78 13 125 ESD
<b>Length</b>	125 mm
<b>Max. soft wire diameter cutting capacity</b>	1.6 mm
<b>Head design</b>	Without bevel, Wire clamp
<b>Surface</b>	Plain
<b>Material of handle</b>	2-component plastic
<b>ESD-capable</b>	Yes
<b>Gross Weight</b>	0.057 kg
<b>Product Group</b>	535

### EAN

4003773025153