


Features

- Defence Standard 61-12 (Part 4)
- Unscreened industrial cable
- Flame resistant to BSEN60332-1

RS PRO Family Name

RS Stock No.: 236-9251



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Designed for use in high density wiring applications and the interconnection of components, instruments and electronic equipment

Extensively used in aircraft, computers, data processors, telemetry applications, data transmission, military vehicles and equipment

The cable offers good insulation due to the PVC insulation material and installation is easy and efficient thanks to the flexible layout of the cable

General Specifications

Conductor	Annealed Flexible Tinned Copper. 7/0.2mm. 24 AWG.
Insulation Material	PVC
Insulation Colour	*See below table
Sheath Material	PVC
Sheath Colour	Black
Approximate Diameter	7.5mm
Number of conductors	20
Screening	Unscreened
Reel length	25 metres

*Colour of cores table

1 Red	7 Brown	13 Red/Blue	19 Yellow/Blue	25 Yellow/Green	31 White/Brown
2 Blue	8 Violet	8 Violet 14 Green/Red		26 White/Green	32 Brown/Black
3 Green	9 Orange	15 Yellow/Red	21 Blue/Black	27 Green/Black	33 Grey/Brown
4 Yellow	10 Pink	16 White/Red	22 Orange/Blue	28 Orange/Green	34 Yellow/Violet
5 White	11 Turquoise	17 Red/Black	23 Green/Blue	29 Grey/Green	35 Violet/Black
6 Black	12 Grey	18 Red/Brown	24 Grey/Blue	30 Yellow/Brown	36 White/Violet

Mechanical Specifications

Minimum temperature	-15°C
Maximum temperature	+70°C

Electrical Specifications

Conductor resistance	92 ohm/km at 20°C
Insulation resistance	200 M.Ohms/km minimum
Voltage rating	440V
Current rating	1.0 amperes per core (guidance only – dependant on installation)



Approvals

Declarations	MFR Declaration of Conformity
Standards Met	Defence Standard 61-12 (Part 4)

Similar Products

Stock No. Brand Conductor cores Number of cores Reel length length Screened/Unscreened 2369254 RS PRO 7/0.2mm 2 100 Unscreened 2369255 RS PRO 7/0.2mm 3 100 Unscreened 2369260 RS PRO 7/0.2mm 4 100 Unscreened 2369261 RS PRO 7/0.2mm 4 25 Unscreened 2369265 RS PRO 7/0.2mm 6 100 Unscreened 2369267 RS PRO 7/0.2mm 6 25 Unscreened 2369271 RS PRO 7/0.2mm 8 100 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369246 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 10 Unscreened 2369229 RS PRO						
2369255 RS PRO 7/0.2mm 2 25 Unscreened 2369259 RS PRO 7/0.2mm 3 100 Unscreened 2369260 RS PRO 7/0.2mm 4 100 Unscreened 2369261 RS PRO 7/0.2mm 4 25 Unscreened 2369267 RS PRO 7/0.2mm 6 100 Unscreened 2369270 RS PRO 7/0.2mm 8 25 Unscreened 2369271 RS PRO 7/0.2mm 8 25 Unscreened 23692241 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 25 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 <td< th=""><th>Stock No.</th><th>Brand</th><th>Conductor</th><th></th><th></th><th>Screened/Unscreened</th></td<>	Stock No.	Brand	Conductor			Screened/Unscreened
2369259 RS PRO 7/0.2mm 3 100 Unscreened 2369260 RS PRO 7/0.2mm 4 100 Unscreened 2369261 RS PRO 7/0.2mm 4 25 Unscreened 2369265 RS PRO 7/0.2mm 6 25 Unscreened 2369270 RS PRO 7/0.2mm 8 100 Unscreened 2369271 RS PRO 7/0.2mm 8 100 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369249 RS PRO 7/0.2mm 20 25 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369231 RS PRO 16/0.2mm 3	2369254	RS PRO	7/0.2mm	2	100	Unscreened
2369260 RS PRO 7/0.2mm 4 100 Unscreened 2369261 RS PRO 7/0.2mm 4 25 Unscreened 2369265 RS PRO 7/0.2mm 6 100 Unscreened 2369270 RS PRO 7/0.2mm 8 100 Unscreened 2369271 RS PRO 7/0.2mm 8 25 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3	2369255	RS PRO	7/0.2mm	2	25	Unscreened
2369261 RS PRO 7/0.2mm 4 25 Unscreened 2369265 RS PRO 7/0.2mm 6 100 Unscreened 2369270 RS PRO 7/0.2mm 8 100 Unscreened 2369271 RS PRO 7/0.2mm 8 25 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 25 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 <	2369259	RS PRO	7/0.2mm	3	100	Unscreened
2369265 RS PRO 7/0.2mm 6 100 Unscreened 2369267 RS PRO 7/0.2mm 6 25 Unscreened 2369270 RS PRO 7/0.2mm 8 100 Unscreened 2369271 RS PRO 7/0.2mm 8 25 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369231 RS PRO 16/0.2mm 2 25 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4	2369260	RS PRO	7/0.2mm	4	100	Unscreened
2369267 RS PRO 7/0.2mm 6 25 Unscreened 2369270 RS PRO 7/0.2mm 8 100 Unscreened 2369271 RS PRO 7/0.2mm 8 25 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 20 100 Unscreened 2369249 RS PRO 7/0.2mm 20 25 Unscreened 2369251 RS PRO 7/0.2mm 36 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 25 Unscreened 2369230 RS PRO 16/0.2mm 3 100 Unscreened 2369231 RS PRO 16/0.2mm 3 25 Unscreened 2369232 RS PRO 16/0.2mm 4 100 Unscreened 2369233 RS PRO 16/0.2mm 4	2369261	RS PRO	7/0.2mm	4	25	Unscreened
2369270 RS PRO 7/0.2mm 8 100 Unscreened 2369271 RS PRO 7/0.2mm 8 25 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6	2369265	RS PRO	7/0.2mm	6	100	Unscreened
2369271 RS PRO 7/0.2mm 8 25 Unscreened 2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6	2369267	RS PRO	7/0.2mm	6	25	Unscreened
2369245 RS PRO 7/0.2mm 12 100 Unscreened 2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 23692219 RS PRO 16/0.2mm 12	2369270	RS PRO	7/0.2mm	8	100	Unscreened
2369246 RS PRO 7/0.2mm 12 25 Unscreened 2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12	2369271	RS PRO	7/0.2mm	8	25	Unscreened
2369249 RS PRO 7/0.2mm 20 100 Unscreened 2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 3 25 Unscreened 2369234 RS PRO 16/0.2mm 4 100 Unscreened 2369239 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 25 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18	2369245	RS PRO	7/0.2mm	12	100	Unscreened
2369251 RS PRO 7/0.2mm 20 25 Unscreened 2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369219 RS PRO 16/0.2mm 12 25 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 7/0.2mm 18	2369246	RS PRO	7/0.2mm	12	25	Unscreened
2369256 RS PRO 7/0.2mm 36 25 Unscreened 2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 6 100 Unscreened 2369239 RS PRO 16/0.2mm 6 25 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369219 RS PRO 16/0.2mm 12 25 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 7/0.2mm 4	2369249	RS PRO	7/0.2mm	20	100	Unscreened
2369229 RS PRO 16/0.2mm 2 100 Unscreened 2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 7/0.2mm 4 25 Screened 2369263 RS PRO 7/0.2mm 4	2369251	RS PRO	7/0.2mm	20	25	Unscreened
2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 6 100 Unscreened 2369239 RS PRO 16/0.2mm 6 25 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369219 RS PRO 16/0.2mm 12 25 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 7/0.2mm 4 100 Screened 2369262 RS PRO 7/0.2mm 4 25 Screened 2369263 RS PRO 7/0.2mm 4	2369256	RS PRO	7/0.2mm	36	25	Unscreened
2369230 RS PRO 16/0.2mm 2 25 Unscreened 2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 6 100 Unscreened 2369239 RS PRO 16/0.2mm 6 25 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369219 RS PRO 16/0.2mm 12 25 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 7/0.2mm 4 100 Screened 2369262 RS PRO 7/0.2mm 4 25 Screened 2369263 RS PRO 7/0.2mm 4						
2369231 RS PRO 16/0.2mm 3 100 Unscreened 2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369240 RS PRO 16/0.2mm 12 100 Unscreened 2369219 RS PRO 16/0.2mm 12 25 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 500 Screened 2369264 RS PRO 7/0.2mm 6	2369229	RS PRO	16/0.2mm	2	100	Unscreened
2369232 RS PRO 16/0.2mm 3 25 Unscreened 2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 500 Screened 2369264 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6	2369230	RS PRO	16/0.2mm	2	25	Unscreened
2369233 RS PRO 16/0.2mm 4 100 Unscreened 2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 8 <td< td=""><td>2369231</td><td>RS PRO</td><td>16/0.2mm</td><td>3</td><td>100</td><td>Unscreened</td></td<>	2369231	RS PRO	16/0.2mm	3	100	Unscreened
2369234 RS PRO 16/0.2mm 4 25 Unscreened 2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25<	2369232	RS PRO	16/0.2mm	3	25	Unscreened
2369239 RS PRO 16/0.2mm 6 100 Unscreened 2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369226 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 8 100 Screened 2369273 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100<	2369233	RS PRO	16/0.2mm	4	100	Unscreened
2369240 RS PRO 16/0.2mm 6 25 Unscreened 2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369226 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369234	RS PRO	16/0.2mm	4	25	Unscreened
2369219 RS PRO 16/0.2mm 12 100 Unscreened 2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369239	RS PRO	16/0.2mm	6	100	Unscreened
2369220 RS PRO 16/0.2mm 12 25 Unscreened 2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369240	RS PRO	16/0.2mm	6	25	Unscreened
2369225 RS PRO 16/0.2mm 18 100 Unscreened 2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369219	RS PRO	16/0.2mm	12	100	Unscreened
2369226 RS PRO 16/0.2mm 18 25 Unscreened 2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369220	RS PRO	16/0.2mm	12	25	Unscreened
2369262 RS PRO 7/0.2mm 4 100 Screened 2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369225	RS PRO	16/0.2mm	18	100	Unscreened
2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369226	RS PRO	16/0.2mm	18	25	Unscreened
2369263 RS PRO 7/0.2mm 4 25 Screened 2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened						
2369264 RS PRO 7/0.2mm 4 500 Screened 2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369262	RS PRO	7/0.2mm	4	100	Screened
2369268 RS PRO 7/0.2mm 6 100 Screened 2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369263	RS PRO	7/0.2mm	4	25	Screened
2369269 RS PRO 7/0.2mm 6 25 Screened 2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369264	RS PRO	7/0.2mm		500	Screened
2369273 RS PRO 7/0.2mm 8 100 Screened 2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369268	RS PRO	7/0.2mm	6	100	Screened
2369274 RS PRO 7/0.2mm 8 25 Screened 2369247 RS PRO 7/0.2mm 12 100 Screened	2369269	RS PRO	7/0.2mm	6	25	Screened
2369247 RS PRO 7/0.2mm 12 100 Screened	2369273	RS PRO	7/0.2mm	8	100	Screened
	2369274	RS PRO	7/0.2mm	8	25	Screened
2369248 RS PRO 7/0.2mm 12 25 Screened	2369247	RS PRO	7/0.2mm	12	100	Screened
	2369248	RS PRO	7/0.2mm	12	25	Screened



2369252	RS PRO	7/0.2mm	20	100	Screened
---------	--------	---------	----	-----	----------

Similar Products

Stock No.	Brand	Conductor	Number of cores	Reel length	Screened/Unscreened
2369253	RS PRO	7/0.2mm	20	25	Screened
2369257	RS PRO	7/0.2mm	36	100	Screened
2369258	RS PRO	7/0.2mm	36	25	Screened
2369235	RS PRO	16/0.2mm	4	100	Screened
2369236	RS PRO	16/0.2mm	4	25	Screened
2369237	RS PRO	16/0.2mm	4	500	Screened
2369241	RS PRO	16/0.2mm	6	100	Screened
2369242	RS PRO	16/0.2mm	6	25	Screened
2369243	RS PRO	16/0.2mm	6	500	Screened
2369221	RS PRO	16/0.2mm	12	25	Screened
2369223	RS PRO	16/0.2mm	12	50	Screened
2369224	RS PRO	16/0.2mm	12	500	Screened
2369227	RS PRO	16/0.2mm	18	25	Screened
2369228	RS PRO	16/0.2mm	18	50	Screened