


Pluggable Terminal Blocks

3.5 mm Pitch, Closed Ended, Horizontal



Closed ended

Closed headers

Polarised mouldings

Guided pin alignment

Pin/terminal - Tinned phosphor bronze

Rising clamp - Nickel copper flash brass

Screw/torque - M2 steel Tin plated, 0.3Nm

Recommended PCB hole size ϕ 1.2 mm

SPECIFICATION:

Gender of contacts	Male
Rated current to EN	10 A
Pitch	3.5 mm
Termination type	Solder Pin [PCB, Through-Hole]
Rated voltage to EN	200 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-33...+120 °C

PRODUCT RANGE:

Art. Nr.	Poles	A	Length	Connection direction
RND 205-00111	2	8.4 mm	8.4 mm	horizontal
RND 205-00112	3	11.9 mm	11.9 mm	horizontal
RND 205-00113	4	15.4 mm	15.4 mm	horizontal
RND 205-00114	5	18.9 mm	18.9 mm	horizontal
RND 205-00115	6	22.4 mm	22.4 mm	horizontal
RND 205-00117	8	29.4 mm	29.4 mm	horizontal
RND 205-00118	9	32.9 mm	32.9 mm	horizontal