


# Crimp Fittings

# Press-armaturen

# Embouts sertis

# Raccordi a graffare

# Racores para presión




## DSB

DKO Female Swivel, Heavy Duty, 90° Elbow  
 Dichtkopf DKOS, schwere Baureihe, 90° Krümmer  
 DKO série S coudé 90°  
 Femmina girevole DKOS a 90°, serie pesante  
 Hembra loca DKOS, acodado a 90°, serie pesada

Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5DSB3	1S5DSB3	1A5DSB3	M16x1,5		8	5	-3	44,5	27,0	30,5	2,5	19	14	
1G5DSB4	1S5DSB4	1A5DSB4	M16x1,5		8	6	-4	54,0	30,6	28,6	4,2	19	14	
1G6DSB4	1S6DSB4	1A6DSB4	M18x1,5		10	6	-4	54,5	31,0	33,5	4,2	22	17	
1G6DSB5	1S6DSB5	1A6DSB5	M18x1,5		10	8	-5	53,9	30,0	33,5	5,3	22	17	
1G8DSB5	1S8DSB5	1A8DSB5	M20x1,5		12	8	-5	56,9	33,0	36,5	5,3	24	19	
1G8DSB6	1S8DSB6	1A8DSB6	M20x1,5		12	10	-6	59,9	34,6	35,3	6,7	24	19	
1G10DSB6	1S10DSB6	1A10DSB6	M22x1,5		14	10	-6	63,8	38,5	42,0	6,7	27	19	
1G12DSB8	1S12DSB8	1A12DSB8	M24x1,5		16	12	-8	77,7	48,0	45,3	9,6	30	22	
1G16DSB10	1S16DSB10	1A16DSB10	M30x2,0		20	16	-10	82,0	52,6	52,0	12,8	36	27	
1G20DSB12	1S20DSB12	1A20DSB12	M36x2,0		25	19	-12	93,0	62,8	64,6	15,5	46	32	
1G25DSB16	1S25DSB16	1A25DSB16	M42x2,0		30	25	-16	104,0	69,6	74,0	20,7	50	36	

## EK

24° Male, Heavy Duty  
 Außengewindeanschluss 24°, schwere Baureihe  
 Mâle 24° série forte  
 Maschio metrico 24°, serie pesante  
 Macho fijo de 24°, serie pesada



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5EK3	1S5EK3	1A5EK3	M16x1,5		8	5	-3	41,0	23,5		2,5	17		
1G5EK4	1S5EK4	1A5EK4	M16x1,5		8	6	-4	47,5	24,1		4,2	17		
1G6EK4	1S6EK4	1A6EK4	M18x1,5		10	6	-4	47,0	23,6		4,2	19		
1G8EK5	1S8EK5	1A8EK5	M20x1,5		12	8	-5	48,2	24,3		5,3	22		
1G8EK6	1S8EK6	1A8EK6	M20x1,5		12	10	-6	50,3	25,0		6,7	22		
1G10EK6	1S10EK6	1A10EK6	M22x1,5		14	10	-6	52,6	27,3		6,7	24		
1G12EK8	1S12EK8	1A12EK8	M24x1,5		16	12	-8	58,0	28,3		9,6	27		
1G16EK10	1S16EK10	1A16EK10	M30x2,0		20	16	-10	62,0	32,6		12,8	32		
1G20EK12	1S20EK12	1A20EK12	M36x2,0		25	19	-12	65,5	35,3		15,5	41		
1G25EK16	1S25EK16	1A25EK16	M42x2,0		30	25	-16	72,3	37,9		20,7	46		
1G32EK20	1S32EK20	1AP32EK20*	M52x2,0		38	31	-20	88,0	44,0		26,6	55		
		1AT32EK20**	M52x2,0		38	31	-20	88,0	44,0		26,6	55		

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

Specification subject to change without notice