



30A 3Ø 480V AC
 NEMA L16-30R
 UL/CSA
 10 HP



30A 3Ø 600V AC
 NEMA L17-30R
 UL/CSA

Connector Bodies


Watertight Safety-Shroud®		IP66 SUITABILITY	UL Type 4x, 12
Description	Cord Dia.	Catalog Number	
Black Valox® housing, white Valox® clamps.	.350"-1.150" (9-29)	HBL2733SW	HBL2743SW

Insulgrip®		IP20 SUITABILITY
Description	Cord Dia.	Catalog Number
Black and white nylon.	.350"-1.150" (9-29)	HBL2733 HBL2743
Corrosion resistant, yellow nylon.	.350"-1.150" (9-29)	HBL27CM33 HBL27CM43


Note: See page B-53 for accessories.




HBL2733SW



HBL2733



HBL2730SW



HBL2730AR

Receptacles

Watertight Safety-Shroud®		IP66 SUITABILITY	UL Type 4x, 12
Description	Catalog Number		
Gray Valox® housing and flange, back wired.	HBL2730SW HBL2740SW		

Note: See page B-54 for accessories.

Safety-Shroud® Twist-Lock®		IP20 SUITABILITY
Description	Catalog Number	
Gray Valox® angle housing, one gang, back wired.	HBL2730AR HBL2740AR	
Gray Valox® surface mounting, one gang, back wired.	HBL2730SR HBL2740SR	
Gray Valox® semi-flush, two gang, back wired.	HBL2730SR2 HBL2740SR2	

Note: See page B-54 for accessories.

Single Flush Receptacles		IP20 SUITABILITY
Description	Catalog Number	
Black nylon face, back and side wired.	HBL2730 HBL2740	

Note: See page B-52 for accessories.


Insulgrip® Flanged Receptacles

Description	Catalog Number
Nylon casing, back wired.	HBL2736 HBL2746


Note: See page B-52 for accessories.




HBL2736



HBL2730



HBL2730SR2



HBL2730SR

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.

Dimensions in Inches (mm)