

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191890015**  
**Status:** **Active**  
**Overview:** Splices  
**Description:** Krimptite Butt Splice for 10-12 AWG Wire

**Documents:**

Drawing (PDF) Product Specification PS-19902-013-001 (PDF)  
Product Specification 194130103-000 (PDF) RoHS Certificate of Compliance (PDF)  
Product Specification PS-19902-011-001 (PDF)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Splices  
 Series 19189  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview Splices  
 Product Name Butt, Krimptite  
 UPC 800755048872

**Physical**


Barrel Type Closed  
 Insulation None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.742/g  
 Packaging Type Bag  
 Wire Size AWG 10, 12

**Material Info**

Engineering Number C-146

**Reference - Drawing Numbers**

Product Specification 194130103-000, PS-19902-011-001,  
 PS-19902-013-001  
 Sales Drawing SD-19189-008



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

19189 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade Hand Crimp Tool	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>