

Hot air tool

# HL 1820 S - 240V

UK  
EAN 4007841 012663  
Article number 012663



## Function description

All-rounder on 3 levels. The three-stage HL 1820 S hot air tool with three temperature settings: 50, 400 and 600°C. A real all-rounder for de-icing, drying, shaping, heat shrinking, paint stripping, soft-soldering and much more.

## Technical specifications

Temperature	50 – 600 °C	Function, life expectancy, heating element	600 h
Airflow rate	100 – 500 l/min	Replaceable heating element	No
Temperature setting	3-stage	Restart protection	No
Settings made via	multiple-stage switch	Temperature scanner	No
Programming function	No	Thermal cut-out	Yes
Loc function	No	Thermostat	No
Residual heat indicator	Yes	Nozzle receiver, type	34
Cool function	No	Cord length	2.2 m
Motor, type	Brush motor	Dimensions (L x W x H)	253 x 85 x 200 mm
Heating element	Micanite heating element	PU1, net weight	0,83 kg
Mains power supply	220 – 230 V / 50 – 60 Hz	Manufacturer's Warranty	3 years
Function, hanger	Yes	PU1, EAN	4007841012663
Function, life expectancy, motor	600 h		

## Accessories

EAN 4007841 009625	HL Light
EAN 4007841 034566	HL Tool Stand
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070410	Window nozzle 75 mm
EAN 4007841 070311	Window nozzle 50 mm

<https://www.steinell.de>

Subject to technical modifications

10.2022 Page 1 from 2

Hot air tool

# HL 1820 S - 240V

UK  
EAN 4007841 012663  
Article number 012663



## Accessories

EAN 4007841 010317	Paint Scraper Set
EAN 4007841 070519	Reflector nozzle
EAN 4007841 006655	Crimp connectors - Ø 0.5 - 1.5 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm
EAN 4007841 006648	Crimp connectors - Ø 1.5 - 2.5 mm
EAN 4007841 071417	Shrink tubing II - Ø 4,8 - 9,5 mm
EAN 4007841 071318	Shrink tubing I - Ø 1,6 - 4,8 mm
EAN 4007841 072766	Shrink tubing III - Ø 4,8 - 12,0 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E