

Fluorescent T5 (Bakery)

FHE 35W T5 FoodStar Bread
0001860

Product features

- T5 fluorescent lamp for bakery.



PRODUCT OVERVIEW

Product name	FHE 35W T5 FoodStar Bread
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T5
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Hospitality, Residential & Consumer, Retail
ETIM Class	EC000108
E-number FI	4940490
E-number Norway	3815476
Colour temperature (K)	2300
Light colour	Foodstar Bread
CRI (Ra)	83
Colour Variation Initial (SDCM)	SDCM5
Wattage (W)	35.00
Product Voltage (V)	209
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	24000
Product EAN number	5410288018607

DATA TABLE

General data

Product name	FHE 35W T5 FoodStar Bread
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T5
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open

Fluorescent T5 (Bakery) *FHE 35W T5 FoodStar Bread* 0001860

General application	Hospitality, Residential & Consumer, Retail
ETIM Class	EC000108
E-number FI	4940490
E-number Norway	3815476

Optical data

Ambient temperature for maximum luminous flux (°C)	35
Colour temperature (K)	2300
Correlated colour temperature range (K)	2100 - 2500
Light colour	Foodstar Bread
CRI (Ra)	83
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N

Electrical data

Wattage (W)	35.00
Equivalent watt (W)	35
Watt (Rated) - High frequency (W)	34.00
Current (A)	0.170
Product Voltage (V)	209
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	170
Lamp Energy Label (class)	F

Lifetime data

Average life (Nominal) (h)	24000
----------------------------	-------

Physical data

Nominal Product Length (mm)	1450.0
Nominal Product Diameter (mm)	16
Max. Length base to base (mm) - A	1449.0
Length base to pin Min-Max (mm) - B	1453.7-1456.1
Max. Lamp Length (mm) - C/L	1463.2
Max. Lamp Diameter (mm) - D	17.0
Weight (kg)	0.109

Packaging

Single packaging type	Carton
Product EAN number	5410288018607
Packaging single length / height (cm)	146.4
Packaging single width (cm)	1.9
Packaging single depth (cm)	1.9
DUN14 (outer)	15410288018604
Units per outer package	25
Packaging outer length / height (cm)	148.0

Fluorescent T5 (Bakery)

FHE 35W T5 FoodStar Bread
0001860

Packaging outer width (cm)	10.5
Packaging outer depth (cm)	10.5

Safety data

Lamp mercury content (mg)	2.30
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Suitable for household illumination	No

TECHNICAL DRAWINGS

