

## Electronic micrometer set

0-102 mm IP67



### Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

### Execution:

- Carbide measuring faces
- Zero setting at any position
- mm/inch switch-over
- Auto off
- Preset function
- ABS function

### Advantage:

- IP67 protection also with data cable
- Non-rotating spindle
- Switchable measuring force 5 N/10 N at 0-30 mm
- 12 mm adjustment with a single turn

### Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032) and setting gauges



<b>Art. no.</b>	<b>31412 400</b>
<b>Brand</b>	SYLVAC
<b>Manufacturer Part Number</b>	903.1300.10
<b>Min./max. length measuring range</b>	0-102 mm
<b>Digit increment</b>	0.001 mm
<b>Data transmission type</b>	Proximity
<b>Measuring surface diameter</b>	6.5 mm
<b>Measuring spindle increments</b>	12 mm
<b>IP protection class</b>	IP 67
<b>Spindle clamping</b>	No
<b>Number of bracket measuring screws</b>	3
<b>Number of setting dimensions</b>	2
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>DIN</b>	863
<b>Calibration Group</b>	D, E
<b>Gross Weight</b>	2.325 kg
<b>Product Group</b>	317

### EAN

7640125714203