

## Shelf boltless rack, single-row

Plastic-coated RAL 7035



### Application:

Universal shelving system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools

### Execution:

- Shelves height-adjustable in increments of 25 mm for variable adaptation to stored goods
- Shelves with a 50 mm hole grid to accommodate accessories, shelf edge height 40 mm
- For technical reasons, depth reinforcements are always zinc plated, even with coated frames
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm
- With dismantled or pre-assembled frame

### Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



<b>Art. no.</b>	<b>50167 604</b>
<b>Brand</b>	META
<b>Manufacturer Part Number</b>	20067932
<b>Height</b>	2000 mm
<b>Length</b>	1356 mm
<b>Depth</b>	436 mm
<b>Nominal length</b>	1300 mm
<b>Nominal depth</b>	400 mm
<b>Design</b>	Shelving unit
<b>Type of assembly</b>	To insert
<b>Surface</b>	Plastic-coated
<b>Design of the frame</b>	Pre-assembled
<b>Grid dimension</b>	25 mm
<b>Number of shelves</b>	4 PCS
<b>Load-carrying capacity per shelf</b>	230 kg
<b>Load-carrying capacity per field</b>	1650 kg
<b>Number of frame</b>	2 PCS
<b>Quality label</b>	RAL-RG 614/1
<b>Made in</b>	Germany
<b>Gross Weight</b>	33.513 kg
<b>Product Group</b>	508

### EAN

4026212088632