

## Series 600 zinc-plated table trolley, load capacity 500 kg

Load areas 1000x700 mm and 1200x800 mm



### Application:

For safely and easily transporting goods, parts and materials.

### Execution:

- Load areas covered with 2 mm electrolytically zinc-plated sheet steel
- Height of the lower load area 260 mm
- Distance between the load areas 580 mm
- Frame made of 25 mm steel tubing, galvanised
- 2 fixed castors and 2 swivel castors made of solid rubber 200 x 50 mm
- Load capacity of load areas: 250 kg each
- The 600 series also includes cabinet trolleys, front wall carriages and other variants

### Advantage:

- No need to go far to find your tools - work equipment is provided directly at the workstation
- Galvanised load areas - durable and robust



<b>Art. no.</b>	<b>50260 048</b>
<b>Brand</b>	KONGAMEK
<b>Manufacturer Part Number</b>	KM637-3B
<b>Load-carrying capacity</b>	500 kg
<b>Length</b>	1300 mm
<b>Length x width x height</b>	1300 x 800 x 870 mm
<b>ESD-capable</b>	No
<b>Number of loading surfaces</b>	2
<b>Loading surface size</b>	1200 x 800 mm
<b>Loading surface length</b>	1200 mm
<b>Loading-surface width</b>	800 mm
<b>Height</b>	870 mm
<b>Number of fixed rollers</b>	2
<b>Number of steering rollers</b>	2
<b>With wheel lock</b>	Yes
<b>Wheel width</b>	50 mm
<b>Wheel diameter</b>	200 mm
<b>Material of wheel</b>	Solid rubber
<b>Colour</b>	Silver coloured
<b>Surface</b>	Zinc plated
<b>Gross Weight</b>	72.000 kg
<b>Product Group</b>	5AT

### EAN

7350050357924