

## Lever crimping tool 0.5–4 mm<sup>2</sup> with universal crimp die

For crimping wire end ferrules with and without insulation (plastic collars)

**ATORN**<sup>®</sup>

### Application

For crimping wire end ferrules with and without insulation (plastic collars)

### Version

- According to DIN 46288 T.1 and T.4 from 0.5 to 4 mm<sup>2</sup> in a universal pressure die
- Omega spring ensures optimum, effortless power transmission
- Lever system with unlockable force stop function
- Adjustable crimping pressure
- Trapezoidal crimping

### Advantage

- Ergonomically shaped plastic handles for effortless work



<b>Art. no.</b>	<b>53508 007</b>
<b>Length</b>	204 mm
<b>Suitable for min./max. diameter</b>	0.5-4 mm
<b>Material of the grip handle</b>	Plastic

### EAN-Code

4050293716221