

CAT IV Pocket MultiMeter

Autoranging DMM with Non-Contact Voltage Detector and Built-in Flashlight
Includes Diode Test and Continuity Beeper Functions

Features:

- Large high contrast 4000 count LCD display
- Non-Contact Voltage detection identifies live circuits
- Built-in Flashlight
- 11 functions including Frequency, Capacitance, and Duty Cycle
- Built-in storage clips for integrated test leads
- Double molded housing provides extra protection
- Over-range and low battery indication
- Complete with test leads and two AAA batteries

Applications:

- Electrical repair
- Appliance repair
- Home wiring projects
- Testing electrical systems on cars and boats
- Hobby projects



Built-in Non-Contact Voltage Detector. Red LED bar lights when live wire detected.

Specifications	Range	Max. Resolution	Basic Accuracy (%rdg.+digits)
NC Voltage	100 to 600VAC		
DC Voltage	600V	0.1mV	±0.8%
AC Voltage	600V	1mV	±1.0%
Resistance	40MΩ	0.1Ω	±0.8%
DC Current	200mA	0.1μA	±2.0%
AC Current	200mA	0.1μA	±2.5%
Frequency	10kHz	0.001Hz	±1.0%
Capacitance	200μF	0.001nF	±3.0%
Duty Cycle	Yes		
Diode Test	Yes		
Continuity Test	Yes		
Dimensions	4.72 x 2.2 x 01.6" (120 x 55 x 40mm)		
Weight	5.12oz (145g)		

Ordering Information:

- DM220Mini Pocket MultiMeter
409992Vinyl pouch case

