

SPECIFICATIONS

Performance level	PL2
Filter type	C
Capacitance	3900 pF $\pm 20\%$
Working voltage	100 V
Current rating	7,5 A
Insulation resistance	>1 G Ω

FREQUENCY (MHz)	ATTENUATION (dB)
5	6
10	11
50	25
100	35
500	35
1000	32


PCB Layout, component side, thickness 1,6 mm

A

09 64 424 7243	M3
09 64 424 7242	4-40 UNC-2B
Part number	Nut thread

Mod.	Dot.	Name	Det.	Name
			Detail.	08/07/02 CV
36283	12/01/12	SD	Insp.	12/01/12 JB
35300	01/12/08	PK	Stand.	
33800	02/08/06	PK		
31058	08/07/02	CV		

HARTING EURL
F-95972 Paris



D-Sub, male, angled, 37 poles, turned solder pins, clinch nuts and brackets with board locks

TB 09 64 424 724X
Sub.

Maßstab/
Scale
1,5:1
Blatt/
Page
1/4