


PeakTech® TF-50 PROD-ID: P TF-50



Bead Probe, -50 ... +250° C

This temperature probe is typ-K-thermocouples (NiCrNi). This probe is suitable for all of our thermometers published in our catalogue. Bead probe for general Purpose application; not suitable for immersion in liquids.

Model	P TF-50
Range	-50 °C.....+250°C/ -58 °F...+ 482°F
Accuracy	± 0,5 %
Cable length	200 cm
Probe	1,5 mm
EAN-13	4250569401671

