

# **TECHNICAL INFORMATION**

## **ADHESIVE TAPE: PP Acrylic 25mic Low-Noise**

### **FILM PROPERTIES**

Type of Film	Biaxially Oriented Polypropylene (BOPP)
Film Colour	Transparent
Film Thickness (mic)	25 ± 1
Tensile Strength MD (N/mm <sup>2</sup> )	130 ± 30
Elongation at Break MD (%)	140 ± 30

### **ADHESIVE PROPERTIES**

Type of Adhesive	Acrylic (Water-based)
Colour	Transparent / Brown
Peel Adhesion (N/25mm)	5.5 ± 1
Shear Adhesion (h, 25mm x 25mm on stainless steel, 23°C)	Over 170
Rolling Ball Tack (cm)	3

The recommended storage conditions for this product are around 21 °C and 50% relative humidity. Prior to use, carefully check that the contact surfaces are totally dry and clean from oil, grease and dust. The data stated above cannot be considered as binding by contract or by specifications. They correspond to the average values obtained from the tests carried out according to Atlas Tapes norms, in conformity with AFERA norms. Tests are carried out on samples taken from our standard production. These data may vary without any notice – the updated typical value sheets can be forwarded at any time. Since many different factors may influence the product's performance, we recommend testing the product by any application. We remain at your disposal for any further information or recommendations.