

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008560106](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK 396 Crimp Terminal 2478, 18-24 AWG, Bag, Brass, 0.51µm Selective Gold \(Au\)](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
 Series [2478](#)
 Application [Power, Wire-to-Board](#)
 Crimp Quality Equipment [Yes](#)
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-56-0105 \(Reel\)](#)
 Product Name [KK 396, KK 508](#)
 UPC [800753614215](#)

Physical

Gender [Female](#)
 Material - Metal [Brass](#)
 Material - Plating Mating [Gold](#)
 Material - Plating Termination [Gold](#)
 Net Weight [0.150/g](#)
 Packaging Type [Bag](#)
 Plating min - Mating [0.381µm](#)
 Plating min - Termination [0.051µm](#)
 Termination Interface: Style [Crimp or Compression](#)
 Wire Insulation Diameter [2.79mm max.](#)
 Wire Size AWG [18, 20, 22, 24](#)
 Wire Size mm² [N/A](#)

Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Engineering Number [2478-1-\(550\)L](#)

Reference - Drawing Numbers

Packaging Specification [PK-2759-001](#)
 Product Specification [PS-08-50-001](#)
 Sales Drawing [SD-2478](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2478 Series](#)

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,
[5239](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION