

WEATHERPROOF HORN Loudspeakers



- PH20/T
- PH20/TC

TECHNICAL SPECIFICATIONS


Rated power, Watts	20
Tappings 100 volt line, Watts	20/10/5/2.5
Transformer Impedance, Ohms, 100V	500/1k/2k/4k
Tappings 70.7 volt line, Watts	10/5/2.5/1.25
Driver impedance, Ohms	20
Effective frequency range, Hz (BSEN60268-5)	250-8,000
S.P.L. @ 1m, 1 watt, dB, Test Signal Bandwidth 100Hz-10 kHz	101
S.P.L. @ Full power, Octave Bandwidth, dB	114
Acoustic Power (dB-PWL@1 watt) 1 kHz, dB	98/98
Dispersion at 1k/2kHz, Degrees	130/70
Directivity Axial Q factor, 1 k/2kHz	4.9/13.6
Dimensions, front & depth, mm	Ø203 x 254
Net weight, Kgs	1.7
Colour/Finish	Grey RAL7035
Material	ABS plastic housing with UV inhibitors
Mounting	Stainless Steel U Bracket

- PH20/TC is BS5839 Part 8 Voice Alarm compliant

▶ PH20/T ▶ PH20/TC


WEATHERPROOF HORN LOUSPEAKERS

▼ side view
unit: mm




CE


▼ front view
unit: mm



▼ circuit diagram
PH20/T



speech octave band sensitivity



Penton UK Ltd

Unit 2 Teville Industrials | Dominion Way | Worthing | West Sussex | BN14 8NW
T: +44 (0)1903 215315 | F: +44(0)1903 215415 | E: SALES@PENTONUK.CO.UK

www.pentonuk.co.uk