

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



RJ45 coupling, Degree of protection: IP20, Number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), Material: Fiberglass, PBT, Connection method: Female, Keystone



## **Key Commercial Data**

Packing unit	5 STK
Minimum order quantity	5 STK
GTIN	4 017918 876937
GTIN	4017918876937
Weight per Piece (excluding packing)	9.620 g
Custom tariff number	85366990
Country of origin	Germany

#### Technical data

#### Mechanical characteristics

Number of positions	8
Number of slots	1
Shielded	yes
Insertion/withdrawal cycles	≥ 1000
Connection method	Female
Insulation resistance	500 ΜΩ
Degree of protection	IP20

#### Ambient conditions

Ambient temperature (operation)	-20 °C 60 °C

## Material data

Flammability rating according to UL 94	V0
Housing material	Fiberglass, PBT
Housing surface material	metal-plated

01/24/2017 Page 1 / 5



## Technical data

## Material data

Contact carrier material	ABS
Contact material	Copper alloy
Contact surface material	Gold over nickel

#### Electrical characteristics

Number of positions	8
Nominal voltage U <sub>N</sub>	150 V
Nominal current I <sub>N</sub>	1.5 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
GRP transmission properties	CAT5 (IEC 11801:2002)
Transmission speed	1 Gbps
Rated current	1.5 A
Overvoltage category	II
Degree of pollution	2
Dielectric strength	1000 V AC (60 Hz, 1 min)
Contact resistance	20 mΩ
Rated voltage (III/3)	150 V

## Standards and Regulations

Flammability rating according to UL 94	V0

## **Environmental Product Compliance**


China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


## **Drawings**

## Schematic diagram



## Dimensional drawing





RJ45 socket insert, keystone



## Articles in set

RJ45 coupling - VS-08-BU-RJ45/BU - 1689064



RJ45 coupling, Degree of protection: IP20, Number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), Material: Fiberglass, PBT, Connection method: Female, Keystone

## Classifications

## eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440312
eCl@ss 8.0	27440205
eCl@ss 9.0	27440205

#### **ETIM**

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438
ETIM 6.0	EC000438

### **UNSPSC**

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

## Approvals

Approvals

Approvals

EAC

Ex Approvals



## Approvals

Approval details

EAC

EHE

B.01742

### Accessories

Accessories

Panel mounting frame

Panel mounting frames - VS-08-A-RJ45/MOD-1-IP20 - 1689433



RJ45 panel mounting frame, 1x, IP20, for modular socket inserts (Keystone), without mounting screws

Panel mounting frames - VS-08-A-RJ45/MOD-1-R-IP67 - 1689844



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for round panel cutout, with grommet, with thread and union nut, color: gray

Panel mounting frames - VS-08-A-RJ45/MOD-1-IP67 - 1689080



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws, color: gray

Panel mounting frames - VS-08-A-RJ45/MOD-1-R-IP67 BK - 1658053



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for round panel cutout, with grommet, with thread and union nut, color: black



#### Accessories

Panel mounting frames - VS-08-A-RJ45/MOD-1-IP67-BK - 1658642



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws, color: black

Panel mounting frames - VS-08-A-S-RJ45/MOD-1-R-IP67 - 1654772



RJ45 panel mounting frame, IP67, irradiated for welding applications, for modular socket inserts (Keystone), for round panel cutout, with grommet, with thread and union nut

Panel mounting frames - VS-08-A-S-RJ45/MOD-1-IP67 - 1652868



RJ45 panel mounting frame, IP67, irradiated for welding applications, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws

Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com