

## Coaxial Panel Connector 22\_BNC-50-0-5/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 4 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0074 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing DOU-00010863  
Catalogue drawing DCA-00010865  
Mounting hole DOU-00008762

### Ordering Information

Bulk 100 pcs package 22\_BNC-50-0-5/133\_NH  
Single package 22\_BNC-50-0-5/133\_NE