

Han SC module, female without ferrules



Part number	09 14 004 4712
Specification	Han SC module, female without ferrules
HARTING eCatalogue	https://b2b.harting.com/09140044712

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] SC module
Size of the module	Single module
Version	
Gender	Female
Number of contacts	4
Details	Please order contacts separately. Please order fixing plate separately.
Technical characteristics	
Limiting temperature	-40 +85 °C
Mating cycles	≥500
Material properties	
Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Page 1 / 2 | Creation date 2024-04-26 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)
Specifications and approvals	
Approvals	DNV GL
Commercial data	
Packaging size	2
Net weight	6.98 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140020214
	50000400
ETIM	EC000438