

Lineal recessed 1400 Wit 2320lm 3000K Ra>80 DALI

Artikelcode: 8246095677
 EAN: 5703821180184



Elektrisch

System wattage: 21W
 Spanning: 220-240V
 Max. armaturen per stroomonderbreker: B10: 13, B16: 20, C10: 21, C16: 33

Lichttechniek

Soort lichtbron: LED
 Luminous flux: 2320lm
 Werkzaamheid: 110 lm/W
 Kleurtemperatuur: 3000K
 Kleurweergave (CRI): Ra>80
 MacAdams factor: SDCM: 3
 levensduur: L80/B10>100,000
 Lichtverdeling: Direct
 UGR: UGR<28
 Fotobiologische veiligheid: RG 0

Controle/dimmen

Type: DALI

Bescherming

Isolatieklasse: Klasse I

Energie en goedkeuringen

Bevat een lichtbron met energieklasse: C

Materiaal en afwerking

Behuizing: Aluminium
 Kleur: Wit (RAL 9003)

Montage/Aansluiting



Montage: Inbouw, Binnen
 Module: 1400
 Aansluiting: 5 pol Winsta mini og 5x1,5 doorvoerbedrading

Afmetingen

Lengte (mm) L: 1401
 Breedte (mm) W: 62
 Hoogte (mm) H: 62
 Gewicht (kg) bruto/netto: 2.9 / 2.6

Verpakking

Verpakkingsafmetingen (mm): 1505 x 71 x 64



5 7 0 3 8 2 1 1 8 0 1 8 4