

Wheeled workbench, working height 970 mm

With 4 drawers, 1 shelf and 1 extra large drawer

Application:

The mobile workstation with versatile options for use.

Execution:

- Solidly welded sheet steel structure with end-to-end closed rear wall
- Push handlebar on one front side
- Workbench top panel made of solid beech, glued together longitudinally in bars, thickness 40 mm
- Optionally with integrated housing on the side, fitted with easy-view tilting bins



Art. no.	50272 111
Brand	HK
Manufacturer Part Number	50272111
Number of fixed rollers	2 PCS
Working height	970 mm
Number of steering rollers	2 PCS
Worktop width	1140 mm
Number of drawers	4 PCS
Worktop height	40 mm
Number of doors	1 PCS
Worktop depth	650 mm
Pullout type	Partial extension
On castors	Yes
Moving device, can be lowered	No
Colour of front	Anthracite grey RAL 7016
Cabinet colour	Light grey RAL 7035
With single pull-out safety brake	No
Surface	Powder-coated
With wheel lock	Yes
Load-carrying capacity	600 kg
Dynamic load-carrying capacity	400 kg
Wheel diameter	125 mm
Type	mobile
Lock type	Cylinder lock
Material of worktop	Solid beech
Drawer front height	1 x 150 mm, 1 x 90 mm, 1 x 180 mm, 1 x 270 mm
Material	Sheet steel
Drawer width (inner dimension)	940/410 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	940/410 x 540 mm
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of wheel	Polyurethane
Central locking	Yes
Gross Weight	110.000 kg
Product Group	501

EAN

4053625403141