

## Voltage tester DUSPOL expert

Voltage tester with LED display

**BENNING**

### Application:

for use in all installation fields and renewable energy sectors. CAT IV 690 V, CAT III 1000 V.  
Tested and approved in line with DIN EN 61243-3(VDE 0682-401):2015.

### Version:

- Continuity test (acoustic/optical) Cable breakage detector Voltage indication from 50 V even with empty batteries High voltage display



<b>Art. no.</b>	<b>75017 032</b>
<b>Model</b>	DUSPOL expert
<b>Display</b>	LED, Audible
<b>Max. continuity test</b>	100 kOhm
<b>Min./max. voltage range AC</b>	12-1000 V/AC
<b>Min./max. voltage range DC</b>	12-1000 V/DC
<b>Min./max. continuity test</b>	0-100 kOhm
<b>Phase-sequence test</b>	Yes
<b>Phase sequence test</b>	Yes
<b>Polarity testing</b>	Yes
<b>Vibration control system</b>	Yes
<b>Measurement point lighting</b>	Yes
<b>IP protection class</b>	IP 65
<b>Length x width x height</b>	330 x 85 x 55 mm
<b>Weight</b>	0.37 kg
<b>Overvoltage protection category</b>	CAT IV/600 V, CAT III/ 1000 V

### EAN-Code

4014651502628