

Vario Starpoint VRS-F type metric ring bolt

Screwable sling point, 360° rotation



Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% electromagnetically crack-tested in accordance with DIN EN 1677-1
- Patented 100% crack-tested hexagon socket screw, non-detachable
- can be rotated 360°
- Stated carrying capacity for adverse load area F
- Powder-coated surface: pink, fluorescent

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing
- Tool-free assembly

Delivery:

Includes annealed star profile key for tool-free assembly. Special lengths and other threads upon request.



Art. no.	77232 020
Brand	RUD
Manufacturer Part Number	25250000015192
Thread dimension	M20
Load-carrying capacity	2300 kg
Distance between lower edge of retainer holder and retainer	58 mm
Internal width	40 mm
Width of support plate	41 mm
Usable thread length	30 mm
Colour	Pink
Gross Weight	0.631 kg
Product Group	781