

Lok-it! 1200 W 80 V/32/P50

Lok-it! | Halogen lamps



Product datasheet

Technical data


Electrical data

Nominal wattage	1200 W
Nominal voltage	80.0 V

Photometrical data

Nominal luminous flux	20000 lm
Luminous flux	37500 lm
Color temperature	3200 K

Dimensions & weight



Diameter	25.0 mm
Length	129.5 mm
Light center length (LCL)	84.0 mm
Illuminated field	14.7*14.5 mm ²

Lifespan

Lifespan	250 h
----------	-------

Additional product data

Base (standard designation)	-
-----------------------------	---

Capabilities

Burning position	Any
------------------	-----

Certificates & standards

EEL – Energy Label	B
--------------------	---

Product datasheet

Country specific categorizations

Order reference	LOK-IT! 1200W 8
-----------------	-----------------

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321382795	Lok-it! 1200 W 80 V/32/P50	Folding carton box 1	70 mm x 70 mm x 160 mm	0.78 dm ³	178.00 g
4008321382801	Lok-it! 1200 W 80 V/32/P50	Shipping carton box 12	294 mm x 222 mm x 175 mm	11.42 dm ³	5393.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.