



Verbindungstechnik

Steckhülsen und Flachstecker isoliert 2,8 mm

Clips femelles et languettes plates isolés

Receptacles and taps insulated

DIN 46245/1

- * ausgenommen
- * excepté
- * excepted

UL-No. E235796

mit Stützhülse

Werkstoff:

MS sn = Messing verzinkt

Temperaturbeständigkeit:

PVC -10°C bis +75°C

PA -55°C bis +105°C

Strombelastbarkeit:

0.5 – 1.0 mm²/10A max.

1.5 – 2.5 mm²/15A max.

avec douille-support

Matière:

MS sn = laiton étamé

Résistant à une température de:

PVC -10°C à +75°C

PA -55°C à +105°C

Intensité admissible:

0.5 – 1.0 mm²/10A max.

1.5 – 2.5 mm²/15A max.

with extra support-sleeve

Material:

MS sn = tin-plated brass

Temperature range:


PVC -10°C up to +75°C

PA -55°C up to +105°C

Current carrying capacity:

0.5 – 1.0 mm²/10A max.

1.5 – 2.5 mm²/15A max.



PVC									
mm ²	AWG	Größe Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	A mm	øD mm	Werkzeuge Outils Toolings
0.14-0.5	26-22	2.8 x 0.5		389805	46245	16	7.8	1	3974n, 3984l, 3984lx
	26-22	2.8 x 0.8		389808	46245	16	7.8	1	
0.5-1	22-18	2.8 x 0.5		390005	46245/T1	19	10.5	1.7	3974n, 3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s
	22-18	2.8 x 0.8		390008	46245/T1	19	10.5	1.7	
1.5-2.5	16-14	2.8 x 0.5		389905	46245	19.5	10.5	2.3	
	16-14	2.8 x 0.8		389908	46245	19.5	10.5	2.3	