



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [ ] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE	TITLE	SCALE	PART NO.	SHEET
1 BODY	BRASS	GOLD		DRAWN G.R.S.	04/29/99	<b>Connex</b> Connector Corporation MMCX CRIMP JACK (FOR RG-316/u DOUBLE BRAID CABLE)	NA	262119	1 OF 1
2 INSULATOR	TEFLON	NATURAL		CHECKED			SIZE A	REV. N	
3 BARREL	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.3-6 ± 0.2 6-30 ± 0.4 30-120 ± 0.6 120-315 ± 1 315-1000 ± 1.6 1000-2000 ± 2.4	ISSUED			FSQA NO. 99001	DWG. NO. 262119.DWG	
4 CONTACT PIN	BER. COPPER	GOLD							
5 FERRULE	COPPER	GOLD							
6									
7									
8			DO NOT SCALE DRAWING						