

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 34_BNC-75-0-1/133_N

Rev.: C 

Description

Bulkhead adaptor jack/jack
BNC jack (female) / BNC jack (female)

Interface standards
Interface compatible with IEC 61169-8



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1 GHz

Mechanical Data

Number of matings 500
Weight 0.0169 kg

Environmental Data

Operating Temperature -65 °C to 165 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts (BNC)

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Gasket	MVQ (Silicone Rubber)

Piece Parts (BNC)

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Gasket	MVQ (Silicone Rubber)

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Mounting hole DOU-00008751

Ordering Information

Single package 34_BNC-75-0-1/133_NE
Bulk 100 pcs package 34_BNC-75-0-1/133_NH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions