

1) Tapered thread end max. 4P  
2) Trilobular cross-section

**BN 14551**

**Hexalobular (6 Lobe) socket pan head thread forming screws**

with slot and ribs, metric thread

Steel case-hardened 450-560 HV

zinc plated blue, added lubricant




ISO 4042

Quenched and tempered fasteners  $\geq 360$  HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!  
Further notice to residual risks can be found in the introduction section.



A technical brochure is available on request

Article#	d <sub>1</sub>	d <sub>2</sub> max.	k max.	n		t max.	L
1008625	M3	6	2,52	0,6	X10	1,2	5
1083368							6
1083449							8
3646072							10
3646073							12
5523780							16
1083546	M4	8	3,25	1	X20	1,9	6
1013394							8
1808206							10
1861719							12
3646074							16