


Artikel 224255/57



Power for entire lamp:	3.3W
Lumen for entire lamp:	200LM
Module power:	3.3W
Module Lumen:	250LM
color temperature	3000K
Ra:	>80
SMD LED QTY	28PCS
lifetime:	25000H
Voltage/current	5V1A
Water proof level	IP54
Switch:	touch switch
Material:	PC/ABS/Aluminium
Switch:	ON/OFF, touch dimming: 10% -100%
Energy efficiency level	G
type:	18650 lithium battery
specifications:	3.7V 1800mAh
Qty:	2pcs
Working time :	6-7H
Charging time:	6-7H