


E11774



Wirable socket

SDOGH050MSSFKPG



Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage [V]	< 45 AC / < 70 DC
Max. current load total [A]	4; (...40 °C)

Operating conditions

Ambient temperature [°C]	-25...100
Protection	IP 68

Mechanical data

Weight [g]	29.9
Dimensions [mm]	20 x 20 x 46
Materials	PA
Material nut	brass, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

screw terminals: ...0.75 mm²; Cable sheath: Ø 6...8 mm


Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated

E11774

Wirable socket

SDOGH050MSSFKPG



Connection

