

## MODLINK MSDD DATA INSERT

1 × SUB-D9 fem./fem.+1 × SUB-D9 male/male+1 × RJ45+1 × USB-A

RJ45; USB; SUB-D9 GC; SUB-D9 GC

1 × RJ45, 8-pole metal, CAT5e (female/female)

1 × USB (female/female) form A

1 × SUB-D9 GC (female/female)

1 × SUB-D9 GC (male/male)

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### General data

Dimensions H × W × D 88×51×45 mm

#### Insert 2

Article number	4000-68000-1140000
Operating voltage	SUB-D: max. 125 V AC/150 V DC; RJ45: max. 48 V AC/DC; RJ12: max. 48 V AC/DC; USB: max. 30 V AC/DC; PS2: max. 30 V AC/DC; DVI: max. 40 V AC
Operating current	SUB-D: max. 3 A; RJ45: max. 1 A; RJ12: max. 1 A; USB: max. 1 A; PS2: max. 1 A; DVI: max. 1.5 A
Connection cross section	SUB-D: max. 0.5 mm <sup>2</sup> (AWG 20); PS2: max. 0.22 mm <sup>2</sup> (AWG 24)
Locking of ports	SUB-D: UNC 4...40 bolt; RJ45: staple; RJ12: staple; USB: snap-in; PS2: snap-in
Specification	SUB-D: (DIN 41652/IEC 60807-1); RJ45: CAT5e (100 MHz - Mbit/s); USB: 2.0/Type 2dB (max. 480 Mbit/s)
Mounting depth mounted	SUB-D: approx. 32 mm; RJ45: approx. 32 mm; RJ12: approx. 32 mm; USB: approx. 80 mm; PS2: approx. 32 mm

Dimensions H x W x D	88x51x45
----------------------	----------

Shielded	no
----------	----

**Commercial data**

country of origin	CZ
-------------------	----

customs tariff number	85366990
-----------------------	----------

minimum order quantity	1
------------------------	---