


TECHNICAL INFORMATION

Type 98
Union Elbow 90° taper seat M/F
UA12

gebo®
fittings



SIZE	A [mm]	B [mm]	C [mm]	S1 [mm]	S2max [mm]	R/Rp Z1
3/8"	25	65	17	21,2	36	3/8"
1/2"	28	76	18	25	41	1/2"
3/4"	33	82	20	31	50	3/4"
1"	38	94	22	38	55	1"
1 1/4"	45	107	24	48	70	1 1/4"
1 1/2"	50	115	25	53,5	75	1 1/2"
2"	58	128	27	66,6	90	2"
2 1/2"	78	156	30	84	110	2 1/2"
3"	83	168	31	97	130	3"

Technical characteristics:

- products according to DIN EN 10242, Design Symbol A
- certified by DVGW CERT