

## Accessory

---

PICO-LPG-780-1064-BOX  
Order Number: 70144871

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		40	°C
Storage Temperature	-50		50	°C

## Optical Parameters

---

LB Rating	190-315 D LB8 + IR LB4
	315-420 DIR LB5
	420-445 DIR LB4
	765-1100 DIRM LB5
	775-1085 D LB5 + IRM LB6
	790-1080 D LB6 + IRM LB7
	950-1085 DIRM LB6

---

Lens Color	Grün
------------	------

## Mechanical Parameters

---

Material	Plastic
Weight	150 g

(\*) Over the complete operating temperature range

## Features

---



- Laser glasses for infrared wavelengths
- Incl. wall holder
- Stickers with mandatory and hazard sign


## Picture

---



## Safety Label

---



## Valid Revision

---

| 28-OCT-2020